

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517713

Luminaire Tested: HVL12-8-LD4-3STD-35-UNV-O-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517713
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL12-8-LD4-3STD-35-UNV-O-EDD-90
Description: 8 FOOT, 12 INCH WIDE, HVL LED LUMINAIRE, WITH 3500K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17414.0 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 1' x L: 8' x H: 0.17')
CIE Type: Direct


Input Watts (W): 196.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517713

CATALOG NUMBER: HVL12-8-LD4-3STD-35-UNV-O-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P517713

CATALOG NUMBER: HVL12-8-LD4-3STD-35-UNV-O-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			98
1	108	102	98	94	105	100	96	92	95	92	89	91	88	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	77	73	79	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	52	62	56	51	60	54	50			47
5	75	61	52	45	72	60	52	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	40	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7749	7749	7749
5°	7748	7624	7638
10°	7711	7535	7538
15°	7658	7430	7404
20°	7602	7305	7275
25°	7532	7175	7141
30°	7449	7034	6981
35°	7341	6875	6824
40°	7230	6706	6632
45°	7111	6519	6422
50°	6952	6297	6193
55°	6783	6052	5937
60°	6580	5717	5631
65°	6236	5338	5334
70°	5729	4882	4982
75°	4997	4382	4691
80°	3876	3915	4472
85°	2234	3491	4350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7111 cd/sqm

TEST NUMBER: P517713

CATALOG NUMBER: HVL12-8-LD4-3STD-35-UNV-O-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	545.0	3.1
10°-20°	1563.4	9.0
20°-30°	2372.2	13.6
30°-40°	2868.3	16.5
40°-50°	2992.9	17.2
50°-60°	2736.4	15.7
60°-70°	2133.2	12.2
70°-80°	1334.4	7.7
80°-90°	606.1	3.5
90°-100°	203.1	1.2
100°-110°	51.0	0.3
110°-120°	8.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4480.6	25.7
0°-40°	7348.9	42.2
0°-60°	13078.2	75.1
0°-90°	17151.9	98.5
90°-120°	262.2	1.5
90°-150°	262.2	1.5
90°-180°	262.0	1.5
0°-180°	17414.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5760	5760	5760	5760	5760	
5°	5747	5736	5711	5738	5738	546
15°	5529	5538	5523	5554	5553	1561
25°	5123	5127	5132	5176	5184	2360
35°	4535	4555	4574	4620	4639	2838
45°	3815	3849	3880	3918	3937	2940
55°	2978	3013	3068	3113	3134	2660
65°	2046	2081	2153	2239	2274	2024
75°	1036	1100	1260	1411	1464	1104
85°	179	331	569	752	819	227
90°	1	124	335	504	565	7
95°	1	33	174	315	364	1
105°	3	4	28	84	113	3
115°	4	4	5	15	22	3
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517713

CATALOG NUMBER: HVL12-8-LD4-3STD-35-UNV-O-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5759.5	5759.5	5759.5	5759.5	5759.5
2.5°	5766.3	5758.1	5732.3	5758.1	5756.8
5°	5747.3	5736.4	5710.6	5737.8	5737.8
7.5°	5709.3	5705.2	5682.1	5713.3	5713.3
10°	5664.5	5663.1	5644.1	5678.0	5679.4
12.5°	5602.0	5607.4	5589.8	5622.4	5626.4
15°	5528.7	5538.2	5523.3	5554.5	5553.1
17.5°	5448.6	5454.0	5443.1	5478.4	5477.1
20°	5349.5	5356.3	5348.1	5384.8	5388.8
22.5°	5239.5	5249.0	5247.6	5285.7	5296.5
25°	5122.7	5126.8	5132.2	5175.7	5183.8
27.5°	4993.7	5000.5	5010.0	5049.4	5057.6
30°	4852.5	4863.4	4874.3	4915.0	4925.9
32.5°	4703.2	4714.0	4727.6	4780.6	4786.0
35°	4534.8	4555.2	4574.2	4620.4	4639.4
37.5°	4366.5	4392.3	4409.9	4458.8	4473.7
40°	4188.6	4214.4	4242.9	4294.5	4304.0
42.5°	4002.6	4032.5	4066.4	4112.6	4128.9
45°	3815.2	3849.2	3880.4	3918.4	3937.4
47.5°	3612.9	3646.9	3684.9	3728.3	3740.6
50°	3403.8	3443.2	3483.9	3524.7	3546.4
52.5°	3189.3	3236.8	3283.0	3326.4	3346.8
55°	2977.5	3012.8	3068.5	3113.3	3133.6
57.5°	2757.6	2787.4	2837.7	2911.0	2921.8
60°	2533.5	2560.7	2612.3	2672.0	2696.5
62.5°	2286.4	2323.1	2377.4	2453.4	2475.1
65°	2046.1	2081.4	2153.4	2238.9	2274.2
67.5°	1813.9	1826.1	1918.5	2008.1	2065.1
70°	1539.7	1585.8	1693.1	1803.1	1846.5
72.5°	1303.4	1349.6	1467.7	1596.7	1651.0
75°	1035.9	1099.8	1260.0	1410.7	1463.6
77.5°	801.1	871.7	1069.9	1222.0	1283.1
80°	559.4	669.4	885.2	1056.3	1122.8
82.5°	351.7	487.4	718.2	897.5	955.8
85°	179.2	331.3	568.9	752.2	818.7
87.5°	47.5	214.5	442.6	617.8	685.7
90°	1.4	123.6	335.4	503.7	564.8
92.5°	1.4	69.2	249.8	400.5	463.0
95°	1.4	32.6	173.8	315.0	363.9
97.5°	1.4	13.6	119.5	237.6	286.5
100°	1.4	6.8	76.0	172.4	214.5
102.5°	2.7	4.1	47.5	123.6	157.5
105°	2.7	4.1	28.5	84.2	112.7
107.5°	2.7	4.1	16.3	57.0	77.4
110°	4.1	4.1	9.5	35.3	51.6

TEST NUMBER: P517713

CATALOG NUMBER: HVL12-8-LD4-3STD-35-UNV-O-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	4.1	4.1	5.4	23.1	33.9
115°	4.1	4.1	5.4	14.9	21.7
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)