

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P518012

Luminaire Tested: HVL8-4-LD4-1HI-30-UNV-C-EDD

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P518012
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-4-LD4-1HI-30-UNV-C-EDD
Description: 4 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 3000K, 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4506.0 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 4' x H: 0.17')
CIE Type: Direct


Input Watts (W): 43
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P518012

CATALOG NUMBER: HVL8-4-LD4-1HI-30-UNV-C-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P518012

CATALOG NUMBER: HVL8-4-LD4-1HI-30-UNV-C-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			99
1	108	103	98	94	105	100	96	92	96	92	89	91	89	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	51	62	56	51	60	54	50			47
5	75	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	39	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6037	6037	6037
5°	6024	5947	6008
10°	5945	6028	6045
15°	5837	5864	5611
20°	5705	5493	5366
25°	5565	5255	5400
30°	5354	5063	5459
35°	5203	4882	5363
40°	5042	4745	5396
45°	4867	4569	5299
50°	4656	4385	5258
55°	4345	4187	5255
60°	4107	3916	5031
65°	3631	3594	4871
70°	2962	3174	4367
75°	2114	2666	3987
80°	1186	2154	3579
85°	439	1626	3152

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5299 cd/sqm

TEST NUMBER: P518012

CATALOG NUMBER: HVL8-4-LD4-1HI-30-UNV-C-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.8	3.2
10°-20°	409.4	9.1
20°-30°	609.1	13.5
30°-40°	732.2	16.2
40°-50°	770.6	17.1
50°-60°	715.1	15.9
60°-70°	565.4	12.5
70°-80°	345.4	7.7
80°-90°	150.5	3.3
90°-100°	46.8	1.0
100°-110°	10.5	0.2
110°-120°	4.2	0.1
120°-130°	2.4	0.1
130°-140°	0.6	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1162.3	25.8
0°-40°	1894.4	42.0
0°-60°	3380.1	75.0
0°-90°	4441.4	98.6
90°-120°	61.6	1.4
90°-150°	64.6	1.4
90°-180°	65.0	1.4
0°-180°	4506.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1496	1496	1496	1496	1496	
5°	1492	1489	1494	1511	1515	141
15°	1412	1466	1481	1432	1433	398
25°	1274	1355	1293	1332	1354	585
35°	1087	1117	1134	1237	1279	679
45°	888	892	966	1118	1160	685
55°	654	665	770	939	1013	588
65°	414	427	543	718	783	410
75°	157	208	303	465	494	171
85°	14	49	118	229	263	22
90°	0	15	62	145	171	1
95°	0	4	27	80	97	0
105°	0	2	6	16	22	0
115°	0	1	4	7	7	0
125°	0	1	2	5	6	0
135°	1	1	1	2	2	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P518012

CATALOG NUMBER: HVL8-4-LD4-1HI-30-UNV-C-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1495.7	1495.7	1495.7	1495.7	1495.7
2.5°	1497.6	1493.6	1485.4	1493.3	1495.4
5°	1492.1	1489.0	1494.2	1511.0	1515.2
7.5°	1479.6	1491.2	1504.9	1535.4	1545.1
10°	1461.0	1482.9	1524.1	1550.0	1539.9
12.5°	1438.5	1475.6	1530.8	1480.2	1456.7
15°	1412.3	1466.5	1480.8	1431.8	1432.7
17.5°	1381.5	1458.9	1414.7	1413.5	1404.6
20°	1348.3	1433.3	1374.8	1372.3	1362.9
22.5°	1312.6	1399.5	1339.4	1334.6	1360.2
25°	1273.9	1355.3	1293.4	1332.1	1353.8
27.5°	1225.5	1297.4	1255.0	1309.9	1337.0
30°	1176.4	1237.7	1215.7	1292.2	1340.4
32.5°	1130.4	1175.2	1183.4	1285.5	1293.4
35°	1086.8	1117.0	1133.8	1236.8	1278.8
37.5°	1039.0	1047.2	1091.7	1216.3	1256.9
40°	990.3	985.1	1056.4	1182.8	1238.9
42.5°	937.9	936.0	1018.9	1166.1	1194.1
45°	888.2	892.1	965.6	1118.5	1160.3
47.5°	837.3	842.5	915.0	1066.4	1118.2
50°	778.2	784.9	869.9	1020.1	1086.8
52.5°	714.2	727.0	826.0	976.2	1043.6
55°	654.2	664.8	770.3	938.8	1013.4
57.5°	599.3	605.7	712.7	891.5	947.9
60°	545.4	546.9	658.4	839.1	893.1
62.5°	483.6	486.3	602.7	777.3	849.5
65°	414.1	427.2	542.7	718.2	783.4
67.5°	349.2	372.0	481.4	663.9	698.1
70°	279.7	318.4	421.4	600.2	624.3
72.5°	216.0	261.4	359.8	529.0	562.8
75°	156.6	207.5	302.6	465.0	494.2
77.5°	105.4	157.2	248.9	394.3	433.0
80°	63.1	114.9	201.1	328.8	372.3
82.5°	32.3	77.1	156.0	275.7	314.7
85°	14.0	48.8	117.9	228.8	262.6
87.5°	4.0	27.7	86.8	184.9	213.6
90°	0.3	14.6	61.9	145.0	170.9
92.5°	0.3	7.0	43.6	109.7	129.5
95°	0.3	3.7	27.1	79.5	97.2
97.5°	0.3	2.1	16.5	56.4	71.3
100°	0.3	1.8	9.8	37.5	50.9
102.5°	0.3	2.1	6.7	23.8	33.2
105°	0.3	2.1	5.5	15.5	21.9
107.5°	0.6	2.1	4.9	11.6	15.2
110°	0.3	1.8	5.2	8.8	11.9

TEST NUMBER: P518012

CATALOG NUMBER: HVL8-4-LD4-1HI-30-UNV-C-EDD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.6	1.5	4.9	7.3	8.8
115°	0.3	1.2	4.3	7.0	7.3
117.5°	0.6	0.9	3.4	7.0	7.3
120°	0.6	0.6	2.7	6.7	7.6
122.5°	0.6	0.6	2.1	6.1	7.3
125°	0.3	0.6	1.8	4.6	6.4
127.5°	0.6	0.6	1.5	3.7	4.9
130°	0.6	0.6	1.2	2.7	3.7
132.5°	0.6	0.6	0.9	2.1	2.7
135°	0.6	0.6	0.6	1.5	2.1
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)