

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P518028

Luminaire Tested: HVL8-4-LD4-1LO-30-UNV-C-EDD

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P518028
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-4-LD4-1LO-30-UNV-C-EDD
Description: 4 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 3000K, 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2718.0 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 4' x H: 0.17')
CIE Type: Direct


Input Watts (W): 23
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P518028

CATALOG NUMBER: HVL8-4-LD4-1LO-30-UNV-C-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P518028

CATALOG NUMBER: HVL8-4-LD4-1LO-30-UNV-C-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			99
1	108	103	98	94	105	100	96	92	96	92	89	91	89	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	51	62	56	51	60	54	50			47
5	75	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	39	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3642	3642	3642
5°	3633	3587	3624
10°	3586	3636	3647
15°	3521	3537	3385
20°	3441	3313	3237
25°	3357	3170	3257
30°	3230	3054	3293
35°	3139	2945	3235
40°	3041	2862	3255
45°	2936	2756	3196
50°	2808	2645	3172
55°	2621	2526	3170
60°	2477	2362	3035
65°	2190	2167	2938
70°	1786	1915	2635
75°	1275	1608	2405
80°	714	1299	2159
85°	267	981	1901

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 3196 cd/sqm

TEST NUMBER: P518028

CATALOG NUMBER: HVL8-4-LD4-1LO-30-UNV-C-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.7	3.2
10°-20°	246.9	9.1
20°-30°	367.4	13.5
30°-40°	441.6	16.2
40°-50°	464.8	17.1
50°-60°	431.3	15.9
60°-70°	341.0	12.5
70°-80°	208.3	7.7
80°-90°	90.8	3.3
90°-100°	28.3	1.0
100°-110°	6.3	0.2
110°-120°	2.5	0.1
120°-130°	1.4	0.1
130°-140°	0.4	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	701.1	25.8
0°-40°	1142.7	42.0
0°-60°	2038.9	75.0
0°-90°	2679.0	98.6
90°-120°	37.2	1.4
90°-150°	39.0	1.4
90°-180°	39.0	1.4
0°-180°	2718.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	902	902	902	902	902	
5°	900	898	901	911	914	85
15°	852	885	893	864	864	240
25°	768	818	780	804	817	353
35°	656	674	684	746	771	410
45°	536	538	582	675	700	413
55°	395	401	465	566	611	355
65°	250	258	327	433	472	247
75°	94	125	182	280	298	103
85°	8	29	71	138	158	13
90°	0	9	37	88	103	0
95°	0	2	16	48	59	0
105°	0	1	3	9	13	0
115°	0	1	3	4	4	0
125°	0	0	1	3	4	0
135°	0	0	0	1	1	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P518028

CATALOG NUMBER: HVL8-4-LD4-1LO-30-UNV-C-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	902.2	902.2	902.2	902.2	902.2
2.5°	903.3	900.9	896.0	900.8	902.0
5°	900.0	898.2	901.3	911.4	914.0
7.5°	892.5	899.5	907.7	926.1	932.0
10°	881.3	894.5	919.3	934.9	928.9
12.5°	867.7	890.1	923.4	892.9	878.7
15°	851.9	884.6	893.2	863.6	864.2
17.5°	833.3	880.0	853.3	852.6	847.3
20°	813.3	864.6	829.3	827.8	822.1
22.5°	791.8	844.2	807.9	805.0	820.4
25°	768.4	817.5	780.2	803.5	816.6
27.5°	739.2	782.6	757.0	790.1	806.5
30°	709.6	746.6	733.3	779.5	808.5
32.5°	681.9	708.9	713.8	775.4	780.2
35°	655.6	673.8	683.9	746.0	771.4
37.5°	626.7	631.7	658.5	733.7	758.1
40°	597.3	594.2	637.2	713.5	747.3
42.5°	565.7	564.6	614.6	703.4	720.3
45°	535.7	538.1	582.4	674.7	699.9
47.5°	505.1	508.2	551.9	643.3	674.5
50°	469.4	473.4	524.7	615.3	655.6
52.5°	430.8	438.5	498.3	588.9	629.5
55°	394.6	401.0	464.6	566.3	611.3
57.5°	361.5	365.4	429.9	537.8	571.8
60°	329.0	329.9	397.2	506.2	538.7
62.5°	291.7	293.3	363.5	468.8	512.4
65°	249.8	257.7	327.3	433.2	472.5
67.5°	210.6	224.4	290.4	400.5	421.1
70°	168.7	192.1	254.2	362.1	376.6
72.5°	130.3	157.7	217.1	319.1	339.5
75°	94.5	125.2	182.5	280.5	298.1
77.5°	63.6	94.8	150.2	237.8	261.2
80°	38.0	69.3	121.3	198.3	224.6
82.5°	19.5	46.5	94.1	166.3	189.9
85°	8.5	29.4	71.1	138.0	158.4
87.5°	2.4	16.7	52.4	111.6	128.8
90°	0.2	8.8	37.3	87.5	103.1
92.5°	0.2	4.2	26.3	66.2	78.1
95°	0.2	2.2	16.4	48.0	58.6
97.5°	0.2	1.3	9.9	34.0	43.0
100°	0.2	1.1	5.9	22.6	30.7
102.5°	0.2	1.3	4.0	14.3	20.0
105°	0.2	1.3	3.3	9.4	13.2
107.5°	0.4	1.3	2.9	7.0	9.2
110°	0.2	1.1	3.1	5.3	7.2

TEST NUMBER: P518028

CATALOG NUMBER: HVL8-4-LD4-1LO-30-UNV-C-EDD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.4	0.9	2.9	4.4	5.3
115°	0.2	0.7	2.6	4.2	4.4
117.5°	0.4	0.6	2.0	4.2	4.4
120°	0.4	0.4	1.7	4.0	4.6
122.5°	0.4	0.4	1.3	3.7	4.4
125°	0.2	0.4	1.1	2.8	3.9
127.5°	0.4	0.4	0.9	2.2	2.9
130°	0.4	0.4	0.7	1.7	2.2
132.5°	0.4	0.4	0.6	1.3	1.7
135°	0.4	0.4	0.4	0.9	1.3
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)