

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P518080

Luminaire Tested: HVL8-4-LD4-2LO-35-UNV-C-EDD

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P518080
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-4-LD4-2LO-35-UNV-C-EDD
Description: 4 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 3500K, 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5418.0 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 4' x H: 0.17')
CIE Type: Direct


Input Watts (W): 46.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P518080

CATALOG NUMBER: HVL8-4-LD4-2LO-35-UNV-C-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P518080

CATALOG NUMBER: HVL8-4-LD4-2LO-35-UNV-C-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			99
1	108	103	98	94	105	100	96	92	96	92	89	91	89	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	51	62	56	51	60	54	50			47
5	75	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	39	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7260	7260	7260
5°	7243	7151	7224
10°	7148	7248	7269
15°	7018	7051	6746
20°	6860	6605	6452
25°	6692	6319	6493
30°	6438	6088	6564
35°	6257	5870	6448
40°	6062	5705	6488
45°	5853	5494	6371
50°	5598	5272	6322
55°	5225	5035	6319
60°	4938	4709	6049
65°	4365	4321	5856
70°	3561	3817	5252
75°	2541	3206	4794
80°	1425	2590	4304
85°	530	1956	3791

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 6371 cd/sqm

TEST NUMBER: P518080

CATALOG NUMBER: HVL8-4-LD4-2LO-35-UNV-C-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.9	3.2
10°-20°	492.2	9.1
20°-30°	732.4	13.5
30°-40°	880.4	16.2
40°-50°	926.6	17.1
50°-60°	859.8	15.9
60°-70°	679.8	12.5
70°-80°	415.3	7.7
80°-90°	180.9	3.3
90°-100°	56.3	1.0
100°-110°	12.7	0.2
110°-120°	5.1	0.1
120°-130°	2.9	0.1
130°-140°	0.8	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1397.5	25.8
0°-40°	2277.9	42.0
0°-60°	4064.3	75.0
0°-90°	5340.3	98.6
90°-120°	74.1	1.4
90°-150°	77.7	1.4
90°-180°	78.0	1.4
0°-180°	5418.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1798	1798	1798	1798	1798	
5°	1794	1790	1797	1817	1822	170
15°	1698	1763	1780	1722	1723	478
25°	1532	1630	1555	1602	1628	703
35°	1307	1343	1363	1487	1538	817
45°	1068	1073	1161	1345	1395	823
55°	787	799	926	1129	1218	707
65°	498	514	652	864	942	493
75°	188	250	364	559	594	206
85°	17	59	142	275	316	26
90°	0	18	74	174	206	1
95°	0	4	33	96	117	0
105°	0	3	7	19	26	1
115°	0	2	5	8	9	1
125°	0	1	2	6	8	1
135°	1	1	1	2	3	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P518080

CATALOG NUMBER: HVL8-4-LD4-2LO-35-UNV-C-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1798.5	1798.5	1798.5	1798.5	1798.5
2.5°	1800.7	1795.9	1786.0	1795.6	1798.1
5°	1794.1	1790.4	1796.6	1816.8	1821.9
7.5°	1779.1	1793.0	1809.5	1846.1	1857.8
10°	1756.7	1783.1	1832.6	1863.7	1851.6
12.5°	1729.6	1774.3	1840.6	1779.8	1751.6
15°	1698.1	1763.3	1780.5	1721.5	1722.6
17.5°	1661.1	1754.2	1701.0	1699.6	1688.9
20°	1621.2	1723.4	1653.0	1650.1	1638.7
22.5°	1578.3	1682.7	1610.5	1604.7	1635.4
25°	1531.8	1629.6	1555.2	1601.7	1627.8
27.5°	1473.5	1560.0	1509.1	1575.0	1607.6
30°	1414.5	1488.2	1461.8	1553.8	1611.6
32.5°	1359.2	1413.1	1423.0	1545.7	1555.2
35°	1306.8	1343.1	1363.2	1487.1	1537.6
37.5°	1249.3	1259.2	1312.7	1462.5	1511.3
40°	1190.7	1184.5	1270.2	1422.2	1489.6
42.5°	1127.7	1125.5	1225.1	1402.1	1435.8
45°	1068.0	1072.7	1161.0	1344.9	1395.1
47.5°	1006.8	1013.0	1100.2	1282.3	1344.6
50°	935.7	943.8	1046.0	1226.6	1306.8
52.5°	858.8	874.1	993.2	1173.8	1254.8
55°	786.6	799.4	926.2	1128.8	1218.5
57.5°	720.6	728.3	856.9	1072.0	1139.8
60°	655.8	657.6	791.7	1009.0	1073.8
62.5°	581.4	584.7	724.7	934.6	1021.4
65°	497.9	513.6	652.5	863.5	941.9
67.5°	419.9	447.3	578.9	798.3	839.3
70°	336.3	382.9	506.7	721.7	750.7
72.5°	259.8	314.3	432.7	636.0	676.7
75°	188.3	249.5	363.8	559.1	594.2
77.5°	126.8	189.0	299.3	474.1	520.6
80°	75.8	138.1	241.8	395.3	447.7
82.5°	38.8	92.7	187.6	331.6	378.5
85°	16.9	58.6	141.8	275.1	315.8
87.5°	4.8	33.3	104.4	222.4	256.8
90°	0.4	17.6	74.4	174.4	205.5
92.5°	0.4	8.4	52.4	131.9	155.7
95°	0.4	4.4	32.6	95.6	116.9
97.5°	0.4	2.6	19.8	67.8	85.7
100°	0.4	2.2	11.7	45.1	61.2
102.5°	0.4	2.6	8.1	28.6	39.9
105°	0.4	2.6	6.6	18.7	26.4
107.5°	0.7	2.6	5.9	13.9	18.3
110°	0.4	2.2	6.2	10.6	14.3

TEST NUMBER: P518080

CATALOG NUMBER: HVL8-4-LD4-2LO-35-UNV-C-EDD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.7	1.8	5.9	8.8	10.6
115°	0.4	1.5	5.1	8.4	8.8
117.5°	0.7	1.1	4.0	8.4	8.8
120°	0.7	0.7	3.3	8.1	9.2
122.5°	0.7	0.7	2.6	7.3	8.8
125°	0.4	0.7	2.2	5.5	7.7
127.5°	0.7	0.7	1.8	4.4	5.9
130°	0.7	0.7	1.5	3.3	4.4
132.5°	0.7	0.7	1.1	2.6	3.3
135°	0.7	0.7	0.7	1.8	2.6
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)