

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P518123

Luminaire Tested: HVL8-4-LD4-3LO-30-UNV-C-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P518123
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-4-LD4-3LO-30-UNV-C-EDD-90
Description: 4 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 3000K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8141.1 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 4' x H: 0.17')
CIE Type: Direct


Input Watts (W): 67.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P518123

CATALOG NUMBER: HVL8-4-LD4-3LO-30-UNV-C-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P518123

CATALOG NUMBER: HVL8-4-LD4-3LO-30-UNV-C-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			99
1	108	103	98	94	105	100	96	92	96	92	89	91	89	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	51	62	56	51	60	54	50			47
5	75	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	39	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10908	10908	10908
5°	10883	10745	10855
10°	10740	10890	10922
15°	10545	10595	10137
20°	10307	9924	9695
25°	10055	9494	9755
30°	9674	9148	9863
35°	9402	8820	9688
40°	9109	8573	9749
45°	8794	8255	9573
50°	8411	7922	9500
55°	7850	7565	9494
60°	7420	7076	9089
65°	6559	6492	8799
70°	5352	5735	7891
75°	3820	4817	7203
80°	2143	3892	6467
85°	794	2938	5696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 9573 cd/sqm

TEST NUMBER: P518123

CATALOG NUMBER: HVL8-4-LD4-3LO-30-UNV-C-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	259.7	3.2
10°-20°	739.6	9.1
20°-30°	1100.5	13.5
30°-40°	1322.8	16.2
40°-50°	1392.3	17.1
50°-60°	1291.9	15.9
60°-70°	1021.5	12.5
70°-80°	624.0	7.7
80°-90°	271.9	3.3
90°-100°	84.6	1.0
100°-110°	19.0	0.2
110°-120°	7.7	0.1
120°-130°	4.3	0.1
130°-140°	1.2	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2099.9	25.8
0°-40°	3422.7	42.0
0°-60°	6106.9	75.0
0°-90°	8024.3	98.6
90°-120°	111.3	1.4
90°-150°	116.8	1.4
90°-180°	117.0	1.4
0°-180°	8141.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2702	2702	2702	2702	2702	
5°	2696	2690	2700	2730	2738	255
15°	2552	2650	2675	2587	2588	719
25°	2302	2449	2337	2407	2446	1057
35°	1964	2018	2048	2234	2310	1227
45°	1605	1612	1744	2021	2096	1237
55°	1182	1201	1392	1696	1831	1062
65°	748	772	980	1298	1415	741
75°	283	375	547	840	893	309
85°	25	88	213	413	474	39
90°	1	26	112	262	309	1
95°	1	7	49	144	176	0
105°	1	4	10	28	40	1
115°	1	2	8	13	13	1
125°	1	1	3	8	12	1
135°	1	1	1	3	4	1
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P518123

CATALOG NUMBER: HVL8-4-LD4-3LO-30-UNV-C-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2702.4	2702.4	2702.4	2702.4	2702.4
2.5°	2705.7	2698.5	2683.7	2698.0	2701.8
5°	2695.8	2690.3	2699.6	2729.9	2737.6
7.5°	2673.2	2694.1	2718.9	2773.9	2791.5
10°	2639.6	2679.2	2753.6	2800.4	2782.2
12.5°	2598.9	2666.0	2765.7	2674.3	2631.9
15°	2551.5	2649.5	2675.4	2586.8	2588.4
17.5°	2495.9	2635.8	2555.9	2553.7	2537.8
20°	2435.9	2589.5	2483.8	2479.4	2462.4
22.5°	2371.5	2528.4	2420.0	2411.2	2457.4
25°	2301.6	2448.6	2336.8	2406.8	2445.8
27.5°	2214.1	2344.0	2267.5	2366.6	2415.6
30°	2125.5	2236.1	2196.5	2334.6	2421.6
32.5°	2042.3	2123.3	2138.1	2322.5	2336.8
35°	1963.6	2018.1	2048.4	2234.5	2310.4
37.5°	1877.2	1892.0	1972.4	2197.6	2270.8
40°	1789.1	1779.7	1908.6	2137.0	2238.3
42.5°	1694.4	1691.1	1840.8	2106.7	2157.4
45°	1604.7	1611.8	1744.5	2020.9	2096.3
47.5°	1512.8	1522.1	1653.1	1926.7	2020.3
50°	1406.0	1418.1	1571.7	1843.0	1963.6
52.5°	1290.4	1313.5	1492.4	1763.8	1885.4
55°	1181.9	1201.2	1391.6	1696.1	1830.9
57.5°	1082.8	1094.4	1287.6	1610.7	1712.6
60°	985.4	988.1	1189.6	1516.1	1613.5
62.5°	873.6	878.6	1088.9	1404.3	1534.8
65°	748.1	771.8	980.4	1297.5	1415.3
67.5°	630.9	672.2	869.8	1199.5	1261.2
70°	505.4	575.3	761.3	1084.5	1128.0
72.5°	390.3	472.3	650.1	955.7	1016.8
75°	283.0	374.9	546.6	840.1	892.9
77.5°	190.5	284.1	449.8	712.3	782.3
80°	114.0	207.5	363.3	594.0	672.7
82.5°	58.4	139.3	281.9	498.2	568.7
85°	25.3	88.1	213.0	413.4	474.5
87.5°	7.2	50.1	156.9	334.1	385.9
90°	0.6	26.4	111.8	262.0	308.8
92.5°	0.6	12.7	78.7	198.2	234.0
95°	0.6	6.6	49.0	143.7	175.6
97.5°	0.6	3.9	29.7	101.8	128.8
100°	0.6	3.3	17.6	67.7	91.9
102.5°	0.6	3.9	12.1	42.9	60.0
105°	0.6	3.9	9.9	28.1	39.6
107.5°	1.1	3.9	8.8	20.9	27.5
110°	0.6	3.3	9.4	16.0	21.5

TEST NUMBER: P518123

CATALOG NUMBER: HVL8-4-LD4-3LO-30-UNV-C-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1.1	2.8	8.8	13.2	16.0
115°	0.6	2.2	7.7	12.7	13.2
117.5°	1.1	1.7	6.1	12.7	13.2
120°	1.1	1.1	5.0	12.1	13.8
122.5°	1.1	1.1	3.9	11.0	13.2
125°	0.6	1.1	3.3	8.3	11.6
127.5°	1.1	1.1	2.8	6.6	8.8
130°	1.1	1.1	2.2	5.0	6.6
132.5°	1.1	1.1	1.7	3.9	5.0
135°	1.1	1.1	1.1	2.8	3.9
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)