

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P518127

Luminaire Tested: HVL8-4-LD4-3LO-35-UNV-C-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P518127
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-4-LD4-3LO-35-UNV-C-EDD-90
Description: 4 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 3500K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8545.0 lumens
Efficiency: N/A
Efficacy: 126.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 4' x H: 0.17')
CIE Type: Direct


Input Watts (W): 67.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P518127

CATALOG NUMBER: HVL8-4-LD4-3LO-35-UNV-C-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P518127

CATALOG NUMBER: HVL8-4-LD4-3LO-35-UNV-C-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			99
1	108	103	98	94	105	100	96	92	96	92	89	91	89	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	51	62	56	51	60	54	50			47
5	75	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	39	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11449	11449	11449
5°	11423	11278	11394
10°	11273	11430	11464
15°	11068	11120	10641
20°	10819	10417	10176
25°	10554	9966	10240
30°	10154	9602	10353
35°	9868	9257	10169
40°	9561	8998	10233
45°	9230	8665	10048
50°	8828	8315	9971
55°	8240	7940	9966
60°	7788	7427	9540
65°	6884	6815	9236
70°	5617	6019	8282
75°	4008	5056	7561
80°	2249	4086	6788
85°	834	3084	5979

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 10048 cd/sqm

TEST NUMBER: P518127

CATALOG NUMBER: HVL8-4-LD4-3LO-35-UNV-C-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	272.6	3.2
10°-20°	776.3	9.1
20°-30°	1155.1	13.5
30°-40°	1388.5	16.2
40°-50°	1461.4	17.1
50°-60°	1356.0	15.9
60°-70°	1072.2	12.5
70°-80°	654.9	7.7
80°-90°	285.3	3.3
90°-100°	88.8	1.0
100°-110°	20.0	0.2
110°-120°	8.0	0.1
120°-130°	4.5	0.1
130°-140°	1.2	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2204.1	25.8
0°-40°	3592.5	42.0
0°-60°	6410.0	75.0
0°-90°	8422.5	98.6
90°-120°	116.8	1.4
90°-150°	122.6	1.4
90°-180°	123.0	1.4
0°-180°	8545.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2836	2836	2836	2836	2836	
5°	2830	2824	2834	2865	2874	268
15°	2678	2781	2808	2715	2717	754
25°	2416	2570	2453	2526	2567	1109
35°	2061	2118	2150	2345	2425	1288
45°	1684	1692	1831	2121	2200	1298
55°	1241	1261	1461	1780	1922	1115
65°	785	810	1029	1362	1486	778
75°	297	394	574	882	937	324
85°	27	92	224	434	498	41
90°	1	28	117	275	324	1
95°	1	7	51	151	184	0
105°	1	4	10	30	42	1
115°	1	2	8	13	14	1
125°	1	1	4	9	12	1
135°	1	1	1	3	4	1
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P518127

CATALOG NUMBER: HVL8-4-LD4-3LO-35-UNV-C-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2836.5	2836.5	2836.5	2836.5	2836.5
2.5°	2839.9	2832.4	2816.8	2831.9	2835.9
5°	2829.5	2823.8	2833.6	2865.4	2873.5
7.5°	2805.9	2827.8	2853.8	2911.6	2930.1
10°	2770.6	2812.2	2890.2	2939.3	2920.3
12.5°	2727.8	2798.3	2902.9	2807.0	2762.5
15°	2678.2	2781.0	2808.2	2715.1	2716.9
17.5°	2619.8	2766.6	2682.8	2680.5	2663.7
20°	2556.8	2718.0	2607.1	2602.5	2584.5
22.5°	2489.2	2653.9	2540.1	2530.8	2579.3
25°	2415.8	2570.1	2452.8	2526.2	2567.2
27.5°	2324.0	2460.3	2380.0	2484.0	2535.4
30°	2230.9	2347.1	2305.5	2450.5	2541.8
32.5°	2143.7	2228.6	2244.2	2437.8	2452.8
35°	2061.1	2118.3	2150.0	2345.3	2425.1
37.5°	1970.3	1985.9	2070.3	2306.6	2383.5
40°	1877.9	1868.1	2003.3	2243.1	2349.4
42.5°	1778.5	1775.0	1932.2	2211.3	2264.4
45°	1684.3	1691.8	1831.1	2121.1	2200.3
47.5°	1587.8	1597.6	1735.2	2022.3	2120.6
50°	1475.7	1488.4	1649.7	1934.5	2061.1
52.5°	1354.4	1378.7	1566.4	1851.3	1979.0
55°	1240.6	1260.8	1460.7	1780.2	1921.8
57.5°	1136.6	1148.7	1351.5	1690.7	1797.6
60°	1034.3	1037.2	1248.7	1591.3	1693.6
62.5°	917.0	922.2	1142.9	1474.0	1610.9
65°	785.2	810.1	1029.1	1361.9	1485.6
67.5°	662.2	705.5	912.9	1259.1	1323.8
70°	530.4	603.8	799.1	1138.3	1183.9
72.5°	409.7	495.8	682.4	1003.1	1067.2
75°	297.0	393.5	573.8	881.7	937.2
77.5°	199.9	298.2	472.1	747.7	821.1
80°	119.6	217.8	381.4	623.5	706.1
82.5°	61.2	146.2	295.8	522.9	596.9
85°	26.6	92.4	223.6	433.9	498.1
87.5°	7.5	52.6	164.7	350.7	405.0
90°	0.6	27.7	117.3	275.0	324.2
92.5°	0.6	13.3	82.6	208.0	245.6
95°	0.6	6.9	51.4	150.8	184.3
97.5°	0.6	4.0	31.2	106.9	135.2
100°	0.6	3.5	18.5	71.1	96.5
102.5°	0.6	4.0	12.7	45.1	63.0
105°	0.6	4.0	10.4	29.5	41.6
107.5°	1.2	4.0	9.2	22.0	28.9
110°	0.6	3.5	9.8	16.8	22.5

TEST NUMBER: P518127

CATALOG NUMBER: HVL8-4-LD4-3LO-35-UNV-C-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1.2	2.9	9.2	13.9	16.8
115°	0.6	2.3	8.1	13.3	13.9
117.5°	1.2	1.7	6.4	13.3	13.9
120°	1.2	1.2	5.2	12.7	14.4
122.5°	1.2	1.2	4.0	11.6	13.9
125°	0.6	1.2	3.5	8.7	12.1
127.5°	1.2	1.2	2.9	6.9	9.2
130°	1.2	1.2	2.3	5.2	6.9
132.5°	1.2	1.2	1.7	4.0	5.2
135°	1.2	1.2	1.2	2.9	4.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)