

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517783

Luminaire Tested: HVL8-1-LD4-2HI-50-UNV-C-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517783
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-1-LD4-2HI-50-UNV-C-EDD-90
Description: 1 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 5000K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2007.0 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 1' x H: 0.17')
CIE Type: Direct


Input Watts (W): 21.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517783

CATALOG NUMBER: HVL8-1-LD4-2HI-50-UNV-C-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P517783

CATALOG NUMBER: HVL8-1-LD4-2HI-50-UNV-C-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		101
1	108	103	98	94	105	100	96	92	96	92	89		91	89	86		87
2	98	89	82	76	95	87	80	75	83	78	73		80	75	71		76
3	89	78	69	63	86	76	68	62	73	66	61		70	64	59		67
4	81	69	60	53	79	67	59	52	65	57	51		62	56	51		60
5	75	61	52	45	72	60	51	45	58	50	44		56	49	44		54
6	69	55	46	39	67	54	46	39	52	45	39		50	44	38		49
7	64	50	41	35	62	49	41	35	47	40	34		46	39	34		44
8	59	46	37	31	58	45	37	31	43	36	31		42	35	30		41
9	55	42	34	28	54	41	33	28	40	33	28		39	32	27		38
10	52	39	31	25	51	38	30	25	37	30	25		36	29	25		35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10756	10756	10756
5°	10617	10515	10704
10°	10364	10579	10770
15°	10064	10219	9996
20°	9728	9501	9560
25°	9379	9023	9621
30°	8912	8628	9726
35°	8544	8251	9554
40°	8156	7951	9613
45°	7742	7585	9440
50°	7263	7204	9368
55°	6625	6797	9363
60°	6086	6271	8964
65°	5190	5658	8677
70°	4034	4896	7782
75°	2684	4005	7102
80°	1343	3119	6375
85°	395	2226	5618

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 9440 cd/sqm

TEST NUMBER: P517783

CATALOG NUMBER: HVL8-1-LD4-2HI-50-UNV-C-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.0	3.2
10°-20°	182.3	9.1
20°-30°	271.3	13.5
30°-40°	326.1	16.2
40°-50°	343.3	17.1
50°-60°	318.5	15.9
60°-70°	251.8	12.5
70°-80°	153.8	7.7
80°-90°	67.0	3.3
90°-100°	20.9	1.0
100°-110°	4.7	0.2
110°-120°	1.9	0.1
120°-130°	1.1	0.1
130°-140°	0.3	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	517.7	25.8
0°-40°	843.8	42.0
0°-60°	1505.5	75.0
0°-90°	1978.2	98.6
90°-120°	27.4	1.4
90°-150°	28.8	1.4
90°-180°	29.0	1.4
0°-180°	2007.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	666	666	666	666	666	
5°	665	663	666	673	675	63
15°	629	653	660	638	638	177
25°	567	604	576	593	603	260
35°	484	498	505	551	570	303
45°	396	397	430	498	517	305
55°	291	296	343	418	451	262
65°	184	190	242	320	349	183
75°	70	92	135	207	220	76
85°	6	22	52	102	117	10
90°	0	6	28	65	76	0
95°	0	2	12	35	43	0
105°	0	1	2	7	10	0
115°	0	0	2	3	3	0
125°	0	0	1	2	3	0
135°	0	0	0	1	1	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517783

CATALOG NUMBER: HVL8-1-LD4-2HI-50-UNV-C-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	666.2	666.2	666.2	666.2	666.2
2.5°	667.0	665.3	661.6	665.1	666.1
5°	664.6	663.2	665.5	673.0	674.9
7.5°	659.0	664.2	670.3	683.9	688.2
10°	650.7	660.5	678.8	690.4	685.9
12.5°	640.7	657.3	681.8	659.3	648.8
15°	629.0	653.2	659.6	637.7	638.1
17.5°	615.3	649.8	630.1	629.6	625.6
20°	600.5	638.4	612.3	611.3	607.0
22.5°	584.7	623.3	596.6	594.4	605.8
25°	567.4	603.7	576.1	593.3	603.0
27.5°	545.8	577.9	559.0	583.4	595.5
30°	524.0	551.3	541.5	575.6	597.0
32.5°	503.5	523.4	527.1	572.6	576.1
35°	484.1	497.5	505.0	550.9	569.6
37.5°	462.8	466.4	486.3	541.8	559.8
40°	441.1	438.8	470.5	526.8	551.8
42.5°	417.7	416.9	453.8	519.4	531.9
45°	395.6	397.4	430.1	498.2	516.8
47.5°	372.9	375.2	407.5	475.0	498.1
50°	346.6	349.6	387.5	454.4	484.1
52.5°	318.1	323.8	367.9	434.8	464.8
55°	291.4	296.1	343.1	418.1	451.4
57.5°	266.9	269.8	317.4	397.1	422.2
60°	242.9	243.6	293.3	373.8	397.8
62.5°	215.4	216.6	268.4	346.2	378.4
65°	184.4	190.3	241.7	319.9	348.9
67.5°	155.5	165.7	214.4	295.7	310.9
70°	124.6	141.8	187.7	267.4	278.1
72.5°	96.2	116.4	160.3	235.6	250.7
75°	69.8	92.4	134.8	207.1	220.1
77.5°	47.0	70.0	110.9	175.6	192.8
80°	28.1	51.2	89.6	146.4	165.8
82.5°	14.4	34.3	69.5	122.8	140.2
85°	6.2	21.7	52.5	101.9	117.0
87.5°	1.8	12.3	38.7	82.4	95.1
90°	0.1	6.5	27.5	64.6	76.1
92.5°	0.1	3.1	19.4	48.9	57.7
95°	0.1	1.6	12.1	35.4	43.3
97.5°	0.1	0.9	7.3	25.1	31.8
100°	0.1	0.8	4.3	16.7	22.7
102.5°	0.1	0.9	3.0	10.6	14.8
105°	0.1	0.9	2.4	6.9	9.8
107.5°	0.3	0.9	2.2	5.2	6.8
110°	0.1	0.8	2.3	3.9	5.3

TEST NUMBER: P517783

CATALOG NUMBER: HVL8-1-LD4-2HI-50-UNV-C-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.3	0.7	2.2	3.3	3.9
115°	0.1	0.5	1.9	3.1	3.3
117.5°	0.3	0.4	1.5	3.1	3.3
120°	0.3	0.3	1.2	3.0	3.4
122.5°	0.3	0.3	0.9	2.7	3.3
125°	0.1	0.3	0.8	2.0	2.8
127.5°	0.3	0.3	0.7	1.6	2.2
130°	0.3	0.3	0.5	1.2	1.6
132.5°	0.3	0.3	0.4	0.9	1.2
135°	0.3	0.3	0.3	0.7	0.9
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)