

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517892

Luminaire Tested: HVL8-2-LD4-1LO-40-UNV-C-EDD

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517892
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-2-LD4-1LO-40-UNV-C-EDD
Description: 2 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 4000K, 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1441.0 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 2' x H: 0.17')
CIE Type: Direct


Input Watts (W): 11.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517892

CATALOG NUMBER: HVL8-2-LD4-1LO-40-UNV-C-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P517892

CATALOG NUMBER: HVL8-2-LD4-1LO-40-UNV-C-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		101
1	108	103	98	94	105	100	96	92	96	92	89		91	89	86		87
2	98	89	82	76	95	87	80	75	83	78	73		80	75	71		76
3	89	78	69	63	86	76	68	62	73	66	61		70	64	59		67
4	81	69	60	53	79	67	59	52	65	57	51		62	56	51		60
5	75	61	52	45	72	60	51	45	58	50	44		56	49	44		54
6	69	55	46	39	67	54	46	39	52	44	39		50	44	38		49
7	64	50	41	35	62	49	41	35	47	40	34		46	39	34		44
8	59	46	37	31	58	45	37	31	43	36	31		42	35	30		41
9	55	42	34	28	54	41	33	28	40	33	28		39	32	27		38
10	52	39	31	25	51	38	30	25	37	30	25		36	29	25		35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3861	3861	3861
5°	3839	3794	3843
10°	3774	3836	3867
15°	3692	3723	3589
20°	3595	3478	3432
25°	3493	3319	3453
30°	3346	3190	3491
35°	3237	3067	3430
40°	3119	2972	3451
45°	2993	2853	3389
50°	2844	2728	3363
55°	2631	2593	3361
60°	2461	2414	3218
65°	2146	2201	3115
70°	1719	1931	2794
75°	1192	1606	2549
80°	638	1279	2290
85°	213	945	2017

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 3389 cd/sqm

TEST NUMBER: P517892

CATALOG NUMBER: HVL8-2-LD4-1LO-40-UNV-C-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	3.2
10°-20°	130.9	9.1
20°-30°	194.8	13.5
30°-40°	234.1	16.2
40°-50°	246.4	17.1
50°-60°	228.7	15.9
60°-70°	180.8	12.5
70°-80°	110.5	7.7
80°-90°	48.1	3.3
90°-100°	15.0	1.0
100°-110°	3.4	0.2
110°-120°	1.4	0.1
120°-130°	0.8	0.1
130°-140°	0.2	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	371.7	25.8
0°-40°	605.8	42.0
0°-60°	1081.0	75.0
0°-90°	1420.4	98.6
90°-120°	19.7	1.4
90°-150°	20.7	1.4
90°-180°	21.0	1.5
0°-180°	1441.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	478	478	478	478	478	
5°	477	476	478	483	485	45
15°	452	469	474	458	458	127
25°	407	433	414	426	433	187
35°	348	357	363	396	409	217
45°	284	285	309	358	371	219
55°	209	213	246	300	324	188
65°	132	137	174	230	250	131
75°	50	66	97	149	158	55
85°	4	16	38	73	84	7
90°	0	5	20	46	55	0
95°	0	1	9	25	31	0
105°	0	1	2	5	7	0
115°	0	0	1	2	2	0
125°	0	0	1	2	2	0
135°	0	0	0	0	1	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517892

CATALOG NUMBER: HVL8-2-LD4-1LO-40-UNV-C-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	478.3	478.3	478.3	478.3	478.3
2.5°	478.9	477.7	475.0	477.6	478.2
5°	477.2	476.2	477.8	483.2	484.6
7.5°	473.2	476.9	481.3	491.0	494.1
10°	467.2	474.2	487.4	495.7	492.5
12.5°	460.0	471.9	489.5	473.4	465.9
15°	451.6	469.0	473.6	457.9	458.2
17.5°	441.8	466.5	452.4	452.0	449.2
20°	431.2	458.4	439.6	438.9	435.8
22.5°	419.8	447.5	428.3	426.8	435.0
25°	407.4	433.4	413.6	426.0	432.9
27.5°	391.9	414.9	401.4	418.9	427.6
30°	376.2	395.8	388.8	413.2	428.6
32.5°	361.5	375.8	378.5	411.1	413.6
35°	347.6	357.2	362.6	395.5	409.0
37.5°	332.3	334.9	349.1	389.0	401.9
40°	316.7	315.0	337.8	378.3	396.2
42.5°	299.9	299.3	325.8	372.9	381.9
45°	284.0	285.3	308.8	357.7	371.1
47.5°	267.8	269.4	292.6	341.0	357.6
50°	248.9	251.0	278.2	326.2	347.6
52.5°	228.4	232.5	264.2	312.2	333.7
55°	209.2	212.6	246.3	300.2	324.1
57.5°	191.7	193.7	227.9	285.1	303.1
60°	174.4	174.9	210.6	268.4	285.6
62.5°	154.6	155.5	192.7	248.6	271.7
65°	132.4	136.6	173.5	229.7	250.5
67.5°	111.7	119.0	154.0	212.3	223.2
70°	89.5	101.8	134.8	192.0	199.7
72.5°	69.1	83.6	115.1	169.2	180.0
75°	50.1	66.4	96.8	148.7	158.0
77.5°	33.7	50.3	79.6	126.1	138.5
80°	20.2	36.7	64.3	105.1	119.1
82.5°	10.3	24.7	49.9	88.2	100.7
85°	4.5	15.6	37.7	73.2	84.0
87.5°	1.3	8.9	27.8	59.1	68.3
90°	0.1	4.7	19.8	46.4	54.7
92.5°	0.1	2.2	13.9	35.1	41.4
95°	0.1	1.2	8.7	25.4	31.1
97.5°	0.1	0.7	5.3	18.0	22.8
100°	0.1	0.6	3.1	12.0	16.3
102.5°	0.1	0.7	2.1	7.6	10.6
105°	0.1	0.7	1.8	5.0	7.0
107.5°	0.2	0.7	1.6	3.7	4.9
110°	0.1	0.6	1.7	2.8	3.8

TEST NUMBER: P517892

CATALOG NUMBER: HVL8-2-LD4-1LO-40-UNV-C-EDD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.2	0.5	1.6	2.3	2.8
115°	0.1	0.4	1.4	2.2	2.3
117.5°	0.2	0.3	1.1	2.2	2.3
120°	0.2	0.2	0.9	2.1	2.4
122.5°	0.2	0.2	0.7	1.9	2.3
125°	0.1	0.2	0.6	1.5	2.0
127.5°	0.2	0.2	0.5	1.2	1.6
130°	0.2	0.2	0.4	0.9	1.2
132.5°	0.2	0.2	0.3	0.7	0.9
135°	0.2	0.2	0.2	0.5	0.7
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)