

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517758

Luminaire Tested: HVL8-1-LD4-1STD-30-UNV-O-EDD

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517758
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-1-LD4-1STD-30-UNV-O-EDD
Description: 1 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 3000K, 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 793.0 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 1' x H: 0.17')
CIE Type: Direct


Input Watts (W): 8.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517758

CATALOG NUMBER: HVL8-1-LD4-1STD-30-UNV-O-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P517758

CATALOG NUMBER: HVL8-1-LD4-1STD-30-UNV-O-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			98
1	108	102	98	94	105	100	96	92	95	92	89	91	88	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	77	73	79	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	52	62	56	51	60	54	50			47
5	75	61	52	45	72	60	52	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	40	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4235	4235	4235
5°	4181	4110	4144
10°	4108	4005	4061
15°	4029	3896	3962
20°	3946	3779	3865
25°	3856	3660	3767
30°	3759	3537	3654
35°	3645	3403	3544
40°	3526	3265	3415
45°	3400	3116	3275
50°	3248	2950	3125
55°	3083	2768	2960
60°	2892	2544	2767
65°	2623	2297	2576
70°	2270	2011	2353
75°	1815	1705	2152
80°	1219	1403	1965
85°	523	1098	1791

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3400 cd/sqm

TEST NUMBER: P517758

CATALOG NUMBER: HVL8-1-LD4-1STD-30-UNV-O-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.8	3.1
10°-20°	71.2	9.0
20°-30°	108.0	13.6
30°-40°	130.6	16.5
40°-50°	136.3	17.2
50°-60°	124.6	15.7
60°-70°	97.2	12.3
70°-80°	60.8	7.7
80°-90°	27.6	3.5
90°-100°	9.3	1.2
100°-110°	2.3	0.3
110°-120°	0.4	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	204.0	25.7
0°-40°	334.7	42.2
0°-60°	595.6	75.1
0°-90°	781.1	98.5
90°-120°	11.9	1.5
90°-150°	11.9	1.5
90°-180°	12.0	1.5
0°-180°	793.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	262	262	262	262	262	
5°	262	261	260	261	261	25
15°	252	252	252	253	253	71
25°	233	234	234	236	236	107
35°	206	207	208	210	211	129
45°	174	175	177	178	179	134
55°	136	137	140	142	143	121
65°	93	95	98	102	104	92
75°	47	50	57	64	67	50
85°	8	15	26	34	37	10
90°	0	6	15	23	26	0
95°	0	2	8	14	17	0
105°	0	0	1	4	5	0
115°	0	0	0	1	1	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517758

CATALOG NUMBER: HVL8-1-LD4-1STD-30-UNV-O-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	262.3	262.3	262.3	262.3	262.3
2.5°	262.6	262.2	261.0	262.2	262.2
5°	261.7	261.2	260.1	261.3	261.3
7.5°	260.0	259.8	258.8	260.2	260.2
10°	257.9	257.9	257.0	258.6	258.6
12.5°	255.1	255.4	254.5	256.0	256.2
15°	251.8	252.2	251.5	252.9	252.9
17.5°	248.1	248.4	247.9	249.5	249.4
20°	243.6	243.9	243.5	245.2	245.4
22.5°	238.6	239.0	239.0	240.7	241.2
25°	233.3	233.5	233.7	235.7	236.1
27.5°	227.4	227.7	228.1	229.9	230.3
30°	221.0	221.5	222.0	223.8	224.3
32.5°	214.2	214.7	215.3	217.7	217.9
35°	206.5	207.4	208.3	210.4	211.3
37.5°	198.8	200.0	200.8	203.0	203.7
40°	190.7	191.9	193.2	195.6	196.0
42.5°	182.3	183.6	185.2	187.3	188.0
45°	173.7	175.3	176.7	178.4	179.3
47.5°	164.5	166.1	167.8	169.8	170.3
50°	155.0	156.8	158.7	160.5	161.5
52.5°	145.2	147.4	149.5	151.5	152.4
55°	135.6	137.2	139.7	141.8	142.7
57.5°	125.6	126.9	129.2	132.6	133.1
60°	115.4	116.6	119.0	121.7	122.8
62.5°	104.1	105.8	108.3	111.7	112.7
65°	93.2	94.8	98.1	102.0	103.6
67.5°	82.6	83.2	87.4	91.4	94.0
70°	70.1	72.2	77.1	82.1	84.1
72.5°	59.4	61.5	66.8	72.7	75.2
75°	47.2	50.1	57.4	64.2	66.7
77.5°	36.5	39.7	48.7	55.6	58.4
80°	25.5	30.5	40.3	48.1	51.1
82.5°	16.0	22.2	32.7	40.9	43.5
85°	8.2	15.1	25.9	34.3	37.3
87.5°	2.2	9.8	20.2	28.1	31.2
90°	0.1	5.6	15.3	22.9	25.7
92.5°	0.1	3.2	11.4	18.2	21.1
95°	0.1	1.5	7.9	14.3	16.6
97.5°	0.1	0.6	5.4	10.8	13.0
100°	0.1	0.3	3.5	7.9	9.8
102.5°	0.1	0.2	2.2	5.6	7.2
105°	0.1	0.2	1.3	3.8	5.1
107.5°	0.1	0.2	0.7	2.6	3.5
110°	0.2	0.2	0.4	1.6	2.3

TEST NUMBER: P517758

CATALOG NUMBER: HVL8-1-LD4-1STD-30-UNV-O-EDD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.2	0.2	0.2	1.1	1.5
115°	0.2	0.2	0.2	0.7	1.0
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)