

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P518024

Luminaire Tested: HVL8-4-LD4-1HI-50-UNV-C-EDD

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P518024
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-4-LD4-1HI-50-UNV-C-EDD
Description: 4 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 5000K, 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4858.1 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 4' x H: 0.17')
CIE Type: Direct

Input Watts (W): 43
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P518024
CATALOG NUMBER: HVL8-4-LD4-1HI-50-UNV-C-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P518024

CATALOG NUMBER: HVL8-4-LD4-1HI-50-UNV-C-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			99
1	108	103	98	94	105	100	96	92	96	92	89	91	89	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	51	62	56	51	60	54	50			47
5	75	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	39	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6509	6509	6509
5°	6494	6411	6477
10°	6409	6498	6517
15°	6292	6322	6049
20°	6151	5922	5785
25°	6000	5666	5821
30°	5773	5459	5886
35°	5610	5263	5781
40°	5435	5116	5818
45°	5248	4926	5712
50°	5019	4727	5669
55°	4685	4514	5666
60°	4427	4222	5424
65°	3914	3874	5251
70°	3194	3422	4709
75°	2278	2874	4298
80°	1278	2322	3859
85°	474	1753	3400

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5712 cd/sqm

TEST NUMBER: P518024

CATALOG NUMBER: HVL8-4-LD4-1HI-50-UNV-C-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.0	3.2
10°-20°	441.4	9.1
20°-30°	656.7	13.5
30°-40°	789.4	16.2
40°-50°	830.8	17.1
50°-60°	771.0	15.9
60°-70°	609.6	12.5
70°-80°	372.3	7.7
80°-90°	162.2	3.3
90°-100°	50.5	1.0
100°-110°	11.3	0.2
110°-120°	4.6	0.1
120°-130°	2.6	0.1
130°-140°	0.7	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1253.1	25.8
0°-40°	2042.4	42.0
0°-60°	3644.2	75.0
0°-90°	4788.4	98.6
90°-120°	66.4	1.4
90°-150°	69.7	1.4
90°-180°	70.0	1.4
0°-180°	4858.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1613	1613	1613	1613	1613	
5°	1609	1605	1611	1629	1634	152
15°	1523	1581	1596	1544	1545	429
25°	1373	1461	1394	1436	1460	631
35°	1172	1204	1222	1333	1379	732
45°	958	962	1041	1206	1251	738
55°	705	717	830	1012	1093	634
65°	446	461	585	774	845	442
75°	169	224	326	501	533	184
85°	15	53	127	247	283	23
90°	0	16	67	156	184	1
95°	0	4	29	86	105	0
105°	0	2	6	17	24	0
115°	0	1	5	8	8	1
125°	0	1	2	5	7	1
135°	1	1	1	2	2	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P518024

CATALOG NUMBER: HVL8-4-LD4-1HI-50-UNV-C-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1612.6	1612.6	1612.6	1612.6	1612.6
2.5°	1614.6	1610.3	1601.4	1610.0	1612.3
5°	1608.6	1605.4	1610.9	1629.0	1633.6
7.5°	1595.2	1607.7	1622.4	1655.3	1665.8
10°	1575.1	1598.8	1643.1	1671.1	1660.2
12.5°	1550.8	1590.9	1650.4	1595.8	1570.5
15°	1522.6	1581.1	1596.5	1543.6	1544.6
17.5°	1489.4	1572.8	1525.2	1523.9	1514.4
20°	1453.6	1545.2	1482.2	1479.6	1469.4
22.5°	1415.2	1508.8	1444.1	1438.8	1466.4
25°	1373.4	1461.2	1394.5	1436.2	1459.5
27.5°	1321.2	1398.7	1353.1	1412.2	1441.4
30°	1268.3	1334.4	1310.7	1393.2	1445.1
32.5°	1218.7	1267.0	1275.9	1385.9	1394.5
35°	1171.7	1204.3	1222.3	1333.4	1378.7
37.5°	1120.2	1129.0	1177.0	1311.4	1355.1
40°	1067.6	1062.0	1138.9	1275.2	1335.7
42.5°	1011.1	1009.1	1098.5	1257.2	1287.4
45°	957.6	961.8	1041.0	1205.9	1250.9
47.5°	902.7	908.3	986.5	1149.7	1205.6
50°	839.0	846.2	937.9	1099.8	1171.7
52.5°	770.0	783.8	890.6	1052.5	1125.1
55°	705.3	716.8	830.4	1012.1	1092.6
57.5°	646.2	653.1	768.4	961.2	1022.0
60°	588.0	589.7	709.9	904.7	962.8
62.5°	521.3	524.3	649.8	838.0	915.8
65°	446.4	460.6	585.1	774.3	844.6
67.5°	376.5	401.1	519.0	715.8	752.6
70°	301.6	343.3	454.3	647.1	673.1
72.5°	232.9	281.9	388.0	570.3	606.7
75°	168.8	223.7	326.2	501.3	532.8
77.5°	113.7	169.5	268.4	425.1	466.8
80°	68.0	123.8	216.8	354.4	401.4
82.5°	34.8	83.1	168.2	297.3	339.3
85°	15.1	52.6	127.1	246.7	283.2
87.5°	4.3	29.9	93.6	199.4	230.3
90°	0.3	15.8	66.7	156.4	184.3
92.5°	0.3	7.6	47.0	118.3	139.6
95°	0.3	3.9	29.2	85.7	104.8
97.5°	0.3	2.3	17.7	60.8	76.9
100°	0.3	2.0	10.5	40.4	54.9
102.5°	0.3	2.3	7.2	25.6	35.8
105°	0.3	2.3	5.9	16.8	23.7
107.5°	0.7	2.3	5.3	12.5	16.4
110°	0.3	2.0	5.6	9.5	12.8

TEST NUMBER: P518024

CATALOG NUMBER: HVL8-4-LD4-1HI-50-UNV-C-EDD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.7	1.6	5.3	7.9	9.5
115°	0.3	1.3	4.6	7.6	7.9
117.5°	0.7	1.0	3.6	7.6	7.9
120°	0.7	0.7	3.0	7.2	8.2
122.5°	0.7	0.7	2.3	6.6	7.9
125°	0.3	0.7	2.0	4.9	6.9
127.5°	0.7	0.7	1.6	3.9	5.3
130°	0.7	0.7	1.3	3.0	3.9
132.5°	0.7	0.7	1.0	2.3	3.0
135°	0.7	0.7	0.7	1.6	2.3
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)