

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P518055

Luminaire Tested: HVL8-4-LD4-1STD-50-UNV-C-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P518055
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-4-LD4-1STD-50-UNV-C-EDD-90
Description: 4 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 5000K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3775.0 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 4' x H: 0.17')
CIE Type: Direct


Input Watts (W): 32.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P518055

CATALOG NUMBER: HVL8-4-LD4-1STD-50-UNV-C-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P518055

CATALOG NUMBER: HVL8-4-LD4-1STD-50-UNV-C-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			99
1	108	103	98	94	105	100	96	92	96	92	89	91	89	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	51	62	56	51	60	54	50			47
5	75	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	39	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5058	5058	5058
5°	5046	4982	5033
10°	4980	5050	5064
15°	4890	4913	4701
20°	4779	4602	4495
25°	4663	4403	4524
30°	4486	4242	4573
35°	4359	4090	4492
40°	4224	3975	4520
45°	4078	3828	4439
50°	3900	3674	4405
55°	3641	3508	4403
60°	3440	3281	4215
65°	3041	3010	4080
70°	2481	2659	3659
75°	1771	2234	3340
80°	993	1805	2998
85°	367	1363	2641

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 4439 cd/sqm

TEST NUMBER: P518055

CATALOG NUMBER: HVL8-4-LD4-1STD-50-UNV-C-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.4	3.2
10°-20°	343.0	9.1
20°-30°	510.3	13.5
30°-40°	613.4	16.2
40°-50°	645.6	17.1
50°-60°	599.1	15.9
60°-70°	473.7	12.5
70°-80°	289.3	7.7
80°-90°	126.1	3.3
90°-100°	39.3	1.0
100°-110°	8.8	0.2
110°-120°	3.5	0.1
120°-130°	2.0	0.1
130°-140°	0.5	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	973.7	25.8
0°-40°	1587.1	42.0
0°-60°	2831.8	75.0
0°-90°	3720.9	98.6
90°-120°	51.6	1.4
90°-150°	54.2	1.4
90°-180°	54.0	1.4
0°-180°	3775.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1253	1253	1253	1253	1253	
5°	1250	1248	1252	1266	1269	118
15°	1183	1229	1241	1200	1200	333
25°	1067	1135	1084	1116	1134	490
35°	910	936	950	1036	1071	569
45°	744	747	809	937	972	574
55°	548	557	645	786	849	492
65°	347	358	455	602	656	344
75°	131	174	254	390	414	143
85°	12	41	99	192	220	18
90°	0	12	52	122	143	1
95°	0	3	23	67	81	0
105°	0	2	5	13	18	0
115°	0	1	4	6	6	0
125°	0	0	2	4	5	0
135°	0	0	0	1	2	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P518055

CATALOG NUMBER: HVL8-4-LD4-1STD-50-UNV-C-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1253.1	1253.1	1253.1	1253.1	1253.1
2.5°	1254.6	1251.3	1244.4	1251.1	1252.8
5°	1250.0	1247.5	1251.8	1265.9	1269.4
7.5°	1239.6	1249.3	1260.8	1286.3	1294.4
10°	1224.0	1242.4	1276.8	1298.5	1290.1
12.5°	1205.1	1236.2	1282.5	1240.1	1220.4
15°	1183.2	1228.6	1240.6	1199.5	1200.3
17.5°	1157.4	1222.2	1185.2	1184.2	1176.8
20°	1129.5	1200.8	1151.8	1149.7	1141.8
22.5°	1099.7	1172.4	1122.1	1118.1	1139.5
25°	1067.3	1135.4	1083.6	1116.0	1134.1
27.5°	1026.7	1086.9	1051.4	1097.4	1120.1
30°	985.6	1036.9	1018.5	1082.6	1122.9
32.5°	947.0	984.6	991.4	1077.0	1083.6
35°	910.5	935.8	949.8	1036.1	1071.3
37.5°	870.5	877.3	914.6	1019.0	1053.0
40°	829.6	825.3	885.0	990.9	1037.9
42.5°	785.7	784.2	853.6	976.9	1000.4
45°	744.1	747.4	808.9	937.1	972.0
47.5°	701.5	705.8	766.6	893.4	936.8
50°	651.9	657.6	728.8	854.6	910.5
52.5°	598.3	609.1	692.0	817.9	874.3
55°	548.1	557.0	645.3	786.5	849.0
57.5°	502.1	507.5	597.1	746.9	794.1
60°	456.9	458.2	551.6	703.0	748.2
62.5°	405.1	407.4	504.9	651.2	711.7
65°	346.9	357.9	454.6	601.7	656.3
67.5°	292.5	311.7	403.3	556.2	584.8
70°	234.3	266.8	353.0	502.9	523.0
72.5°	181.0	219.0	301.5	443.1	471.5
75°	131.2	173.8	253.5	389.5	414.0
77.5°	88.3	131.7	208.6	330.3	362.7
80°	52.8	96.2	168.5	275.4	311.9
82.5°	27.1	64.6	130.7	231.0	263.7
85°	11.7	40.8	98.8	191.7	220.0
87.5°	3.3	23.2	72.8	154.9	178.9
90°	0.3	12.3	51.8	121.5	143.2
92.5°	0.3	5.9	36.5	91.9	108.5
95°	0.3	3.1	22.7	66.6	81.4
97.5°	0.3	1.8	13.8	47.2	59.7
100°	0.3	1.5	8.2	31.4	42.6
102.5°	0.3	1.8	5.6	19.9	27.8
105°	0.3	1.8	4.6	13.0	18.4
107.5°	0.5	1.8	4.1	9.7	12.8
110°	0.3	1.5	4.3	7.4	10.0

TEST NUMBER: P518055

CATALOG NUMBER: HVL8-4-LD4-1STD-50-UNV-C-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.5	1.3	4.1	6.1	7.4
115°	0.3	1.0	3.6	5.9	6.1
117.5°	0.5	0.8	2.8	5.9	6.1
120°	0.5	0.5	2.3	5.6	6.4
122.5°	0.5	0.5	1.8	5.1	6.1
125°	0.3	0.5	1.5	3.8	5.4
127.5°	0.5	0.5	1.3	3.1	4.1
130°	0.5	0.5	1.0	2.3	3.1
132.5°	0.5	0.5	0.8	1.8	2.3
135°	0.5	0.5	0.5	1.3	1.8
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)