

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517837

Luminaire Tested: HVL8-1-LD4-3LO-30-UNV-O-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517837
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-1-LD4-3LO-30-UNV-O-EDD-90
Description: 1 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 3000K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1843.0 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 1' x H: 0.17')
CIE Type: Direct


Input Watts (W): 16.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517837

CATALOG NUMBER: HVL8-1-LD4-3LO-30-UNV-O-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P517837

CATALOG NUMBER: HVL8-1-LD4-3LO-30-UNV-O-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			98
1	108	102	98	94	105	100	96	92	95	92	89	91	88	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	77	73	79	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	52	62	56	51	60	54	50			47
5	75	61	52	45	72	60	52	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	40	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9843	9843	9843
5°	9717	9550	9632
10°	9548	9309	9439
15°	9362	9057	9207
20°	9172	8783	8982
25°	8963	8508	8753
30°	8735	8220	8493
35°	8470	7910	8236
40°	8197	7587	7936
45°	7903	7243	7612
50°	7548	6854	7263
55°	7164	6435	6878
60°	6718	5911	6431
65°	6093	5335	5986
70°	5274	4675	5468
75°	4215	3960	4999
80°	2829	3261	4568
85°	1211	2553	4158

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7903 cd/sqm

TEST NUMBER: P517837

CATALOG NUMBER: HVL8-1-LD4-3LO-30-UNV-O-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.7	3.1
10°-20°	165.5	9.0
20°-30°	251.1	13.6
30°-40°	303.6	16.5
40°-50°	316.8	17.2
50°-60°	289.6	15.7
60°-70°	225.8	12.3
70°-80°	141.2	7.7
80°-90°	64.1	3.5
90°-100°	21.5	1.2
100°-110°	5.4	0.3
110°-120°	0.8	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	474.2	25.7
0°-40°	777.8	42.2
0°-60°	1384.1	75.1
0°-90°	1815.3	98.5
90°-120°	27.7	1.5
90°-150°	27.7	1.5
90°-180°	28.0	1.5
0°-180°	1843.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	610	610	610	610	610	
5°	608	607	604	607	607	58
15°	585	586	585	588	588	165
25°	542	543	543	548	549	250
35°	480	482	484	489	491	300
45°	404	407	411	415	417	311
55°	315	319	325	330	332	281
65°	216	220	228	237	241	214
75°	110	116	133	149	155	117
85°	19	35	60	80	87	24
90°	0	13	36	53	60	1
95°	0	3	18	33	38	0
105°	0	0	3	9	12	0
115°	0	0	1	2	2	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517837

CATALOG NUMBER: HVL8-1-LD4-3LO-30-UNV-O-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	609.6	609.6	609.6	609.6	609.6
2.5°	610.3	609.4	606.7	609.4	609.3
5°	608.3	607.1	604.4	607.3	607.3
7.5°	604.2	603.8	601.4	604.7	604.7
10°	599.5	599.4	597.3	600.9	601.1
12.5°	592.9	593.5	591.6	595.0	595.5
15°	585.1	586.1	584.6	587.9	587.7
17.5°	576.6	577.2	576.1	579.8	579.7
20°	566.2	566.9	566.0	569.9	570.3
22.5°	554.5	555.5	555.4	559.4	560.6
25°	542.2	542.6	543.2	547.8	548.6
27.5°	528.5	529.2	530.2	534.4	535.3
30°	513.6	514.7	515.9	520.2	521.3
32.5°	497.8	498.9	500.3	505.9	506.5
35°	479.9	482.1	484.1	489.0	491.0
37.5°	462.1	464.9	466.7	471.9	473.5
40°	443.3	446.0	449.0	454.5	455.5
42.5°	423.6	426.8	430.4	435.3	437.0
45°	403.8	407.4	410.7	414.7	416.7
47.5°	382.4	386.0	390.0	394.6	395.9
50°	360.2	364.4	368.7	373.0	375.3
52.5°	337.5	342.6	347.5	352.1	354.2
55°	315.1	318.9	324.8	329.5	331.6
57.5°	291.8	295.0	300.3	308.1	309.2
60°	268.1	271.0	276.5	282.8	285.4
62.5°	242.0	245.9	251.6	259.7	262.0
65°	216.5	220.3	227.9	237.0	240.7
67.5°	192.0	193.3	203.0	212.5	218.6
70°	162.9	167.8	179.2	190.8	195.4
72.5°	137.9	142.8	155.3	169.0	174.7
75°	109.6	116.4	133.3	149.3	154.9
77.5°	84.8	92.3	113.2	129.3	135.8
80°	59.2	70.8	93.7	111.8	118.8
82.5°	37.2	51.6	76.0	95.0	101.2
85°	19.0	35.1	60.2	79.6	86.6
87.5°	5.0	22.7	46.8	65.4	72.6
90°	0.1	13.1	35.5	53.3	59.8
92.5°	0.1	7.3	26.4	42.4	49.0
95°	0.1	3.4	18.4	33.3	38.5
97.5°	0.1	1.4	12.6	25.1	30.3
100°	0.1	0.7	8.0	18.2	22.7
102.5°	0.3	0.4	5.0	13.1	16.7
105°	0.3	0.4	3.0	8.9	11.9
107.5°	0.3	0.4	1.7	6.0	8.2
110°	0.4	0.4	1.0	3.7	5.5

TEST NUMBER: P517837

CATALOG NUMBER: HVL8-1-LD4-3LO-30-UNV-O-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.4	0.4	0.6	2.4	3.6
115°	0.4	0.4	0.6	1.6	2.3
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)