

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P518087

Luminaire Tested: HVL8-4-LD4-2LO-50-UNV-C-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P518087
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-4-LD4-2LO-50-UNV-C-EDD-90
Description: 4 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 5000K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5565.0 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 4' x H: 0.17')
CIE Type: Direct


Input Watts (W): 46.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P518087

CATALOG NUMBER: HVL8-4-LD4-2LO-50-UNV-C-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P518087

CATALOG NUMBER: HVL8-4-LD4-2LO-50-UNV-C-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			99
1	108	103	98	94	105	100	96	92	96	92	89	91	89	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	51	62	56	51	60	54	50			47
5	75	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	39	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7457	7457	7457
5°	7440	7345	7420
10°	7342	7444	7466
15°	7208	7242	6930
20°	7046	6784	6627
25°	6874	6490	6669
30°	6613	6254	6742
35°	6427	6029	6623
40°	6227	5860	6664
45°	6011	5643	6544
50°	5750	5415	6494
55°	5366	5171	6490
60°	5072	4837	6213
65°	4484	4438	6015
70°	3658	3920	5394
75°	2610	3293	4924
80°	1465	2661	4420
85°	543	2008	3894

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 6544 cd/sqm

TEST NUMBER: P518087

CATALOG NUMBER: HVL8-4-LD4-2LO-50-UNV-C-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.5	3.2
10°-20°	505.6	9.1
20°-30°	752.3	13.5
30°-40°	904.2	16.2
40°-50°	951.8	17.1
50°-60°	883.1	15.9
60°-70°	698.3	12.5
70°-80°	426.5	7.7
80°-90°	185.8	3.3
90°-100°	57.9	1.0
100°-110°	13.0	0.2
110°-120°	5.2	0.1
120°-130°	2.9	0.1
130°-140°	0.8	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1435.4	25.8
0°-40°	2339.7	42.0
0°-60°	4174.6	75.0
0°-90°	5485.2	98.6
90°-120°	76.1	1.4
90°-150°	79.8	1.4
90°-180°	80.0	1.4
0°-180°	5565.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1847	1847	1847	1847	1847	
5°	1843	1839	1845	1866	1871	175
15°	1744	1811	1829	1768	1769	491
25°	1573	1674	1597	1645	1672	722
35°	1342	1380	1400	1527	1579	839
45°	1097	1102	1192	1381	1433	846
55°	808	821	951	1159	1252	726
65°	511	528	670	887	968	506
75°	193	256	374	574	610	211
85°	17	60	146	283	324	27
90°	0	18	76	179	211	1
95°	0	4	34	98	120	0
105°	0	3	7	19	27	1
115°	0	2	5	9	9	1
125°	0	1	2	6	8	1
135°	1	1	1	2	3	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P518087

CATALOG NUMBER: HVL8-4-LD4-2LO-50-UNV-C-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1847.3	1847.3	1847.3	1847.3	1847.3
2.5°	1849.5	1844.6	1834.5	1844.3	1846.9
5°	1842.8	1839.0	1845.4	1866.1	1871.4
7.5°	1827.3	1841.6	1858.6	1896.2	1908.2
10°	1804.4	1831.5	1882.3	1914.3	1901.8
12.5°	1776.5	1822.4	1890.6	1828.1	1799.1
15°	1744.2	1811.2	1828.8	1768.3	1769.4
17.5°	1706.2	1801.7	1747.2	1745.7	1734.8
20°	1665.1	1770.1	1697.9	1694.9	1683.2
22.5°	1621.1	1728.4	1654.2	1648.2	1679.8
25°	1573.3	1673.8	1597.4	1645.2	1671.9
27.5°	1513.5	1602.3	1550.0	1617.7	1651.2
30°	1452.9	1528.5	1501.5	1595.9	1655.4
32.5°	1396.1	1451.4	1461.6	1587.6	1597.4
35°	1342.3	1379.5	1400.2	1527.4	1579.3
37.5°	1283.2	1293.4	1348.3	1502.2	1552.3
40°	1223.0	1216.6	1304.6	1460.8	1530.1
42.5°	1158.3	1156.0	1258.4	1440.1	1474.7
45°	1096.9	1101.8	1192.5	1381.4	1433.0
47.5°	1034.1	1040.5	1130.0	1317.1	1381.0
50°	961.1	969.4	1074.3	1259.9	1342.3
52.5°	882.1	897.9	1020.2	1205.7	1288.8
55°	807.9	821.1	951.3	1159.4	1251.6
57.5°	740.2	748.1	880.2	1101.1	1170.7
60°	673.6	675.5	813.2	1036.3	1102.9
62.5°	597.2	600.6	744.3	960.0	1049.1
65°	511.4	527.6	670.2	886.9	967.5
67.5°	431.2	459.5	594.6	820.0	862.1
70°	345.4	393.2	520.4	741.3	771.0
72.5°	266.8	322.9	444.4	653.3	695.0
75°	193.4	256.3	373.7	574.2	610.4
77.5°	130.2	194.2	307.4	486.9	534.7
80°	77.9	141.9	248.4	406.0	459.8
82.5°	39.9	95.2	192.7	340.6	388.7
85°	17.3	60.2	145.6	282.6	324.4
87.5°	4.9	34.2	107.2	228.4	263.8
90°	0.4	18.1	76.4	179.1	211.1
92.5°	0.4	8.7	53.8	135.5	159.9
95°	0.4	4.5	33.5	98.2	120.0
97.5°	0.4	2.6	20.3	69.6	88.1
100°	0.4	2.3	12.0	46.3	62.8
102.5°	0.4	2.6	8.3	29.4	41.0
105°	0.4	2.6	6.8	19.2	27.1
107.5°	0.8	2.6	6.0	14.3	18.8
110°	0.4	2.3	6.4	10.9	14.7

TEST NUMBER: P518087

CATALOG NUMBER: HVL8-4-LD4-2LO-50-UNV-C-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.8	1.9	6.0	9.0	10.9
115°	0.4	1.5	5.3	8.7	9.0
117.5°	0.8	1.1	4.1	8.7	9.0
120°	0.8	0.8	3.4	8.3	9.4
122.5°	0.8	0.8	2.6	7.5	9.0
125°	0.4	0.8	2.3	5.6	7.9
127.5°	0.8	0.8	1.9	4.5	6.0
130°	0.8	0.8	1.5	3.4	4.5
132.5°	0.8	0.8	1.1	2.6	3.4
135°	0.8	0.8	0.8	1.9	2.6
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)