

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517878

Luminaire Tested: HVL8-2-LD4-1HI-40-UNV-O-EDD

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517878
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-2-LD4-1HI-40-UNV-O-EDD
Description: 2 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 4000K, 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1817.0 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 2' x H: 0.17')
CIE Type: Direct


Input Watts (W): 21.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517878

CATALOG NUMBER: HVL8-2-LD4-1HI-40-UNV-O-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P517878

CATALOG NUMBER: HVL8-2-LD4-1HI-40-UNV-O-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		101
1	108	102	98	94	105	100	96	92	95	92	89		91	88	86		87
2	98	89	82	76	95	87	80	75	83	77	73		79	75	71		76
3	89	78	69	63	86	76	68	62	73	66	61		70	64	59		67
4	81	69	60	53	79	67	59	52	65	57	52		62	56	51		60
5	75	61	52	45	72	60	52	45	58	50	44		56	49	44		54
6	69	55	46	40	67	54	46	39	52	45	39		50	44	38		49
7	64	50	41	35	62	49	41	35	47	40	34		46	39	34		44
8	59	46	37	31	58	45	37	31	43	36	31		42	35	30		41
9	55	42	34	28	54	41	33	28	40	33	28		39	32	27		38
10	52	39	31	25	51	38	30	25	37	30	25		36	29	25		35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4852	4852	4852
5°	4825	4731	4748
10°	4775	4635	4653
15°	4716	4530	4538
20°	4654	4415	4428
25°	4583	4298	4315
30°	4503	4173	4187
35°	4406	4037	4060
40°	4304	3895	3912
45°	4195	3741	3752
50°	4058	3564	3580
55°	3908	3372	3391
60°	3730	3125	3170
65°	3460	2851	2951
70°	3086	2531	2696
75°	2572	2182	2464
80°	1844	1838	2253
85°	887	1489	2050

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4195 cd/sqm

TEST NUMBER: P517878

CATALOG NUMBER: HVL8-2-LD4-1HI-40-UNV-O-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.9	3.1
10°-20°	163.1	9.0
20°-30°	247.5	13.6
30°-40°	299.3	16.5
40°-50°	312.3	17.2
50°-60°	285.5	15.7
60°-70°	222.6	12.3
70°-80°	139.2	7.7
80°-90°	63.2	3.5
90°-100°	21.2	1.2
100°-110°	5.3	0.3
110°-120°	0.8	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	467.5	25.7
0°-40°	766.8	42.2
0°-60°	1364.6	75.1
0°-90°	1789.7	98.5
90°-120°	27.4	1.5
90°-150°	27.4	1.5
90°-180°	27.0	1.5
0°-180°	1817.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	601	601	601	601	601	
5°	600	598	596	599	599	57
15°	577	578	576	580	579	163
25°	534	535	536	540	541	246
35°	473	475	477	482	484	296
45°	398	402	405	409	411	307
55°	311	314	320	325	327	278
65°	214	217	225	234	237	211
75°	108	115	132	147	153	115
85°	19	35	59	78	85	24
90°	0	13	35	53	59	1
95°	0	3	18	33	38	0
105°	0	0	3	9	12	0
115°	0	0	1	2	2	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517878

CATALOG NUMBER: HVL8-2-LD4-1HI-40-UNV-O-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	601.0	601.0	601.0	601.0	601.0
2.5°	601.7	600.8	598.1	600.8	600.7
5°	599.7	598.5	595.9	598.7	598.7
7.5°	595.7	595.3	592.9	596.1	596.1
10°	591.0	590.9	588.9	592.5	592.6
12.5°	584.5	585.1	583.2	586.6	587.1
15°	576.9	577.9	576.3	579.6	579.4
17.5°	568.5	569.1	567.9	571.6	571.5
20°	558.2	558.9	558.0	561.9	562.3
22.5°	546.7	547.7	547.5	551.5	552.6
25°	534.5	534.9	535.5	540.0	540.9
27.5°	521.1	521.8	522.8	526.9	527.7
30°	506.3	507.5	508.6	512.8	514.0
32.5°	490.7	491.9	493.3	498.8	499.4
35°	473.2	475.3	477.3	482.1	484.1
37.5°	455.6	458.3	460.1	465.2	466.8
40°	437.0	439.7	442.7	448.1	449.1
42.5°	417.6	420.8	424.3	429.1	430.8
45°	398.1	401.6	404.9	408.9	410.8
47.5°	377.0	380.5	384.5	389.0	390.3
50°	355.2	359.3	363.5	367.8	370.0
52.5°	332.8	337.7	342.6	347.1	349.2
55°	310.7	314.4	320.2	324.8	327.0
57.5°	287.7	290.8	296.1	303.7	304.9
60°	264.4	267.2	272.6	278.8	281.4
62.5°	238.6	242.4	248.1	256.0	258.3
65°	213.5	217.2	224.7	233.6	237.3
67.5°	189.3	190.5	200.2	209.5	215.5
70°	160.7	165.5	176.7	188.1	192.7
72.5°	136.0	140.8	153.1	166.6	172.3
75°	108.1	114.8	131.5	147.2	152.7
77.5°	83.6	91.0	111.6	127.5	133.9
80°	58.4	69.8	92.4	110.2	117.2
82.5°	36.7	50.9	74.9	93.6	99.7
85°	18.7	34.6	59.4	78.5	85.4
87.5°	5.0	22.4	46.2	64.5	71.5
90°	0.1	12.9	35.0	52.6	58.9
92.5°	0.1	7.2	26.1	41.8	48.3
95°	0.1	3.4	18.1	32.9	38.0
97.5°	0.1	1.4	12.5	24.8	29.9
100°	0.1	0.7	7.9	18.0	22.4
102.5°	0.3	0.4	5.0	12.9	16.4
105°	0.3	0.4	3.0	8.8	11.8
107.5°	0.3	0.4	1.7	6.0	8.1
110°	0.4	0.4	1.0	3.7	5.4

TEST NUMBER: P517878

CATALOG NUMBER: HVL8-2-LD4-1HI-40-UNV-O-EDD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.4	0.4	0.6	2.4	3.5
115°	0.4	0.4	0.6	1.6	2.3
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)