

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P518112

Luminaire Tested: HVL8-4-LD4-3HI-35-UNV-C-EDD

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P518112
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-4-LD4-3HI-35-UNV-C-EDD
Description: 4 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 3500K, 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14165.0 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 4' x H: 0.17')
CIE Type: Direct


Input Watts (W): 125.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P518112

CATALOG NUMBER: HVL8-4-LD4-3HI-35-UNV-C-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P518112

CATALOG NUMBER: HVL8-4-LD4-3HI-35-UNV-C-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			99
1	108	103	98	94	105	100	96	92	96	92	89	91	89	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	51	62	56	51	60	54	50			47
5	75	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	39	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18979	18979	18979
5°	18936	18695	18887
10°	18687	18948	19004
15°	18348	18434	17639
20°	17934	17268	16869
25°	17496	16520	16975
30°	16832	15917	17161
35°	16358	15346	16857
40°	15849	14916	16963
45°	15301	14364	16656
50°	14635	13784	16529
55°	13659	13163	16520
60°	12909	12311	15815
65°	11413	11296	15311
70°	9311	9979	13730
75°	6644	8381	12533
80°	3728	6773	11252
85°	1383	5113	9912

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 16656 cd/sqm

TEST NUMBER: P518112

CATALOG NUMBER: HVL8-4-LD4-3HI-35-UNV-C-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	451.9	3.2
10°-20°	1286.9	9.1
20°-30°	1914.8	13.5
30°-40°	2301.6	16.2
40°-50°	2422.6	17.1
50°-60°	2247.9	15.9
60°-70°	1777.4	12.5
70°-80°	1085.7	7.7
80°-90°	473.0	3.3
90°-100°	147.3	1.0
100°-110°	33.1	0.2
110°-120°	13.3	0.1
120°-130°	7.5	0.1
130°-140°	2.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3653.7	25.8
0°-40°	5955.3	42.0
0°-60°	10625.8	75.0
0°-90°	13961.9	98.6
90°-120°	193.6	1.4
90°-150°	203.1	1.4
90°-180°	203.0	1.4
0°-180°	14165.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4702	4702	4702	4702	4702	
5°	4690	4681	4697	4750	4763	445
15°	4440	4610	4655	4501	4504	1251
25°	4005	4260	4066	4188	4256	1839
35°	3417	3511	3564	3888	4020	2135
45°	2792	2804	3035	3516	3647	2152
55°	2056	2090	2421	2951	3186	1848
65°	1302	1343	1706	2258	2463	1289
75°	492	652	951	1462	1554	537
85°	44	153	371	719	826	68
90°	1	46	194	456	537	2
95°	1	12	85	250	306	1
105°	1	7	17	49	69	1
115°	1	4	13	22	23	2
125°	1	2	6	14	20	2
135°	2	2	2	5	7	1
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P518112

CATALOG NUMBER: HVL8-4-LD4-3HI-35-UNV-C-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4702.0	4702.0	4702.0	4702.0	4702.0
2.5°	4707.8	4695.3	4669.4	4694.3	4701.1
5°	4690.5	4680.9	4697.2	4749.9	4763.3
7.5°	4651.2	4687.6	4730.7	4826.5	4857.2
10°	4592.8	4661.8	4791.1	4872.5	4840.9
12.5°	4521.9	4638.8	4812.2	4653.2	4579.4
15°	4439.6	4610.1	4655.1	4500.9	4503.7
17.5°	4342.8	4586.1	4447.2	4443.4	4415.6
20°	4238.4	4505.7	4321.7	4314.1	4284.4
22.5°	4126.4	4399.3	4210.6	4195.3	4275.8
25°	4004.7	4260.4	4066.0	4187.7	4255.7
27.5°	3852.4	4078.5	3945.3	4117.7	4203.0
30°	3698.2	3890.7	3821.8	4062.2	4213.5
32.5°	3553.6	3694.4	3720.2	4041.1	4066.0
35°	3416.6	3511.4	3564.1	3887.9	4020.0
37.5°	3266.2	3292.1	3431.9	3823.7	3951.1
40°	3113.0	3096.7	3320.8	3718.3	3894.6
42.5°	2948.2	2942.5	3203.0	3665.6	3753.8
45°	2792.1	2804.5	3035.4	3516.2	3647.4
47.5°	2632.1	2648.4	2876.4	3352.4	3515.3
50°	2446.3	2467.4	2734.6	3206.8	3416.6
52.5°	2245.2	2285.4	2596.7	3068.9	3280.6
55°	2056.5	2090.0	2421.4	2951.1	3185.8
57.5°	1884.1	1904.2	2240.4	2802.6	2979.8
60°	1714.5	1719.3	2069.9	2637.9	2807.4
62.5°	1520.1	1528.7	1894.6	2443.4	2670.4
65°	1301.7	1342.9	1705.9	2257.6	2462.6
67.5°	1097.7	1169.5	1513.4	2087.1	2194.4
70°	879.3	1000.9	1324.7	1886.9	1962.6
72.5°	679.1	821.8	1131.2	1662.8	1769.1
75°	492.3	652.3	951.1	1461.7	1553.6
77.5°	331.4	494.2	782.6	1239.4	1361.1
80°	198.3	361.1	632.2	1033.5	1170.5
82.5°	101.5	242.3	490.4	866.8	989.4
85°	44.1	153.3	370.7	719.3	825.7
87.5°	12.5	87.2	273.0	581.4	671.4
90°	1.0	46.0	194.4	455.9	537.3
92.5°	1.0	22.0	137.0	344.8	407.1
95°	1.0	11.5	85.2	250.0	305.5
97.5°	1.0	6.7	51.7	177.2	224.1
100°	1.0	5.7	30.7	117.8	160.0
102.5°	1.0	6.7	21.1	74.7	104.4
105°	1.0	6.7	17.2	48.8	69.0
107.5°	1.9	6.7	15.3	36.4	47.9
110°	1.0	5.7	16.3	27.8	37.4

TEST NUMBER: P518112

CATALOG NUMBER: HVL8-4-LD4-3HI-35-UNV-C-EDD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1.9	4.8	15.3	23.0	27.8
115°	1.0	3.8	13.4	22.0	23.0
117.5°	1.9	2.9	10.5	22.0	23.0
120°	1.9	1.9	8.6	21.1	23.9
122.5°	1.9	1.9	6.7	19.2	23.0
125°	1.0	1.9	5.7	14.4	20.1
127.5°	1.9	1.9	4.8	11.5	15.3
130°	1.9	1.9	3.8	8.6	11.5
132.5°	1.9	1.9	2.9	6.7	8.6
135°	1.9	1.9	1.9	4.8	6.7
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)