

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P518116

Luminaire Tested: HVL8-4-LD4-3HI-40-UNV-C-EDD

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P518116
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-4-LD4-3HI-40-UNV-C-EDD
Description: 4 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 4000K, 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14307.0 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 4' x H: 0.17')
CIE Type: Direct


Input Watts (W): 125.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P518116

CATALOG NUMBER: HVL8-4-LD4-3HI-40-UNV-C-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P518116

CATALOG NUMBER: HVL8-4-LD4-3HI-40-UNV-C-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			99
1	108	103	98	94	105	100	96	92	96	92	89	91	89	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	51	62	56	51	60	54	50			47
5	75	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	39	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19170	19170	19170
5°	19126	18883	19077
10°	18875	19138	19194
15°	18531	18619	17816
20°	18114	17441	17037
25°	17672	16686	17145
30°	17001	16077	17334
35°	16522	15500	17026
40°	16008	15066	17132
45°	15454	14508	16823
50°	14782	13922	16695
55°	13796	13295	16686
60°	13039	12435	15974
65°	11527	11409	15464
70°	9404	10079	13868
75°	6712	8466	12659
80°	3766	6840	11364
85°	1396	5164	10010

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 16823 cd/sqm

TEST NUMBER: P518116

CATALOG NUMBER: HVL8-4-LD4-3HI-40-UNV-C-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	456.4	3.2
10°-20°	1299.8	9.1
20°-30°	1934.0	13.5
30°-40°	2324.7	16.2
40°-50°	2446.9	17.1
50°-60°	2270.4	15.9
60°-70°	1795.2	12.5
70°-80°	1096.6	7.7
80°-90°	477.7	3.3
90°-100°	148.7	1.0
100°-110°	33.4	0.2
110°-120°	13.4	0.1
120°-130°	7.5	0.1
130°-140°	2.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3690.3	25.8
0°-40°	6015.0	42.0
0°-60°	10732.3	75.0
0°-90°	14101.8	98.6
90°-120°	195.6	1.4
90°-150°	205.2	1.4
90°-180°	205.0	1.4
0°-180°	14307.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4749	4749	4749	4749	4749	
5°	4738	4728	4744	4798	4811	449
15°	4484	4656	4702	4546	4549	1263
25°	4045	4303	4107	4230	4298	1857
35°	3451	3547	3600	3927	4060	2157
45°	2820	2833	3066	3552	3684	2174
55°	2077	2111	2446	2981	3218	1866
65°	1315	1356	1723	2280	2487	1302
75°	497	659	961	1476	1569	543
85°	44	155	374	726	834	69
90°	1	46	196	460	543	2
95°	1	12	86	252	309	1
105°	1	7	17	49	70	1
115°	1	4	14	22	23	2
125°	1	2	6	14	20	2
135°	2	2	2	5	7	1
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P518116

CATALOG NUMBER: HVL8-4-LD4-3HI-40-UNV-C-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4749.1	4749.1	4749.1	4749.1	4749.1
2.5°	4755.0	4742.4	4716.3	4741.4	4748.2
5°	4737.5	4727.9	4744.3	4797.5	4811.1
7.5°	4697.9	4734.6	4778.2	4874.9	4905.9
10°	4638.9	4708.5	4839.1	4921.3	4889.4
12.5°	4567.3	4685.3	4860.4	4699.8	4625.3
15°	4484.1	4656.3	4701.7	4546.0	4548.9
17.5°	4386.4	4632.1	4491.8	4487.9	4459.9
20°	4280.9	4550.8	4365.1	4357.3	4327.3
22.5°	4167.7	4443.4	4252.9	4237.4	4318.6
25°	4044.9	4303.2	4106.8	4229.6	4298.3
27.5°	3891.0	4119.3	3984.9	4159.0	4245.1
30°	3735.3	3929.7	3860.1	4102.9	4255.8
32.5°	3589.2	3731.4	3757.5	4081.6	4106.8
35°	3450.8	3546.6	3599.8	3926.8	4060.3
37.5°	3299.0	3325.1	3466.3	3862.0	3990.7
40°	3144.2	3127.7	3354.1	3755.6	3933.6
42.5°	2977.8	2972.0	3235.1	3702.4	3791.4
45°	2820.1	2832.7	3065.8	3551.5	3684.0
47.5°	2658.5	2675.0	2905.2	3386.0	3550.5
50°	2470.8	2492.1	2762.0	3239.0	3450.8
52.5°	2267.7	2308.3	2622.7	3099.7	3313.5
55°	2077.1	2110.9	2445.7	2980.7	3217.7
57.5°	1902.9	1923.3	2262.8	2830.7	3009.7
60°	1731.7	1736.5	2090.6	2664.3	2835.6
62.5°	1535.3	1544.0	1913.6	2467.9	2697.2
65°	1314.7	1356.3	1723.0	2280.2	2487.3
67.5°	1108.7	1181.2	1528.5	2108.0	2216.4
70°	888.1	1011.0	1338.0	1905.8	1982.3
72.5°	685.9	830.1	1142.5	1679.5	1786.9
75°	497.3	658.8	960.7	1476.3	1569.2
77.5°	334.7	499.2	790.4	1251.9	1374.7
80°	200.3	364.7	638.5	1043.9	1182.2
82.5°	102.5	244.8	495.3	875.5	999.4
85°	44.5	154.8	374.4	726.5	833.9
87.5°	12.6	88.0	275.7	587.2	678.2
90°	1.0	46.4	196.4	460.5	542.7
92.5°	1.0	22.3	138.3	348.3	411.2
95°	1.0	11.6	86.1	252.5	308.6
97.5°	1.0	6.8	52.2	179.0	226.4
100°	1.0	5.8	31.0	119.0	161.6
102.5°	1.0	6.8	21.3	75.5	105.5
105°	1.0	6.8	17.4	49.3	69.7
107.5°	1.9	6.8	15.5	36.8	48.4
110°	1.0	5.8	16.4	28.1	37.7

TEST NUMBER: P518116

CATALOG NUMBER: HVL8-4-LD4-3HI-40-UNV-C-EDD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1.9	4.8	15.5	23.2	28.1
115°	1.0	3.9	13.5	22.3	23.2
117.5°	1.9	2.9	10.6	22.3	23.2
120°	1.9	1.9	8.7	21.3	24.2
122.5°	1.9	1.9	6.8	19.3	23.2
125°	1.0	1.9	5.8	14.5	20.3
127.5°	1.9	1.9	4.8	11.6	15.5
130°	1.9	1.9	3.9	8.7	11.6
132.5°	1.9	1.9	2.9	6.8	8.7
135°	1.9	1.9	1.9	4.8	6.8
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)