

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517890

Luminaire Tested: HVL8-2-LD4-1LO-35-UNV-O-EDD

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517890
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-2-LD4-1LO-35-UNV-O-EDD
Description: 2 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 3500K, 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1081.0 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 2' x H: 0.17')
CIE Type: Direct


Input Watts (W): 11.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517890

CATALOG NUMBER: HVL8-2-LD4-1LO-35-UNV-O-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P517890

CATALOG NUMBER: HVL8-2-LD4-1LO-35-UNV-O-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			98
1	108	102	98	94	105	100	96	92	95	92	89	91	88	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	77	73	79	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	52	62	56	51	60	54	50			47
5	75	61	52	45	72	60	52	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	40	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2886	2886	2886
5°	2870	2815	2825
10°	2840	2758	2768
15°	2806	2696	2700
20°	2769	2627	2634
25°	2727	2557	2567
30°	2679	2483	2491
35°	2621	2402	2415
40°	2561	2317	2328
45°	2496	2226	2232
50°	2414	2121	2130
55°	2324	2006	2017
60°	2219	1860	1886
65°	2058	1696	1756
70°	1836	1506	1603
75°	1530	1298	1467
80°	1095	1094	1340
85°	527	885	1220

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2496 cd/sqm

TEST NUMBER: P517890

CATALOG NUMBER: HVL8-2-LD4-1LO-35-UNV-O-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.8	3.1
10°-20°	97.1	9.0
20°-30°	147.3	13.6
30°-40°	178.1	16.5
40°-50°	185.8	17.2
50°-60°	169.9	15.7
60°-70°	132.4	12.3
70°-80°	82.8	7.7
80°-90°	37.6	3.5
90°-100°	12.6	1.2
100°-110°	3.2	0.3
110°-120°	0.5	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	278.1	25.7
0°-40°	456.2	42.2
0°-60°	811.9	75.1
0°-90°	1064.8	98.5
90°-120°	16.3	1.5
90°-150°	16.3	1.5
90°-180°	16.0	1.5
0°-180°	1081.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	358	358	358	358	358	
5°	357	356	354	356	356	34
15°	343	344	343	345	345	97
25°	318	318	319	321	322	147
35°	282	283	284	287	288	176
45°	237	239	241	243	244	182
55°	185	187	190	193	194	165
65°	127	129	134	139	141	126
75°	64	68	78	88	91	69
85°	11	21	35	47	51	14
90°	0	8	21	31	35	0
95°	0	2	11	20	23	0
105°	0	0	2	5	7	0
115°	0	0	0	1	1	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517890

CATALOG NUMBER: HVL8-2-LD4-1LO-35-UNV-O-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	357.5	357.5	357.5	357.5	357.5
2.5°	358.0	357.4	355.8	357.4	357.4
5°	356.8	356.1	354.5	356.2	356.2
7.5°	354.4	354.2	352.7	354.7	354.7
10°	351.6	351.5	350.4	352.5	352.6
12.5°	347.8	348.1	347.0	349.0	349.3
15°	343.2	343.8	342.9	344.8	344.7
17.5°	338.2	338.6	337.9	340.1	340.0
20°	332.1	332.5	332.0	334.3	334.5
22.5°	325.2	325.8	325.8	328.1	328.8
25°	318.0	318.3	318.6	321.3	321.8
27.5°	310.0	310.4	311.0	313.4	314.0
30°	301.2	301.9	302.6	305.1	305.8
32.5°	292.0	292.6	293.5	296.8	297.1
35°	281.5	282.8	284.0	286.8	288.0
37.5°	271.1	272.7	273.8	276.8	277.7
40°	260.0	261.6	263.4	266.6	267.2
42.5°	248.5	250.3	252.4	255.3	256.3
45°	236.8	238.9	240.9	243.2	244.4
47.5°	224.3	226.4	228.7	231.4	232.2
50°	211.3	213.7	216.3	218.8	220.1
52.5°	198.0	200.9	203.8	206.5	207.8
55°	184.8	187.0	190.5	193.3	194.5
57.5°	171.2	173.0	176.2	180.7	181.4
60°	157.3	159.0	162.2	165.9	167.4
62.5°	141.9	144.2	147.6	152.3	153.6
65°	127.0	129.2	133.7	139.0	141.2
67.5°	112.6	113.4	119.1	124.7	128.2
70°	95.6	98.4	105.1	111.9	114.6
72.5°	80.9	83.8	91.1	99.1	102.5
75°	64.3	68.3	78.2	87.6	90.9
77.5°	49.7	54.1	66.4	75.9	79.6
80°	34.7	41.6	55.0	65.6	69.7
82.5°	21.8	30.3	44.6	55.7	59.3
85°	11.1	20.6	35.3	46.7	50.8
87.5°	2.9	13.3	27.5	38.3	42.6
90°	0.1	7.7	20.8	31.3	35.1
92.5°	0.1	4.3	15.5	24.9	28.7
95°	0.1	2.0	10.8	19.6	22.6
97.5°	0.1	0.8	7.4	14.7	17.8
100°	0.1	0.4	4.7	10.7	13.3
102.5°	0.2	0.3	2.9	7.7	9.8
105°	0.2	0.3	1.8	5.2	7.0
107.5°	0.2	0.3	1.0	3.5	4.8
110°	0.3	0.3	0.6	2.2	3.2

TEST NUMBER: P517890

CATALOG NUMBER: HVL8-2-LD4-1LO-35-UNV-O-EDD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.3	0.3	0.3	1.4	2.1
115°	0.3	0.3	0.3	0.9	1.3
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)