

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P518147

Luminaire Tested: HVL8-4-LD4-3STD-40-UNV-C-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P518147
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-4-LD4-3STD-40-UNV-C-EDD-90
Description: 4 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 4000K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11117.0 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.32 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 4' x H: 0.17')
CIE Type: Direct


Input Watts (W): 95.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P518147

CATALOG NUMBER: HVL8-4-LD4-3STD-40-UNV-C-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P518147

CATALOG NUMBER: HVL8-4-LD4-3STD-40-UNV-C-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			99
1	108	103	98	94	105	100	96	92	96	92	89	91	89	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	78	73	80	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	51	62	56	51	60	54	50			47
5	75	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	39	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14895	14895	14895
5°	14862	14672	14823
10°	14666	14871	14914
15°	14400	14467	13843
20°	14075	13552	13239
25°	13731	12965	13322
30°	13210	12492	13469
35°	12838	12044	13230
40°	12438	11706	13312
45°	12008	11273	13072
50°	11486	10818	12972
55°	10720	10330	12965
60°	10132	9662	12412
65°	8957	8865	12016
70°	7308	7831	10776
75°	5215	6578	9836
80°	2925	5315	8830
85°	1085	4012	7779

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 13072 cd/sqm

TEST NUMBER: P518147

CATALOG NUMBER: HVL8-4-LD4-3STD-40-UNV-C-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	354.7	3.2
10°-20°	1010.0	9.1
20°-30°	1502.8	13.5
30°-40°	1806.4	16.2
40°-50°	1901.3	17.1
50°-60°	1764.2	15.9
60°-70°	1394.9	12.5
70°-80°	852.1	7.7
80°-90°	371.2	3.3
90°-100°	115.6	1.0
100°-110°	26.0	0.2
110°-120°	10.4	0.1
120°-130°	5.9	0.1
130°-140°	1.6	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2867.5	25.8
0°-40°	4673.9	42.0
0°-60°	8339.4	75.0
0°-90°	10957.6	98.6
90°-120°	152.0	1.4
90°-150°	159.4	1.4
90°-180°	159.0	1.4
0°-180°	11117.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3690	3690	3690	3690	3690	
5°	3681	3674	3686	3728	3738	349
15°	3484	3618	3653	3532	3535	982
25°	3143	3344	3191	3287	3340	1443
35°	2681	2756	2797	3051	3155	1676
45°	2191	2201	2382	2760	2863	1689
55°	1614	1640	1900	2316	2500	1450
65°	1022	1054	1339	1772	1933	1012
75°	386	512	746	1147	1219	422
85°	35	120	291	564	648	54
90°	1	36	153	358	422	2
95°	1	9	67	196	240	1
105°	1	5	14	38	54	1
115°	1	3	10	17	18	1
125°	1	2	4	11	16	1
135°	2	2	2	4	5	1
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P518147

CATALOG NUMBER: HVL8-4-LD4-3STD-40-UNV-C-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3690.2	3690.2	3690.2	3690.2	3690.2
2.5°	3694.7	3685.0	3664.7	3684.2	3689.5
5°	3681.2	3673.7	3686.5	3727.8	3738.3
7.5°	3650.4	3679.0	3712.8	3788.0	3812.0
10°	3604.5	3658.7	3760.2	3824.0	3799.2
12.5°	3548.9	3640.6	3776.7	3651.9	3594.0
15°	3484.3	3618.1	3653.4	3532.4	3534.6
17.5°	3408.3	3599.3	3490.3	3487.3	3465.5
20°	3326.4	3536.1	3391.8	3385.8	3362.5
22.5°	3238.4	3452.7	3304.6	3292.6	3355.7
25°	3143.0	3343.7	3191.1	3286.6	3339.9
27.5°	3023.5	3200.9	3096.4	3231.7	3298.6
30°	2902.4	3053.5	2999.4	3188.1	3306.9
32.5°	2788.9	2899.4	2919.7	3171.5	3191.1
35°	2681.4	2755.8	2797.2	3051.3	3155.0
37.5°	2563.4	2583.7	2693.4	3000.9	3100.9
40°	2443.1	2430.3	2606.2	2918.2	3056.5
42.5°	2313.8	2309.3	2513.8	2876.9	2946.0
45°	2191.3	2201.1	2382.2	2759.6	2862.6
47.5°	2065.8	2078.5	2257.4	2631.1	2758.8
50°	1919.9	1936.5	2146.2	2516.8	2681.4
52.5°	1762.1	1793.6	2037.9	2408.5	2574.7
55°	1614.0	1640.3	1900.4	2316.1	2500.3
57.5°	1478.7	1494.4	1758.3	2199.6	2338.6
60°	1345.6	1349.4	1624.5	2070.3	2203.3
62.5°	1193.0	1199.8	1486.9	1917.7	2095.8
65°	1021.6	1053.9	1338.8	1771.8	1932.7
67.5°	861.5	917.9	1187.7	1638.0	1722.2
70°	690.1	785.6	1039.6	1480.9	1540.3
72.5°	533.0	645.0	887.8	1305.0	1388.4
75°	386.4	511.9	746.5	1147.1	1219.3
77.5°	260.1	387.9	614.2	972.7	1068.2
80°	155.6	283.4	496.1	811.1	918.6
82.5°	79.7	190.2	384.9	680.3	776.5
85°	34.6	120.3	290.9	564.5	648.0
87.5°	9.8	68.4	214.2	456.3	527.0
90°	0.8	36.1	152.6	357.8	421.7
92.5°	0.8	17.3	107.5	270.6	319.5
95°	0.8	9.0	66.9	196.2	239.8
97.5°	0.8	5.3	40.6	139.1	175.9
100°	0.8	4.5	24.1	92.5	125.5
102.5°	0.8	5.3	16.5	58.6	81.9
105°	0.8	5.3	13.5	38.3	54.1
107.5°	1.5	5.3	12.0	28.6	37.6
110°	0.8	4.5	12.8	21.8	29.3

TEST NUMBER: P518147

CATALOG NUMBER: HVL8-4-LD4-3STD-40-UNV-C-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1.5	3.8	12.0	18.0	21.8
115°	0.8	3.0	10.5	17.3	18.0
117.5°	1.5	2.3	8.3	17.3	18.0
120°	1.5	1.5	6.8	16.5	18.8
122.5°	1.5	1.5	5.3	15.0	18.0
125°	0.8	1.5	4.5	11.3	15.8
127.5°	1.5	1.5	3.8	9.0	12.0
130°	1.5	1.5	3.0	6.8	9.0
132.5°	1.5	1.5	2.3	5.3	6.8
135°	1.5	1.5	1.5	3.8	5.3
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)