

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517893

Luminaire Tested: HVL8-2-LD4-1LO-40-UNV-O-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517893
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-2-LD4-1LO-40-UNV-O-EDD-90
Description: 2 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 4000K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1305.0 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 2' x H: 0.17')
CIE Type: Direct


Input Watts (W): 11.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517893

CATALOG NUMBER: HVL8-2-LD4-1LO-40-UNV-O-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P517893

CATALOG NUMBER: HVL8-2-LD4-1LO-40-UNV-O-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		98
1	108	102	98	94	105	100	96	92	95	92	89		91	88	86		81
2	98	89	82	76	95	87	80	75	83	77	73		79	75	71		67
3	89	78	69	63	86	76	68	62	73	66	61		70	64	59		56
4	81	69	60	53	79	67	59	52	65	57	52		62	56	51		47
5	75	61	52	45	72	60	52	45	58	50	44		56	49	44		41
6	69	55	46	40	67	54	46	39	52	45	39		50	44	38		36
7	64	50	41	35	62	49	41	35	47	40	34		46	39	34		32
8	59	46	37	31	58	45	37	31	43	36	31		42	35	30		28
9	55	42	34	28	54	41	33	28	40	33	28		39	32	27		25
10	52	39	31	25	51	38	30	25	37	30	25		36	29	25		23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3484	3484	3484
5°	3465	3398	3410
10°	3429	3329	3342
15°	3387	3254	3259
20°	3343	3171	3180
25°	3292	3087	3099
30°	3234	2997	3007
35°	3164	2900	2916
40°	3092	2798	2809
45°	3013	2687	2695
50°	2914	2560	2572
55°	2806	2422	2435
60°	2679	2245	2277
65°	2484	2048	2119
70°	2216	1818	1936
75°	1846	1566	1770
80°	1323	1319	1617
85°	636	1068	1474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3013 cd/sqm

TEST NUMBER: P517893

CATALOG NUMBER: HVL8-2-LD4-1LO-40-UNV-O-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.8	3.1
10°-20°	117.2	9.0
20°-30°	177.8	13.6
30°-40°	215.0	16.5
40°-50°	224.3	17.2
50°-60°	205.1	15.7
60°-70°	159.9	12.3
70°-80°	100.0	7.7
80°-90°	45.4	3.5
90°-100°	15.2	1.2
100°-110°	3.8	0.3
110°-120°	0.6	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	335.8	25.7
0°-40°	550.7	42.2
0°-60°	980.1	75.1
0°-90°	1285.4	98.5
90°-120°	19.6	1.5
90°-150°	19.6	1.5
90°-180°	20.0	1.5
0°-180°	1305.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	432	432	432	432	432	
5°	431	430	428	430	430	41
15°	414	415	414	416	416	117
25°	384	384	385	388	388	177
35°	340	341	343	346	348	213
45°	286	288	291	294	295	220
55°	223	226	230	233	235	199
65°	153	156	161	168	170	152
75°	78	82	94	106	110	83
85°	13	25	43	56	61	17
90°	0	9	25	38	42	1
95°	0	2	13	24	27	0
105°	0	0	2	6	8	0
115°	0	0	0	1	2	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517893

CATALOG NUMBER: HVL8-2-LD4-1LO-40-UNV-O-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	431.6	431.6	431.6	431.6	431.6
2.5°	432.1	431.5	429.6	431.5	431.4
5°	430.7	429.9	428.0	430.0	430.0
7.5°	427.9	427.5	425.8	428.2	428.2
10°	424.5	424.4	423.0	425.5	425.6
12.5°	419.8	420.2	418.9	421.3	421.6
15°	414.3	415.0	413.9	416.3	416.1
17.5°	408.3	408.7	407.9	410.6	410.5
20°	400.9	401.4	400.8	403.5	403.8
22.5°	392.6	393.4	393.3	396.1	396.9
25°	383.9	384.2	384.6	387.9	388.5
27.5°	374.2	374.7	375.5	378.4	379.0
30°	363.6	364.5	365.3	368.3	369.1
32.5°	352.5	353.3	354.3	358.3	358.7
35°	339.8	341.4	342.8	346.2	347.7
37.5°	327.2	329.2	330.5	334.1	335.3
40°	313.9	315.8	318.0	321.8	322.5
42.5°	300.0	302.2	304.7	308.2	309.4
45°	285.9	288.5	290.8	293.6	295.1
47.5°	270.8	273.3	276.1	279.4	280.3
50°	255.1	258.0	261.1	264.1	265.8
52.5°	239.0	242.6	246.0	249.3	250.8
55°	223.1	225.8	230.0	233.3	234.8
57.5°	206.7	208.9	212.7	218.1	219.0
60°	189.9	191.9	195.8	200.2	202.1
62.5°	171.3	174.1	178.2	183.9	185.5
65°	153.3	156.0	161.4	167.8	170.4
67.5°	135.9	136.9	143.8	150.5	154.8
70°	115.4	118.8	126.9	135.1	138.4
72.5°	97.7	101.1	110.0	119.7	123.7
75°	77.6	82.4	94.4	105.7	109.7
77.5°	60.0	65.3	80.2	91.6	96.2
80°	41.9	50.2	66.3	79.2	84.1
82.5°	26.4	36.5	53.8	67.3	71.6
85°	13.4	24.8	42.6	56.4	61.4
87.5°	3.6	16.1	33.2	46.3	51.4
90°	0.1	9.3	25.1	37.7	42.3
92.5°	0.1	5.2	18.7	30.0	34.7
95°	0.1	2.4	13.0	23.6	27.3
97.5°	0.1	1.0	9.0	17.8	21.5
100°	0.1	0.5	5.7	12.9	16.1
102.5°	0.2	0.3	3.6	9.3	11.8
105°	0.2	0.3	2.1	6.3	8.4
107.5°	0.2	0.3	1.2	4.3	5.8
110°	0.3	0.3	0.7	2.6	3.9

TEST NUMBER: P517893

CATALOG NUMBER: HVL8-2-LD4-1LO-40-UNV-O-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.3	0.3	0.4	1.7	2.5
115°	0.3	0.3	0.4	1.1	1.6
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)