

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517894

Luminaire Tested: HVL8-2-LD4-1LO-40-UNV-O-EDD

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517894
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-2-LD4-1LO-40-UNV-O-EDD
Description: 2 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 4000K, 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1096.0 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 2' x H: 0.17')
CIE Type: Direct


Input Watts (W): 11.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517894

CATALOG NUMBER: HVL8-2-LD4-1LO-40-UNV-O-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P517894

CATALOG NUMBER: HVL8-2-LD4-1LO-40-UNV-O-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		98
1	108	102	98	94	105	100	96	92	95	92	89		91	88	86		81
2	98	89	82	76	95	87	80	75	83	77	73		79	75	71		67
3	89	78	69	63	86	76	68	62	73	66	61		70	64	59		56
4	81	69	60	53	79	67	59	52	65	57	52		62	56	51		47
5	75	61	52	45	72	60	52	45	58	50	44		56	49	44		41
6	69	55	46	40	67	54	46	39	52	45	39		50	44	38		36
7	64	50	41	35	62	49	41	35	47	40	34		46	39	34		32
8	59	46	37	31	58	45	37	31	43	36	31		42	35	30		28
9	55	42	34	28	54	41	33	28	40	33	28		39	32	27		25
10	52	39	31	25	51	38	30	25	37	30	25		36	29	25		23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2926	2926	2926
5°	2910	2854	2864
10°	2880	2796	2806
15°	2845	2733	2738
20°	2807	2663	2671
25°	2764	2592	2603
30°	2716	2517	2525
35°	2658	2435	2449
40°	2596	2349	2360
45°	2530	2256	2263
50°	2447	2150	2160
55°	2357	2033	2045
60°	2250	1885	1912
65°	2087	1719	1779
70°	1861	1527	1626
75°	1551	1316	1486
80°	1111	1108	1359
85°	536	898	1236

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2530 cd/sqm

TEST NUMBER: P517894

CATALOG NUMBER: HVL8-2-LD4-1LO-40-UNV-O-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.3	3.1
10°-20°	98.4	9.0
20°-30°	149.3	13.6
30°-40°	180.5	16.5
40°-50°	188.4	17.2
50°-60°	172.2	15.7
60°-70°	134.3	12.2
70°-80°	84.0	7.7
80°-90°	38.2	3.5
90°-100°	12.8	1.2
100°-110°	3.2	0.3
110°-120°	0.5	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	282.0	25.7
0°-40°	462.5	42.2
0°-60°	823.1	75.1
0°-90°	1079.5	98.5
90°-120°	16.5	1.5
90°-150°	16.5	1.5
90°-180°	17.0	1.6
0°-180°	1096.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	362	362	362	362	362	
5°	362	361	359	361	361	34
15°	348	349	348	350	350	98
25°	322	323	323	326	326	149
35°	285	287	288	291	292	179
45°	240	242	244	247	248	185
55°	187	190	193	196	197	167
65°	129	131	136	141	143	127
75°	65	69	79	89	92	69
85°	11	21	36	47	52	14
90°	0	8	21	32	36	0
95°	0	2	11	20	23	0
105°	0	0	2	5	7	0
115°	0	0	0	1	1	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517894

CATALOG NUMBER: HVL8-2-LD4-1LO-40-UNV-O-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	362.5	362.5	362.5	362.5	362.5
2.5°	362.9	362.4	360.8	362.4	362.3
5°	361.7	361.0	359.4	361.1	361.1
7.5°	359.3	359.1	357.6	359.6	359.6
10°	356.5	356.4	355.2	357.4	357.4
12.5°	352.6	352.9	351.8	353.9	354.1
15°	348.0	348.6	347.6	349.6	349.5
17.5°	342.9	343.3	342.6	344.8	344.7
20°	336.7	337.1	336.6	338.9	339.2
22.5°	329.8	330.4	330.3	332.7	333.4
25°	322.4	322.7	323.0	325.7	326.3
27.5°	314.3	314.7	315.3	317.8	318.3
30°	305.4	306.1	306.8	309.3	310.0
32.5°	296.0	296.7	297.5	300.9	301.2
35°	285.4	286.7	287.9	290.8	292.0
37.5°	274.8	276.4	277.6	280.6	281.6
40°	263.6	265.2	267.0	270.3	270.9
42.5°	251.9	253.8	255.9	258.8	259.9
45°	240.1	242.3	244.2	246.6	247.8
47.5°	227.4	229.5	231.9	234.7	235.4
50°	214.2	216.7	219.3	221.8	223.2
52.5°	200.7	203.7	206.6	209.4	210.6
55°	187.4	189.6	193.1	195.9	197.2
57.5°	173.6	175.4	178.6	183.2	183.9
60°	159.5	161.2	164.4	168.2	169.7
62.5°	143.9	146.2	149.6	154.4	155.8
65°	128.8	131.0	135.5	140.9	143.1
67.5°	114.2	114.9	120.7	126.4	130.0
70°	96.9	99.8	106.6	113.5	116.2
72.5°	82.0	84.9	92.4	100.5	103.9
75°	65.2	69.2	79.3	88.8	92.1
77.5°	50.4	54.9	67.3	76.9	80.8
80°	35.2	42.1	55.7	66.5	70.7
82.5°	22.1	30.7	45.2	56.5	60.2
85°	11.3	20.9	35.8	47.3	51.5
87.5°	3.0	13.5	27.9	38.9	43.2
90°	0.1	7.8	21.1	31.7	35.5
92.5°	0.1	4.4	15.7	25.2	29.1
95°	0.1	2.1	10.9	19.8	22.9
97.5°	0.1	0.9	7.5	15.0	18.0
100°	0.1	0.4	4.8	10.9	13.5
102.5°	0.2	0.3	3.0	7.8	9.9
105°	0.2	0.3	1.8	5.3	7.1
107.5°	0.2	0.3	1.0	3.6	4.9
110°	0.3	0.3	0.6	2.2	3.2

TEST NUMBER: P517894

CATALOG NUMBER: HVL8-2-LD4-1LO-40-UNV-O-EDD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.3	0.3	0.3	1.5	2.1
115°	0.3	0.3	0.3	0.9	1.4
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)