

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517910

Luminaire Tested: HVL8-2-LD4-1STD-40-UNV-O-EDD

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517910
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-2-LD4-1STD-40-UNV-O-EDD
Description: 2 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 4000K, 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1412.0 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 2' x H: 0.17')
CIE Type: Direct


Input Watts (W): 16.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517910

CATALOG NUMBER: HVL8-2-LD4-1STD-40-UNV-O-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P517910

CATALOG NUMBER: HVL8-2-LD4-1STD-40-UNV-O-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			98
1	108	102	98	94	105	100	96	92	95	92	89	91	88	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	77	73	79	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	52	62	56	51	60	54	50			47
5	75	61	52	45	72	60	52	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	40	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3770	3770	3770
5°	3749	3676	3689
10°	3711	3601	3616
15°	3665	3520	3527
20°	3617	3431	3440
25°	3562	3339	3353
30°	3500	3243	3253
35°	3424	3137	3155
40°	3345	3027	3040
45°	3261	2907	2916
50°	3153	2770	2783
55°	3036	2620	2635
60°	2898	2428	2463
65°	2688	2215	2293
70°	2397	1967	2095
75°	1998	1696	1915
80°	1433	1428	1750
85°	688	1156	1594

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3261 cd/sqm

TEST NUMBER: P517910

CATALOG NUMBER: HVL8-2-LD4-1STD-40-UNV-O-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.2	3.1
10°-20°	126.8	9.0
20°-30°	192.3	13.6
30°-40°	232.6	16.5
40°-50°	242.7	17.2
50°-60°	221.9	15.7
60°-70°	173.0	12.2
70°-80°	108.2	7.7
80°-90°	49.1	3.5
90°-100°	16.5	1.2
100°-110°	4.1	0.3
110°-120°	0.6	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	363.3	25.7
0°-40°	595.9	42.2
0°-60°	1060.4	75.1
0°-90°	1390.8	98.5
90°-120°	21.2	1.5
90°-150°	21.2	1.5
90°-180°	21.0	1.5
0°-180°	1412.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	467	467	467	467	467	
5°	466	465	463	465	465	44
15°	448	449	448	450	450	127
25°	415	416	416	420	420	191
35°	368	369	371	375	376	230
45°	309	312	315	318	319	238
55°	241	244	249	252	254	216
65°	166	169	175	182	184	164
75°	84	89	102	114	119	90
85°	14	27	46	61	66	18
90°	0	10	27	41	46	1
95°	0	3	14	26	30	0
105°	0	0	2	7	9	0
115°	0	0	0	1	2	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517910

CATALOG NUMBER: HVL8-2-LD4-1STD-40-UNV-O-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	467.0	467.0	467.0	467.0	467.0
2.5°	467.6	466.9	464.8	466.9	466.8
5°	466.0	465.1	463.0	465.2	465.2
7.5°	462.9	462.6	460.7	463.3	463.3
10°	459.3	459.2	457.6	460.4	460.5
12.5°	454.2	454.7	453.2	455.9	456.2
15°	448.3	449.1	447.8	450.4	450.3
17.5°	441.8	442.2	441.4	444.2	444.1
20°	433.8	434.3	433.6	436.6	436.9
22.5°	424.8	425.6	425.5	428.6	429.5
25°	415.4	415.7	416.1	419.7	420.3
27.5°	404.9	405.5	406.2	409.4	410.1
30°	393.5	394.3	395.2	398.5	399.4
32.5°	381.4	382.2	383.3	387.6	388.1
35°	367.7	369.4	370.9	374.6	376.2
37.5°	354.1	356.1	357.6	361.5	362.7
40°	339.6	341.7	344.0	348.2	349.0
42.5°	324.5	327.0	329.7	333.5	334.8
45°	309.4	312.1	314.6	317.7	319.3
47.5°	293.0	295.7	298.8	302.3	303.3
50°	276.0	279.2	282.5	285.8	287.6
52.5°	258.6	262.5	266.2	269.7	271.4
55°	241.4	244.3	248.8	252.4	254.1
57.5°	223.6	226.0	230.1	236.0	236.9
60°	205.4	207.6	211.8	216.7	218.6
62.5°	185.4	188.4	192.8	198.9	200.7
65°	165.9	168.8	174.6	181.5	184.4
67.5°	147.1	148.1	155.6	162.8	167.4
70°	124.8	128.6	137.3	146.2	149.7
72.5°	105.7	109.4	119.0	129.5	133.9
75°	84.0	89.2	102.2	114.4	118.7
77.5°	65.0	70.7	86.8	99.1	104.0
80°	45.4	54.3	71.8	85.7	91.0
82.5°	28.5	39.5	58.2	72.8	77.5
85°	14.5	26.9	46.1	61.0	66.4
87.5°	3.9	17.4	35.9	50.1	55.6
90°	0.1	10.0	27.2	40.8	45.8
92.5°	0.1	5.6	20.3	32.5	37.5
95°	0.1	2.6	14.1	25.5	29.5
97.5°	0.1	1.1	9.7	19.3	23.2
100°	0.1	0.6	6.2	14.0	17.4
102.5°	0.2	0.3	3.9	10.0	12.8
105°	0.2	0.3	2.3	6.8	9.1
107.5°	0.2	0.3	1.3	4.6	6.3
110°	0.3	0.3	0.8	2.9	4.2

TEST NUMBER: P517910

CATALOG NUMBER: HVL8-2-LD4-1STD-40-UNV-O-EDD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.3	0.3	0.4	1.9	2.8
115°	0.3	0.3	0.4	1.2	1.8
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)