

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517929

Luminaire Tested: HVL8-2-LD4-2HI-50-UNV-O-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517929
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-2-LD4-2HI-50-UNV-O-EDD-90
Description: 2 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 5000K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3634.1 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 2' x H: 0.17')
CIE Type: Direct


Input Watts (W): 43.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517929

CATALOG NUMBER: HVL8-2-LD4-2HI-50-UNV-O-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P517929

CATALOG NUMBER: HVL8-2-LD4-2HI-50-UNV-O-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			98
1	108	102	98	94	105	100	96	92	95	92	89	91	88	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	77	73	79	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	52	62	56	51	60	54	50			47
5	75	61	52	45	72	60	52	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	40	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9703	9703	9703
5°	9649	9462	9496
10°	9550	9270	9305
15°	9432	9061	9077
20°	9308	8831	8856
25°	9166	8595	8630
30°	9006	8346	8373
35°	8812	8075	8120
40°	8610	7790	7824
45°	8391	7482	7505
50°	8115	7128	7161
55°	7816	6742	6782
60°	7459	6249	6340
65°	6920	5702	5901
70°	6171	5061	5391
75°	5144	4362	4928
80°	3684	3674	4505
85°	1774	2976	4103

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8391 cd/sqm

TEST NUMBER: P517929

CATALOG NUMBER: HVL8-2-LD4-2HI-50-UNV-O-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.7	3.1
10°-20°	326.3	9.0
20°-30°	495.0	13.6
30°-40°	598.6	16.5
40°-50°	624.6	17.2
50°-60°	571.0	15.7
60°-70°	445.2	12.2
70°-80°	278.5	7.7
80°-90°	126.5	3.5
90°-100°	42.4	1.2
100°-110°	10.7	0.3
110°-120°	1.7	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	935.0	25.7
0°-40°	1533.6	42.2
0°-60°	2729.2	75.1
0°-90°	3579.3	98.5
90°-120°	54.7	1.5
90°-150°	54.7	1.5
90°-180°	55.0	1.5
0°-180°	3634.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1202	1202	1202	1202	1202	
5°	1199	1197	1192	1197	1197	114
15°	1154	1156	1153	1159	1159	326
25°	1069	1070	1071	1080	1082	493
35°	946	951	955	964	968	592
45°	796	803	810	818	822	614
55°	621	629	640	650	654	555
65°	427	434	449	467	475	422
75°	216	230	263	294	305	230
85°	37	69	119	157	171	47
90°	0	26	70	105	118	1
95°	0	7	36	66	76	0
105°	1	1	6	18	24	1
115°	1	1	1	3	4	1
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517929

CATALOG NUMBER: HVL8-2-LD4-2HI-50-UNV-O-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1201.9	1201.9	1201.9	1201.9	1201.9
2.5°	1203.3	1201.6	1196.2	1201.6	1201.3
5°	1199.4	1197.1	1191.7	1197.4	1197.4
7.5°	1191.4	1190.6	1185.8	1192.3	1192.3
10°	1182.1	1181.8	1177.8	1184.9	1185.2
12.5°	1169.0	1170.2	1166.5	1173.3	1174.1
15°	1153.7	1155.7	1152.6	1159.1	1158.8
17.5°	1137.0	1138.2	1135.9	1143.3	1143.0
20°	1116.3	1117.8	1116.1	1123.7	1124.6
22.5°	1093.4	1095.4	1095.1	1103.0	1105.3
25°	1069.0	1069.9	1071.0	1080.1	1081.8
27.5°	1042.1	1043.5	1045.5	1053.7	1055.4
30°	1012.6	1014.9	1017.2	1025.7	1027.9
32.5°	981.5	983.7	986.6	997.6	998.8
35°	946.3	950.6	954.6	964.2	968.2
37.5°	911.2	916.6	920.3	930.5	933.6
40°	874.1	879.5	885.4	896.2	898.2
42.5°	835.3	841.5	848.6	858.2	861.6
45°	796.2	803.3	809.8	817.7	821.7
47.5°	754.0	761.0	769.0	778.0	780.6
50°	710.3	718.5	727.0	735.5	740.1
52.5°	665.6	675.5	685.1	694.2	698.4
55°	621.4	628.7	640.3	649.7	653.9
57.5°	575.5	581.7	592.2	607.5	609.7
60°	528.7	534.4	545.1	557.6	562.7
62.5°	477.1	484.8	496.1	512.0	516.5
65°	427.0	434.4	449.4	467.2	474.6
67.5°	378.5	381.1	400.4	419.1	431.0
70°	321.3	330.9	353.3	376.3	385.3
72.5°	272.0	281.6	306.3	333.2	344.5
75°	216.2	229.5	262.9	294.4	305.4
77.5°	167.2	181.9	223.3	255.0	267.8
80°	116.7	139.7	184.7	220.4	234.3
82.5°	73.4	101.7	149.9	187.3	199.5
85°	37.4	69.1	118.7	157.0	170.9
87.5°	9.9	44.8	92.4	128.9	143.1
90°	0.3	25.8	70.0	105.1	117.9
92.5°	0.3	14.5	52.1	83.6	96.6
95°	0.3	6.8	36.3	65.7	75.9
97.5°	0.3	2.8	24.9	49.6	59.8
100°	0.3	1.4	15.9	36.0	44.8
102.5°	0.6	0.9	9.9	25.8	32.9
105°	0.6	0.9	6.0	17.6	23.5
107.5°	0.6	0.9	3.4	11.9	16.2
110°	0.9	0.9	2.0	7.4	10.8

TEST NUMBER: P517929

CATALOG NUMBER: HVL8-2-LD4-2HI-50-UNV-O-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.9	0.9	1.1	4.8	7.1
115°	0.9	0.9	1.1	3.1	4.5
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)