

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517753

Luminaire Tested: HVL8-1-LD4-1LO-50-UNV-O-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517753
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-1-LD4-1LO-50-UNV-O-EDD-90
Description: 1 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 5000K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 663.0 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 1' x H: 0.17')
CIE Type: Direct


Input Watts (W): 5.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517753

CATALOG NUMBER: HVL8-1-LD4-1LO-50-UNV-O-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P517753

CATALOG NUMBER: HVL8-1-LD4-1LO-50-UNV-O-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			98
1	108	102	98	94	105	100	96	92	95	92	89	91	88	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	77	73	79	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	52	62	56	51	60	54	50			47
5	75	61	52	45	72	60	52	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	40	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3541	3541	3541
5°	3495	3435	3466
10°	3435	3349	3395
15°	3368	3258	3312
20°	3300	3159	3232
25°	3223	3060	3149
30°	3141	2957	3055
35°	3048	2846	2962
40°	2949	2729	2855
45°	2844	2605	2738
50°	2716	2465	2612
55°	2578	2314	2475
60°	2418	2127	2314
65°	2192	1920	2154
70°	1897	1683	1967
75°	1515	1426	1797
80°	1018	1173	1642
85°	434	920	1498

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2844 cd/sqm

TEST NUMBER: P517753

CATALOG NUMBER: HVL8-1-LD4-1LO-50-UNV-O-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.8	3.1
10°-20°	59.5	9.0
20°-30°	90.3	13.6
30°-40°	109.2	16.5
40°-50°	113.9	17.2
50°-60°	104.2	15.7
60°-70°	81.2	12.2
70°-80°	50.8	7.7
80°-90°	23.1	3.5
90°-100°	7.7	1.2
100°-110°	2.0	0.3
110°-120°	0.3	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	170.6	25.7
0°-40°	279.8	42.2
0°-60°	497.9	75.1
0°-90°	653.0	98.5
90°-120°	10.0	1.5
90°-150°	10.0	1.5
90°-180°	10.0	1.5
0°-180°	663.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	219	219	219	219	219	
5°	219	218	217	218	218	21
15°	210	211	210	212	211	59
25°	195	195	195	197	197	90
35°	173	173	174	176	177	108
45°	145	146	148	149	150	112
55°	113	115	117	118	119	101
65°	78	79	82	85	87	77
75°	39	42	48	54	56	42
85°	7	13	22	29	31	9
90°	0	5	13	19	22	0
95°	0	1	7	12	14	0
105°	0	0	1	3	4	0
115°	0	0	0	1	1	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517753

CATALOG NUMBER: HVL8-1-LD4-1LO-50-UNV-O-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	219.3	219.3	219.3	219.3	219.3
2.5°	219.5	219.2	218.2	219.2	219.2
5°	218.8	218.4	217.4	218.5	218.5
7.5°	217.4	217.2	216.3	217.5	217.5
10°	215.7	215.6	214.9	216.2	216.2
12.5°	213.3	213.5	212.8	214.1	214.2
15°	210.5	210.9	210.3	211.5	211.4
17.5°	207.4	207.6	207.2	208.6	208.5
20°	203.7	203.9	203.6	205.0	205.2
22.5°	199.5	199.8	199.8	201.2	201.7
25°	195.0	195.2	195.4	197.1	197.4
27.5°	190.1	190.4	190.7	192.2	192.6
30°	184.7	185.2	185.6	187.1	187.5
32.5°	179.1	179.5	180.0	182.0	182.2
35°	172.7	173.4	174.2	175.9	176.6
37.5°	166.2	167.2	167.9	169.8	170.3
40°	159.5	160.5	161.5	163.5	163.9
42.5°	152.4	153.5	154.8	156.6	157.2
45°	145.3	146.5	147.7	149.2	149.9
47.5°	137.6	138.8	140.3	141.9	142.4
50°	129.6	131.1	132.6	134.2	135.0
52.5°	121.4	123.2	125.0	126.6	127.4
55°	113.4	114.7	116.8	118.5	119.3
57.5°	105.0	106.1	108.0	110.8	111.2
60°	96.5	97.5	99.5	101.7	102.7
62.5°	87.1	88.4	90.5	93.4	94.2
65°	77.9	79.2	82.0	85.2	86.6
67.5°	69.1	69.5	73.0	76.5	78.6
70°	58.6	60.4	64.5	68.6	70.3
72.5°	49.6	51.4	55.9	60.8	62.9
75°	39.4	41.9	48.0	53.7	55.7
77.5°	30.5	33.2	40.7	46.5	48.8
80°	21.3	25.5	33.7	40.2	42.7
82.5°	13.4	18.6	27.3	34.2	36.4
85°	6.8	12.6	21.7	28.6	31.2
87.5°	1.8	8.2	16.9	23.5	26.1
90°	0.1	4.7	12.8	19.2	21.5
92.5°	0.1	2.6	9.5	15.2	17.6
95°	0.1	1.2	6.6	12.0	13.9
97.5°	0.1	0.5	4.5	9.0	10.9
100°	0.1	0.3	2.9	6.6	8.2
102.5°	0.1	0.2	1.8	4.7	6.0
105°	0.1	0.2	1.1	3.2	4.3
107.5°	0.1	0.2	0.6	2.2	2.9
110°	0.2	0.2	0.4	1.3	2.0

TEST NUMBER: P517753

CATALOG NUMBER: HVL8-1-LD4-1LO-50-UNV-O-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.2	0.2	0.2	0.9	1.3
115°	0.2	0.2	0.2	0.6	0.8
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)