

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517866

Luminaire Tested: HVL8-1-LD4-3STD-50-UNV-O-EDD

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517866
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-1-LD4-3STD-50-UNV-O-EDD
Description: 1 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 5000K, 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2559.0 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 1' x H: 0.17')
CIE Type: Direct


Input Watts (W): 23.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517866

CATALOG NUMBER: HVL8-1-LD4-3STD-50-UNV-O-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P517866

CATALOG NUMBER: HVL8-1-LD4-3STD-50-UNV-O-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			98
1	108	102	98	94	105	100	96	92	95	92	89	91	88	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	77	73	79	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	52	62	56	51	60	54	50			47
5	75	61	52	45	72	60	52	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	40	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13666	13666	13666
5°	13492	13260	13374
10°	13257	12926	13105
15°	12999	12573	12783
20°	12734	12195	12471
25°	12444	11813	12154
30°	12128	11413	11794
35°	11762	10983	11436
40°	11381	10536	11019
45°	10974	10056	10569
50°	10482	9518	10084
55°	9947	8933	9552
60°	9329	8208	8927
65°	8463	7407	8311
70°	7327	6490	7592
75°	5853	5502	6941
80°	3929	4528	6345
85°	1677	3545	5776

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10974 cd/sqm

TEST NUMBER: P517866

CATALOG NUMBER: HVL8-1-LD4-3STD-50-UNV-O-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.1	3.1
10°-20°	229.7	9.0
20°-30°	348.6	13.6
30°-40°	421.5	16.5
40°-50°	439.8	17.2
50°-60°	402.1	15.7
60°-70°	313.5	12.2
70°-80°	196.1	7.7
80°-90°	89.1	3.5
90°-100°	29.9	1.2
100°-110°	7.5	0.3
110°-120°	1.2	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	658.4	25.7
0°-40°	1079.9	42.2
0°-60°	1921.8	75.1
0°-90°	2520.5	98.5
90°-120°	38.5	1.5
90°-150°	38.5	1.5
90°-180°	39.0	1.5
0°-180°	2559.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	846	846	846	846	846	
5°	845	843	839	843	843	80
15°	812	814	812	816	816	229
25°	753	753	754	761	762	347
35°	666	669	672	679	682	417
45°	561	566	570	576	579	432
55°	438	443	451	458	460	391
65°	301	306	316	329	334	298
75°	152	162	185	207	215	162
85°	26	49	84	110	120	33
90°	0	18	49	74	83	1
95°	0	5	26	46	54	0
105°	0	1	4	12	17	0
115°	1	1	1	2	3	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517866

CATALOG NUMBER: HVL8-1-LD4-3STD-50-UNV-O-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	846.4	846.4	846.4	846.4	846.4
2.5°	847.4	846.2	842.4	846.2	846.0
5°	844.6	843.0	839.2	843.2	843.2
7.5°	839.0	838.4	835.0	839.6	839.6
10°	832.4	832.2	829.4	834.4	834.6
12.5°	823.2	824.0	821.4	826.2	826.8
15°	812.4	813.8	811.6	816.2	816.0
17.5°	800.7	801.5	799.9	805.1	804.9
20°	786.1	787.1	785.9	791.3	791.9
22.5°	769.9	771.3	771.1	776.7	778.3
25°	752.8	753.4	754.2	760.6	761.8
27.5°	733.8	734.8	736.2	742.0	743.2
30°	713.1	714.7	716.3	722.3	723.9
32.5°	691.1	692.7	694.7	702.5	703.3
35°	666.4	669.4	672.2	679.0	681.8
37.5°	641.7	645.4	648.0	655.2	657.4
40°	615.5	619.3	623.5	631.1	632.5
42.5°	588.2	592.6	597.6	604.3	606.7
45°	560.7	565.6	570.2	575.8	578.6
47.5°	530.9	535.9	541.5	547.9	549.7
50°	500.2	506.0	512.0	518.0	521.1
52.5°	468.7	475.7	482.4	488.8	491.8
55°	437.5	442.7	450.9	457.5	460.5
57.5°	405.2	409.6	417.0	427.8	429.4
60°	372.3	376.3	383.9	392.7	396.2
62.5°	336.0	341.4	349.4	360.5	363.7
65°	300.7	305.9	316.4	329.0	334.2
67.5°	266.6	268.4	281.9	295.1	303.5
70°	226.3	233.0	248.8	265.0	271.3
72.5°	191.5	198.3	215.7	234.6	242.6
75°	152.2	161.6	185.2	207.3	215.1
77.5°	117.7	128.1	157.2	179.6	188.5
80°	82.2	98.4	130.1	155.2	165.0
82.5°	51.7	71.6	105.5	131.9	140.5
85°	26.3	48.7	83.6	110.5	120.3
87.5°	7.0	31.5	65.0	90.8	100.8
90°	0.2	18.2	49.3	74.0	83.0
92.5°	0.2	10.2	36.7	58.9	68.0
95°	0.2	4.8	25.5	46.3	53.5
97.5°	0.2	2.0	17.6	34.9	42.1
100°	0.2	1.0	11.2	25.3	31.5
102.5°	0.4	0.6	7.0	18.2	23.1
105°	0.4	0.6	4.2	12.4	16.6
107.5°	0.4	0.6	2.4	8.4	11.4
110°	0.6	0.6	1.4	5.2	7.6

TEST NUMBER: P517866

CATALOG NUMBER: HVL8-1-LD4-3STD-50-UNV-O-EDD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.6	0.6	0.8	3.4	5.0
115°	0.6	0.6	0.8	2.2	3.2
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)