

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517926

Luminaire Tested: HVL8-2-LD4-2HI-40-UNV-O-EDD

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517926
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-2-LD4-2HI-40-UNV-O-EDD
Description: 2 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 4000K, 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3451.0 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 2' x H: 0.17')
CIE Type: Direct


Input Watts (W): 43.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517926

CATALOG NUMBER: HVL8-2-LD4-2HI-40-UNV-O-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P517926

CATALOG NUMBER: HVL8-2-LD4-2HI-40-UNV-O-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			98
1	108	102	98	94	105	100	96	92	95	92	89	91	88	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	77	73	79	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	52	62	56	51	60	54	50			47
5	75	61	52	45	72	60	52	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	40	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9214	9214	9214
5°	9163	8986	9018
10°	9068	8803	8837
15°	8957	8605	8620
20°	8839	8386	8409
25°	8705	8162	8195
30°	8552	7926	7952
35°	8368	7668	7711
40°	8176	7397	7429
45°	7968	7105	7127
50°	7707	6769	6800
55°	7422	6403	6440
60°	7084	5935	6021
65°	6571	5414	5604
70°	5860	4806	5119
75°	4884	4143	4681
80°	3501	3489	4278
85°	1684	2825	3894

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7968 cd/sqm

TEST NUMBER: P517926

CATALOG NUMBER: HVL8-2-LD4-2HI-40-UNV-O-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.0	3.1
10°-20°	309.8	9.0
20°-30°	470.1	13.6
30°-40°	568.4	16.5
40°-50°	593.1	17.2
50°-60°	542.3	15.7
60°-70°	422.7	12.2
70°-80°	264.4	7.7
80°-90°	120.1	3.5
90°-100°	40.3	1.2
100°-110°	10.1	0.3
110°-120°	1.6	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	887.9	25.7
0°-40°	1456.4	42.2
0°-60°	2591.8	75.1
0°-90°	3399.1	98.5
90°-120°	52.0	1.5
90°-150°	52.0	1.5
90°-180°	52.0	1.5
0°-180°	3451.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1141	1141	1141	1141	1141	
5°	1139	1137	1132	1137	1137	108
15°	1096	1098	1095	1101	1100	309
25°	1015	1016	1017	1026	1027	468
35°	899	903	906	916	919	562
45°	756	763	769	776	780	583
55°	590	597	608	617	621	527
65°	406	412	427	444	451	401
75°	205	218	250	280	290	219
85°	36	66	113	149	162	45
90°	0	24	66	100	112	1
95°	0	6	34	62	72	0
105°	0	1	6	17	22	1
115°	1	1	1	3	4	1
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517926

CATALOG NUMBER: HVL8-2-LD4-2HI-40-UNV-O-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1141.4	1141.4	1141.4	1141.4	1141.4
2.5°	1142.7	1141.1	1136.0	1141.1	1140.8
5°	1139.0	1136.8	1131.7	1137.1	1137.1
7.5°	1131.4	1130.6	1126.0	1132.2	1132.2
10°	1122.5	1122.3	1118.5	1125.2	1125.5
12.5°	1110.2	1111.2	1107.7	1114.2	1115.0
15°	1095.6	1097.5	1094.6	1100.8	1100.5
17.5°	1079.8	1080.8	1078.7	1085.7	1085.4
20°	1060.1	1061.5	1059.9	1067.1	1067.9
22.5°	1038.3	1040.2	1039.9	1047.5	1049.6
25°	1015.2	1016.0	1017.1	1025.7	1027.3
27.5°	989.6	991.0	992.9	1000.7	1002.3
30°	961.6	963.8	966.0	974.0	976.2
32.5°	932.0	934.2	936.9	947.4	948.5
35°	898.7	902.7	906.5	915.6	919.4
37.5°	865.3	870.4	873.9	883.6	886.6
40°	830.1	835.2	840.8	851.1	852.9
42.5°	793.2	799.1	805.9	815.0	818.2
45°	756.1	762.8	769.0	776.5	780.3
47.5°	716.0	722.7	730.2	738.9	741.3
50°	674.6	682.4	690.4	698.5	702.8
52.5°	632.0	641.5	650.6	659.2	663.3
55°	590.1	597.1	608.1	617.0	621.0
57.5°	546.5	552.4	562.4	576.9	579.0
60°	502.1	507.5	517.7	529.5	534.4
62.5°	453.1	460.4	471.1	486.2	490.5
65°	405.5	412.5	426.7	443.7	450.7
67.5°	359.5	361.9	380.2	398.0	409.3
70°	305.1	314.3	335.5	357.3	365.9
72.5°	258.3	267.5	290.9	316.4	327.2
75°	205.3	217.9	249.7	279.6	290.1
77.5°	158.7	172.7	212.0	242.2	254.3
80°	110.9	132.7	175.4	209.3	222.5
82.5°	69.7	96.6	142.3	177.9	189.4
85°	35.5	65.7	112.7	149.1	162.2
87.5°	9.4	42.5	87.7	122.4	135.9
90°	0.3	24.5	66.5	99.8	111.9
92.5°	0.3	13.7	49.5	79.4	91.8
95°	0.3	6.5	34.4	62.4	72.1
97.5°	0.3	2.7	23.7	47.1	56.8
100°	0.3	1.3	15.1	34.2	42.5
102.5°	0.5	0.8	9.4	24.5	31.2
105°	0.5	0.8	5.7	16.7	22.3
107.5°	0.5	0.8	3.2	11.3	15.3
110°	0.8	0.8	1.9	7.0	10.2

TEST NUMBER: P517926

CATALOG NUMBER: HVL8-2-LD4-2HI-40-UNV-O-EDD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.8	0.8	1.1	4.6	6.7
115°	0.8	0.8	1.1	3.0	4.3
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)