

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517949

Luminaire Tested: HVL8-2-LD4-2STD-30-UNV-O-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517949
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-2-LD4-2STD-30-UNV-O-EDD-90
Description: 2 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 3000K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2609.0 lumens
Efficiency: N/A
Efficacy: 79.8 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 2' x H: 0.17')
CIE Type: Direct


Input Watts (W): 32.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517949

CATALOG NUMBER: HVL8-2-LD4-2STD-30-UNV-O-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P517949

CATALOG NUMBER: HVL8-2-LD4-2STD-30-UNV-O-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			98
1	108	102	98	94	105	100	96	92	95	92	89	91	88	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	77	73	79	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	52	62	56	51	60	54	50			47
5	75	61	52	45	72	60	52	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	40	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6966	6966	6966
5°	6928	6793	6817
10°	6856	6655	6681
15°	6771	6505	6517
20°	6683	6340	6358
25°	6581	6171	6196
30°	6466	5992	6012
35°	6326	5797	5830
40°	6181	5593	5617
45°	6024	5371	5388
50°	5826	5118	5141
55°	5611	4840	4869
60°	5356	4487	4552
65°	4969	4093	4236
70°	4431	3634	3870
75°	3692	3133	3538
80°	2645	2638	3234
85°	1276	2136	2946

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6024 cd/sqm

TEST NUMBER: P517949

CATALOG NUMBER: HVL8-2-LD4-2STD-30-UNV-O-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.7	3.1
10°-20°	234.2	9.0
20°-30°	355.4	13.6
30°-40°	429.7	16.5
40°-50°	448.4	17.2
50°-60°	410.0	15.7
60°-70°	319.6	12.2
70°-80°	199.9	7.7
80°-90°	90.8	3.5
90°-100°	30.4	1.2
100°-110°	7.6	0.3
110°-120°	1.2	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	671.3	25.7
0°-40°	1101.0	42.2
0°-60°	1959.4	75.1
0°-90°	2569.7	98.5
90°-120°	39.3	1.5
90°-150°	39.3	1.5
90°-180°	39.0	1.5
0°-180°	2609.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	863	863	863	863	863	
5°	861	859	856	860	860	82
15°	828	830	828	832	832	234
25°	768	768	769	775	777	354
35°	679	682	685	692	695	425
45°	572	577	581	587	590	440
55°	446	451	460	466	470	399
65°	307	312	323	335	341	303
75°	155	165	189	211	219	165
85°	27	50	85	113	123	34
90°	0	18	50	76	85	1
95°	0	5	26	47	54	0
105°	0	1	4	13	17	0
115°	1	1	1	2	3	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517949

CATALOG NUMBER: HVL8-2-LD4-2STD-30-UNV-O-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	862.9	862.9	862.9	862.9	862.9
2.5°	863.9	862.7	858.8	862.7	862.5
5°	861.1	859.4	855.6	859.6	859.6
7.5°	855.4	854.8	851.3	856.0	856.0
10°	848.7	848.5	845.6	850.7	850.9
12.5°	839.3	840.1	837.5	842.4	843.0
15°	828.3	829.7	827.5	832.2	832.0
17.5°	816.3	817.1	815.5	820.8	820.6
20°	801.5	802.5	801.3	806.8	807.4
22.5°	785.0	786.4	786.2	791.9	793.5
25°	767.5	768.1	768.9	775.4	776.7
27.5°	748.2	749.2	750.6	756.5	757.7
30°	727.0	728.6	730.3	736.4	738.0
32.5°	704.6	706.3	708.3	716.2	717.0
35°	679.4	682.5	685.3	692.2	695.1
37.5°	654.2	658.1	660.7	668.0	670.3
40°	627.5	631.4	635.7	643.4	644.8
42.5°	599.7	604.2	609.2	616.2	618.6
45°	571.6	576.7	581.4	587.1	589.9
47.5°	541.3	546.4	552.1	558.6	560.4
50°	510.0	515.9	522.0	528.1	531.3
52.5°	477.8	484.9	491.9	498.4	501.4
55°	446.1	451.4	459.7	466.4	469.5
57.5°	413.1	417.6	425.1	436.1	437.8
60°	379.6	383.6	391.4	400.3	404.0
62.5°	342.6	348.0	356.2	367.6	370.8
65°	306.6	311.8	322.6	335.4	340.7
67.5°	271.8	273.6	287.4	300.9	309.4
70°	230.7	237.6	253.7	270.1	276.6
72.5°	195.3	202.2	219.9	239.2	247.4
75°	155.2	164.8	188.8	211.4	219.3
77.5°	120.0	130.6	160.3	183.1	192.2
80°	83.8	100.3	132.6	158.3	168.2
82.5°	52.7	73.0	107.6	134.5	143.2
85°	26.9	49.6	85.2	112.7	122.7
87.5°	7.1	32.1	66.3	92.6	102.7
90°	0.2	18.5	50.2	75.5	84.6
92.5°	0.2	10.4	37.4	60.0	69.4
95°	0.2	4.9	26.0	47.2	54.5
97.5°	0.2	2.0	17.9	35.6	42.9
100°	0.2	1.0	11.4	25.8	32.1
102.5°	0.4	0.6	7.1	18.5	23.6
105°	0.4	0.6	4.3	12.6	16.9
107.5°	0.4	0.6	2.4	8.5	11.6
110°	0.6	0.6	1.4	5.3	7.7

TEST NUMBER: P517949

CATALOG NUMBER: HVL8-2-LD4-2STD-30-UNV-O-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.6	0.6	0.8	3.5	5.1
115°	0.6	0.6	0.8	2.2	3.3
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)