

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P517961

Luminaire Tested: HVL8-2-LD4-2STD-50-UNV-O-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P517961
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-2-LD4-2STD-50-UNV-O-EDD-90
Description: 2 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 5000K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2824.0 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 2' x H: 0.17')
CIE Type: Direct


Input Watts (W): 32.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P517961

CATALOG NUMBER: HVL8-2-LD4-2STD-50-UNV-O-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P517961

CATALOG NUMBER: HVL8-2-LD4-2STD-50-UNV-O-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			98
1	108	102	98	94	105	100	96	92	95	92	89	91	88	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	77	73	79	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	52	62	56	51	60	54	50			47
5	75	61	52	45	72	60	52	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	40	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7540	7540	7540
5°	7498	7353	7379
10°	7421	7204	7231
15°	7330	7041	7054
20°	7233	6862	6881
25°	7123	6679	6707
30°	6999	6486	6507
35°	6848	6275	6310
40°	6691	6054	6080
45°	6520	5814	5831
50°	6306	5540	5565
55°	6074	5240	5271
60°	5797	4856	4927
65°	5377	4431	4586
70°	4796	3934	4189
75°	3997	3390	3830
80°	2863	2857	3501
85°	1380	2314	3188

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6520 cd/sqm

TEST NUMBER: P517961

CATALOG NUMBER: HVL8-2-LD4-2STD-50-UNV-O-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	3.1
10°-20°	253.5	9.0
20°-30°	384.7	13.6
30°-40°	465.2	16.5
40°-50°	485.3	17.2
50°-60°	443.8	15.7
60°-70°	345.9	12.2
70°-80°	216.4	7.7
80°-90°	98.3	3.5
90°-100°	32.9	1.2
100°-110°	8.3	0.3
110°-120°	1.3	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	726.6	25.7
0°-40°	1191.8	42.2
0°-60°	2120.9	75.1
0°-90°	2781.5	98.5
90°-120°	42.5	1.5
90°-150°	42.5	1.5
90°-180°	43.0	1.5
0°-180°	2824.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	934	934	934	934	934	
5°	932	930	926	930	930	89
15°	897	898	896	901	900	253
25°	831	831	832	839	841	383
35°	735	739	742	749	752	460
45°	619	624	629	635	638	477
55°	483	489	498	505	508	431
65°	332	338	349	363	369	328
75°	168	178	204	229	237	179
85°	29	54	92	122	133	37
90°	0	20	54	82	92	1
95°	0	5	28	51	59	0
105°	0	1	5	14	18	0
115°	1	1	1	2	4	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P517961

CATALOG NUMBER: HVL8-2-LD4-2STD-50-UNV-O-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	934.0	934.0	934.0	934.0	934.0
2.5°	935.1	933.8	929.6	933.8	933.6
5°	932.0	930.3	926.1	930.5	930.5
7.5°	925.9	925.2	921.5	926.5	926.5
10°	918.6	918.4	915.3	920.8	921.0
12.5°	908.5	909.3	906.5	911.8	912.4
15°	896.6	898.1	895.7	900.8	900.5
17.5°	883.6	884.5	882.7	888.4	888.2
20°	867.5	868.6	867.3	873.2	873.9
22.5°	849.7	851.2	851.0	857.2	858.9
25°	830.7	831.4	832.3	839.3	840.7
27.5°	809.8	810.9	812.5	818.9	820.2
30°	786.9	788.7	790.5	797.1	798.8
32.5°	762.7	764.5	766.7	775.3	776.1
35°	735.4	738.7	741.8	749.3	752.4
37.5°	708.1	712.3	715.1	723.1	725.5
40°	679.3	683.4	688.1	696.4	698.0
42.5°	649.1	653.9	659.4	666.9	669.6
45°	618.7	624.2	629.3	635.4	638.5
47.5°	585.9	591.4	597.6	604.6	606.6
50°	552.0	558.4	565.0	571.6	575.1
52.5°	517.2	524.9	532.4	539.4	542.7
55°	482.9	488.6	497.6	504.9	508.2
57.5°	447.2	452.0	460.2	472.1	473.8
60°	410.9	415.3	423.6	433.3	437.3
62.5°	370.8	376.7	385.5	397.9	401.4
65°	331.8	337.5	349.2	363.1	368.8
67.5°	294.2	296.1	311.1	325.6	334.9
70°	249.7	257.2	274.6	292.4	299.4
72.5°	211.4	218.9	238.0	258.9	267.7
75°	168.0	178.3	204.3	228.8	237.4
77.5°	129.9	141.4	173.5	198.2	208.1
80°	90.7	108.5	143.6	171.3	182.1
82.5°	57.0	79.0	116.5	145.5	155.0
85°	29.1	53.7	92.3	122.0	132.8
87.5°	7.7	34.8	71.8	100.2	111.2
90°	0.2	20.0	54.4	81.7	91.6
92.5°	0.2	11.2	40.5	65.0	75.1
95°	0.2	5.3	28.2	51.1	59.0
97.5°	0.2	2.2	19.4	38.5	46.5
100°	0.2	1.1	12.3	28.0	34.8
102.5°	0.4	0.7	7.7	20.0	25.5
105°	0.4	0.7	4.6	13.7	18.3
107.5°	0.4	0.7	2.6	9.2	12.6
110°	0.7	0.7	1.5	5.7	8.4

TEST NUMBER: P517961

CATALOG NUMBER: HVL8-2-LD4-2STD-50-UNV-O-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.7	0.7	0.9	3.7	5.5
115°	0.7	0.7	0.9	2.4	3.5
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)