

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P518070

Luminaire Tested: HVL8-4-LD4-2HI-40-UNV-O-EDD

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P518070
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-4-LD4-2HI-40-UNV-O-EDD
Description: 4 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 4000K, 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6902.0 lumens
Efficiency: N/A
Efficacy: 80.2 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 4' x H: 0.17')
CIE Type: Direct

Input Watts (W): 86.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P518070
CATALOG NUMBER: HVL8-4-LD4-2HI-40-UNV-O-EDD

Luminous Intensity Polar Plot



TEST NUMBER: P518070

CATALOG NUMBER: HVL8-4-LD4-2HI-40-UNV-O-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			98
1	108	102	98	94	105	100	96	92	95	92	89	91	88	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	77	73	79	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	52	62	56	51	60	54	50			47
5	75	61	52	45	72	60	52	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	40	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9214	9214	9214
5°	9196	9008	9018
10°	9135	8847	8837
15°	9056	8669	8620
20°	8971	8469	8409
25°	8871	8264	8195
30°	8754	8046	7952
35°	8606	7806	7711
40°	8452	7554	7430
45°	8287	7278	7127
50°	8071	6960	6800
55°	7838	6611	6440
60°	7561	6158	6020
65°	7110	5652	5604
70°	6462	5055	5120
75°	5542	4401	4680
80°	4168	3759	4278
85°	2227	3110	3895

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8287 cd/sqm

TEST NUMBER: P518070

CATALOG NUMBER: HVL8-4-LD4-2HI-40-UNV-O-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.0	3.1
10°-20°	619.6	9.0
20°-30°	940.2	13.6
30°-40°	1136.9	16.5
40°-50°	1186.2	17.2
50°-60°	1084.6	15.7
60°-70°	845.5	12.2
70°-80°	528.9	7.7
80°-90°	240.2	3.5
90°-100°	80.5	1.2
100°-110°	20.2	0.3
110°-120°	3.2	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1775.9	25.7
0°-40°	2912.7	42.2
0°-60°	5183.5	75.1
0°-90°	6798.1	98.5
90°-120°	103.9	1.5
90°-150°	103.9	1.5
90°-180°	104.0	1.5
0°-180°	6902.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2283	2283	2283	2283	2283	
5°	2278	2274	2263	2274	2274	216
15°	2191	2195	2189	2202	2201	619
25°	2030	2032	2034	2051	2055	936
35°	1797	1805	1813	1831	1839	1125
45°	1512	1526	1538	1553	1561	1165
55°	1180	1194	1216	1234	1242	1054
65°	811	825	854	887	901	802
75°	411	436	499	559	580	438
85°	71	131	226	298	324	90
90°	0	49	133	200	224	3
95°	0	13	69	125	144	0
105°	1	2	11	33	45	1
115°	2	2	2	6	9	1
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P518070

CATALOG NUMBER: HVL8-4-LD4-2HI-40-UNV-O-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2282.8	2282.8	2282.8	2282.8	2282.8
2.5°	2285.5	2282.2	2272.0	2282.2	2281.7
5°	2277.9	2273.6	2263.4	2274.2	2274.2
7.5°	2262.9	2261.2	2252.1	2264.5	2264.5
10°	2245.1	2244.6	2237.0	2250.5	2251.0
12.5°	2220.3	2222.5	2215.5	2228.4	2230.0
15°	2191.3	2195.0	2189.1	2201.5	2201.0
17.5°	2159.5	2161.7	2157.4	2171.4	2170.8
20°	2120.2	2122.9	2119.7	2134.2	2135.9
22.5°	2076.7	2080.4	2079.9	2095.0	2099.3
25°	2030.4	2032.0	2034.1	2051.4	2054.6
27.5°	1979.3	1981.9	1985.7	2001.3	2004.5
30°	1923.3	1927.6	1931.9	1948.0	1952.4
32.5°	1864.1	1868.4	1873.8	1894.8	1896.9
35°	1797.4	1805.4	1813.0	1831.3	1838.8
37.5°	1730.6	1740.9	1747.9	1767.2	1773.2
40°	1660.1	1670.4	1681.7	1702.1	1705.9
42.5°	1586.4	1598.3	1611.7	1630.0	1636.5
45°	1512.2	1525.6	1538.0	1553.1	1560.6
47.5°	1432.0	1445.4	1460.5	1477.7	1482.6
50°	1349.1	1364.7	1380.9	1397.0	1405.6
52.5°	1264.1	1282.9	1301.2	1318.4	1326.5
55°	1180.1	1194.1	1216.2	1233.9	1242.0
57.5°	1093.0	1104.8	1124.7	1153.8	1158.1
60°	1004.2	1014.9	1035.4	1059.0	1068.7
62.5°	906.2	920.7	942.3	972.4	981.0
65°	811.0	825.0	853.5	887.4	901.4
67.5°	718.9	723.8	760.4	795.9	818.5
70°	610.2	628.5	671.1	714.6	731.9
72.5°	516.6	534.9	581.7	632.8	654.4
75°	410.6	435.9	499.4	559.1	580.1
77.5°	317.5	345.5	424.0	484.3	508.5
80°	221.7	265.3	350.9	418.7	445.0
82.5°	139.4	193.2	284.7	355.7	378.8
85°	71.0	131.3	225.5	298.1	324.5
87.5°	18.8	85.0	175.4	244.9	271.8
90°	0.5	49.0	132.9	199.6	223.9
92.5°	0.5	27.4	99.0	158.7	183.5
95°	0.5	12.9	68.9	124.8	144.2
97.5°	0.5	5.4	47.4	94.2	113.5
100°	0.5	2.7	30.1	68.3	85.0
102.5°	1.1	1.6	18.8	49.0	62.4
105°	1.1	1.6	11.3	33.4	44.7
107.5°	1.1	1.6	6.5	22.6	30.7
110°	1.6	1.6	3.8	14.0	20.4

TEST NUMBER: P518070

CATALOG NUMBER: HVL8-4-LD4-2HI-40-UNV-O-EDD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1.6	1.6	2.2	9.1	13.5
115°	1.6	1.6	2.2	5.9	8.6
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)