

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P518181

Luminaire Tested: HVL8-8-LD4-1LO-40-UNV-O-EDD-90

Issue Date: 4/27/2021

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P518181
Test Lab: INNOVATION CENTER
Issue Date: 4/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: HVL8-8-LD4-1LO-40-UNV-O-EDD-90
Description: 8 FOOT, 8 INCH WIDE, HVL LED LUMINAIRE, WITH 4000K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5219.0 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.67' x L: 8' x H: 0.17')
CIE Type: Direct


Input Watts (W): 46
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P518181

CATALOG NUMBER: HVL8-8-LD4-1LO-40-UNV-O-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P518181

CATALOG NUMBER: HVL8-8-LD4-1LO-40-UNV-O-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		98
1	108	102	98	94	105	100	96	92	95	92	89		91	88	86		81
2	98	89	82	76	95	87	80	75	83	77	73		79	75	71		67
3	89	78	69	63	86	76	68	62	73	66	61		70	64	59		56
4	81	69	60	53	79	67	59	52	65	57	52		62	56	51		47
5	75	61	52	45	72	60	52	45	58	50	44		56	49	44		41
6	69	55	46	40	67	54	46	39	52	45	39		50	44	38		36
7	64	50	41	35	62	49	41	35	47	40	34		46	39	34		32
8	59	46	37	31	58	45	37	31	43	36	31		42	35	30		28
9	55	42	34	28	54	41	33	28	40	33	28		39	32	27		25
10	52	39	31	25	51	38	30	25	37	30	25		36	29	25		23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3484	3484	3484
5°	3483	3410	3409
10°	3466	3353	3341
15°	3443	3290	3259
20°	3417	3218	3179
25°	3386	3144	3098
30°	3349	3065	3006
35°	3300	2978	2915
40°	3250	2886	2809
45°	3197	2786	2694
50°	3125	2669	2571
55°	3049	2541	2435
60°	2958	2373	2276
65°	2803	2185	2119
70°	2575	1962	1936
75°	2247	1717	1770
80°	1742	1478	1617
85°	1004	1238	1473

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3197 cd/sqm

TEST NUMBER: P518181

CATALOG NUMBER: HVL8-8-LD4-1LO-40-UNV-O-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.3	3.1
10°-20°	468.5	9.0
20°-30°	710.9	13.6
30°-40°	859.6	16.5
40°-50°	897.0	17.2
50°-60°	820.1	15.7
60°-70°	639.3	12.2
70°-80°	399.9	7.7
80°-90°	181.6	3.5
90°-100°	60.9	1.2
100°-110°	15.3	0.3
110°-120°	2.4	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1342.8	25.7
0°-40°	2202.5	42.2
0°-60°	3919.5	75.1
0°-90°	5140.4	98.5
90°-120°	78.6	1.5
90°-150°	78.6	1.5
90°-180°	79.0	1.5
0°-180°	5219.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1722	1719	1712	1720	1720	164
15°	1657	1660	1655	1665	1664	468
25°	1535	1536	1538	1551	1554	707
35°	1359	1365	1371	1385	1390	851
45°	1143	1154	1163	1174	1180	881
55°	892	903	920	933	939	797
65°	613	624	645	671	682	607
75°	310	330	378	423	439	331
85°	54	99	170	225	245	68
90°	0	37	100	151	169	2
95°	0	10	52	94	109	0
105°	1	1	8	25	34	1
115°	1	1	2	4	6	1
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P518181

CATALOG NUMBER: HVL8-8-LD4-1LO-40-UNV-O-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1726.1	1726.1	1726.1	1726.1	1726.1
2.5°	1728.2	1725.7	1718.0	1725.7	1725.3
5°	1722.5	1719.2	1711.5	1719.6	1719.6
7.5°	1711.1	1709.9	1702.9	1712.3	1712.3
10°	1697.6	1697.2	1691.5	1701.7	1702.1
12.5°	1678.9	1680.6	1675.3	1685.0	1686.3
15°	1657.0	1659.8	1655.3	1664.7	1664.3
17.5°	1632.9	1634.6	1631.3	1641.9	1641.5
20°	1603.2	1605.3	1602.8	1613.8	1615.0
22.5°	1570.3	1573.1	1572.7	1584.1	1587.4
25°	1535.3	1536.5	1538.1	1551.2	1553.6
27.5°	1496.6	1498.7	1501.5	1513.3	1515.8
30°	1454.3	1457.6	1460.8	1473.0	1476.3
32.5°	1409.6	1412.8	1416.9	1432.7	1434.4
35°	1359.1	1365.2	1370.9	1384.7	1390.4
37.5°	1308.6	1316.4	1321.7	1336.3	1340.8
40°	1255.3	1263.1	1271.6	1287.1	1289.9
42.5°	1199.6	1208.5	1218.7	1232.5	1237.4
45°	1143.4	1153.6	1163.0	1174.4	1180.1
47.5°	1082.8	1093.0	1104.4	1117.4	1121.0
50°	1020.1	1031.9	1044.1	1056.3	1062.9
52.5°	955.8	970.1	983.9	996.9	1003.0
55°	892.4	902.9	919.6	933.1	939.2
57.5°	826.4	835.4	850.5	872.4	875.7
60°	759.3	767.4	782.9	800.8	808.1
62.5°	685.2	696.2	712.5	735.3	741.8
65°	613.2	623.8	645.4	671.0	681.6
67.5°	543.6	547.3	575.0	601.8	618.9
70°	461.4	475.3	507.4	540.4	553.4
72.5°	390.6	404.5	439.9	478.5	494.8
75°	310.5	329.6	377.6	422.8	438.7
77.5°	240.1	261.2	320.6	366.2	384.5
80°	167.6	200.6	265.3	316.6	336.5
82.5°	105.4	146.1	215.3	269.0	286.5
85°	53.7	99.3	170.5	225.4	245.4
87.5°	14.2	64.3	132.7	185.1	205.5
90°	0.4	37.0	100.5	151.0	169.3
92.5°	0.4	20.8	74.9	120.0	138.8
95°	0.4	9.8	52.1	94.4	109.1
97.5°	0.4	4.1	35.8	71.2	85.9
100°	0.4	2.0	22.8	51.7	64.3
102.5°	0.8	1.2	14.2	37.0	47.2
105°	0.8	1.2	8.5	25.2	33.8
107.5°	0.8	1.2	4.9	17.1	23.2
110°	1.2	1.2	2.8	10.6	15.5

TEST NUMBER: P518181

CATALOG NUMBER: HVL8-8-LD4-1LO-40-UNV-O-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1.2	1.2	1.6	6.9	10.2
115°	1.2	1.2	1.6	4.5	6.5
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)