

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P580475

Luminaire Tested: **HVSL4-2-LD4-1LO-30-UNV-O-EDD-90**

Issue Date: 12/16/2022



Test Information

Test Method: LM-79-08
Report Number: P580475
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-6)
Test Lab: INNOVATION CENTER
Issue Date: 12/16/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: HVSL4-2-LD4-1LO-30-UNV-O-EDD-90
Description: 2 FOOT, 4INCH WIDE, HVSL LED LUMINAIRE, WITH 3000K, 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1162.0 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 2' x H: 0.17')
CIE Type: Direct

Input Watts (W): 11.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P580475

CATALOG NUMBER: HVSL4-2-LD4-1LO-30-UNV-O-EDD-90

Luminous Intensity Polar Plot





TEST NUMBER: P580475

CATALOG NUMBER: HVSL4-2-LD4-1LO-30-UNV-O-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	101	101	101			98
1	108	102	98	94	105	100	96	92	95	92	89	91	88	86	87	85	83			81
2	98	89	82	76	95	87	80	75	83	77	73	79	75	71	76	72	69			67
3	89	78	69	63	86	76	68	62	73	66	61	70	64	59	67	62	58			56
4	81	69	60	53	79	67	59	52	65	57	52	62	56	51	60	54	50			47
5	75	61	52	45	72	60	52	45	58	50	44	56	49	44	54	48	43			41
6	69	55	46	40	67	54	46	39	52	45	39	50	44	38	49	43	38			36
7	64	50	41	35	62	49	41	35	47	40	34	46	39	34	44	38	34			32
8	59	46	37	31	58	45	37	31	43	36	31	42	35	30	41	35	30			28
9	55	42	34	28	54	41	33	28	40	33	28	39	32	27	38	32	27			25
10	52	39	31	25	51	38	30	25	37	30	25	36	29	25	35	29	25			23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6205	6205	6205
5°	6171	5962	5946
10°	6108	5756	5710
15°	6032	5548	5461
20°	5953	5332	5227
25°	5861	5117	4997
30°	5760	4897	4755
35°	5635	4667	4520
40°	5506	4432	4264
45°	5366	4185	3999
50°	5189	3915	3724
55°	4998	3628	3434
60°	4772	3283	3113
65°	4424	2913	2798
70°	3945	2500	2450
75°	3288	2066	2126
80°	2355	1645	1815
85°	1138	1232	1506



TEST NUMBER: P580475

CATALOG NUMBER: HVSL4-2-LD4-1LO-30-UNV-O-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.4	3.1
10°-20°	104.3	9.0
20°-30°	158.3	13.6
30°-40°	191.4	16.5
40°-50°	199.7	17.2
50°-60°	182.6	15.7
60°-70°	142.3	12.2
70°-80°	89.0	7.7
80°-90°	40.4	3.5
90°-100°	13.6	1.2
100°-110°	3.4	0.3
110°-120°	0.5	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	299.0	25.7
0°-40°	490.4	42.2
0°-60°	872.7	75.1
0°-90°	1144.5	98.5
90°-120°	17.5	1.5
90°-150°	17.5	1.5
90°-180°	18.0	1.5
0°-180°	1162.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	384	384	384	384	384	
5°	384	383	381	383	383	36
15°	369	370	369	371	370	104
25°	342	342	342	345	346	158
35°	303	304	305	308	310	189
45°	255	257	259	262	263	196
55°	199	201	205	208	209	178
65°	136	139	144	149	152	135
75°	69	73	84	94	98	74
85°	12	22	38	50	55	15
90°	0	8	22	34	38	0
95°	0	2	12	21	24	0
105°	0	0	2	6	8	0
115°	0	0	0	1	1	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	



TEST NUMBER: P580475

CATALOG NUMBER: HVSL4-2-LD4-1LO-30-UNV-O-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	384.3	384.3	384.3	384.3	384.3
2.5°	384.8	384.2	382.5	384.2	384.1
5°	383.5	382.8	381.1	382.9	382.9
7.5°	381.0	380.7	379.2	381.2	381.2
10°	378.0	377.9	376.6	378.9	379.0
12.5°	373.8	374.2	373.0	375.2	375.4
15°	368.9	369.6	368.6	370.6	370.5
17.5°	363.6	363.9	363.2	365.6	365.5
20°	357.0	357.4	356.9	359.3	359.6
22.5°	349.6	350.3	350.2	352.7	353.4
25°	341.8	342.1	342.5	345.4	345.9
27.5°	333.2	333.7	334.3	336.9	337.5
30°	323.8	324.5	325.2	328.0	328.7
32.5°	313.8	314.6	315.5	319.0	319.4
35°	302.6	304.0	305.2	308.3	309.6
37.5°	291.4	293.1	294.3	297.5	298.5
40°	279.5	281.2	283.1	286.6	287.2
42.5°	267.1	269.1	271.3	274.4	275.5
45°	254.6	256.8	258.9	261.5	262.7
47.5°	241.1	243.3	245.9	248.8	249.6
50°	227.1	229.8	232.5	235.2	236.6
52.5°	212.8	216.0	219.1	222.0	223.3
55°	198.7	201.0	204.8	207.7	209.1
57.5°	184.0	186.0	189.4	194.2	195.0
60°	169.1	170.9	174.3	178.3	179.9
62.5°	152.6	155.0	158.6	163.7	165.2
65°	136.5	138.9	143.7	149.4	151.8
67.5°	121.0	121.9	128.0	134.0	137.8
70°	102.7	105.8	113.0	120.3	123.2
72.5°	87.0	90.1	97.9	106.5	110.2
75°	69.1	73.4	84.1	94.1	97.7
77.5°	53.5	58.2	71.4	81.5	85.6
80°	37.3	44.7	59.1	70.5	74.9
82.5°	23.5	32.5	47.9	59.9	63.8
85°	12.0	22.1	38.0	50.2	54.6
87.5°	3.2	14.3	29.5	41.2	45.8
90°	0.1	8.2	22.4	33.6	37.7
92.5°	0.1	4.6	16.7	26.7	30.9
95°	0.1	2.2	11.6	21.0	24.3
97.5°	0.1	0.9	8.0	15.9	19.1
100°	0.1	0.5	5.1	11.5	14.3
102.5°	0.2	0.3	3.2	8.2	10.5
105°	0.2	0.3	1.9	5.6	7.5



TEST NUMBER: P580475

CATALOG NUMBER: HVSL4-2-LD4-1LO-30-UNV-O-EDD-90

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.3	0.3	0.4	1.5	2.3
115°	0.3	0.3	0.4	1.0	1.4
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - 90°-270°







107.5°	0.2	0.3	1.1	3.8	5.2
110°	0.3	0.3	0.6	2.4	3.4



(END OF REPORT)