

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572207

Luminaire Tested: **FLD4C-10-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572207
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-10-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 788.0 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572207

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P572207

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62397
5°	62636
10°	62823
15°	62831
20°	62480
25°	61026
30°	57027
35°	49387
40°	38586
45°	27677
50°	17985
55°	10774
60°	6290
65°	4041
70°	2694
75°	2041
80°	1486
85°	0



TEST NUMBER: P572207

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	6.1
10°-20°	139.4	17.7
20°-30°	205.7	26.1
30°-40°	202.9	25.8
40°-50°	124.2	15.8
50°-60°	47.6	6.0
60°-70°	14.9	1.9
70°-80°	4.4	0.6
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	393.4	49.9
0°-40°	596.4	75.7
0°-60°	768.2	97.5
0°-90°	788.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	788.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	508	
5°	508	48
15°	494	139
25°	450	206
35°	329	203
45°	159	124
55°	50	48
65°	14	15
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P572207

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-27 F4X-W-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	507.9
2.5°	509.0
5°	507.9
7.5°	506.8
10°	503.6
12.5°	499.4
15°	494.0
17.5°	487.6
20°	477.9
22.5°	467.3
25°	450.2
27.5°	428.8
30°	402.0
32.5°	368.9
35°	329.3
37.5°	285.5
40°	240.6
42.5°	198.9
45°	159.3
47.5°	124.0
50°	94.1
52.5°	69.5
55°	50.3
57.5°	35.3
60°	25.6
62.5°	19.3
65°	13.9
67.5°	10.7
70°	7.5
72.5°	5.4
75°	4.3
77.5°	2.1
80°	2.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)