

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572277

Luminaire Tested: **FLD4C-10-D010 FEU4C-X-90-35 F4X-W-X-H-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572277
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-10-D010 FEU4C-X-90-35 F4X-W-X-H-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 763.1 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572277

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-35 F4X-W-X-H-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P572277

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-35 F4X-W-X-H-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	112	109	106	104		110	107	104	102		103	101	99			99	97	96			91
2	105	100	95	91		103	98	93	90		95	91	88			91	88	86			82
3	99	91	85	80		97	90	84	80		87	82	78			84	80	77			74
4	92	83	77	72		90	82	76	71		80	75	70			78	73	70			67
5	87	77	70	65		85	76	69	64		74	68	64			72	67	63			61
6	81	71	64	58		80	70	63	58		68	62	58			67	61	57			55
7	76	65	58	53		75	65	58	53		63	57	53			62	56	52			50
8	72	60	53	49		70	60	53	49		59	53	48			58	52	48			46
9	67	56	49	45		66	56	49	45		55	49	44			54	48	44			43
10	64	52	46	41		63	52	46	41		51	45	41			50	45	41			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60419
5°	60650
10°	60840
15°	60834
20°	60506
25°	59088
30°	55226
35°	47827
40°	37351
45°	26808
50°	17412
55°	10431
60°	6094
65°	3924
70°	2622
75°	1946
80°	1486
85°	0



TEST NUMBER: P572277

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-35 F4X-W-X-H-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.8	6.1
10°-20°	134.9	17.7
20°-30°	199.1	26.1
30°-40°	196.5	25.8
40°-50°	120.3	15.8
50°-60°	46.1	6.0
60°-70°	14.4	1.9
70°-80°	4.2	0.6
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	380.9	49.9
0°-40°	577.4	75.7
0°-60°	743.8	97.5
0°-90°	763.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	763.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	492	
5°	492	47
15°	478	135
25°	436	199
35°	319	197
45°	154	120
55°	49	46
65°	14	14
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P572277

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-35 F4X-W-X-H-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	491.8
2.5°	492.8
5°	491.8
7.5°	490.8
10°	487.7
12.5°	483.5
15°	478.3
17.5°	472.1
20°	462.8
22.5°	452.5
25°	435.9
27.5°	415.2
30°	389.3
32.5°	357.2
35°	318.9
37.5°	276.4
40°	232.9
42.5°	192.6
45°	154.3
47.5°	120.1
50°	91.1
52.5°	67.3
55°	48.7
57.5°	34.2
60°	24.8
62.5°	18.7
65°	13.5
67.5°	10.4
70°	7.3
72.5°	5.2
75°	4.1
77.5°	2.1
80°	2.1
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)