

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572285

Luminaire Tested: **FLD4C-10-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572285
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-10-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 984.0 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572285

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV

Luminous Intensity Polar Plot



TEST NUMBER: P572285

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92						
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84						
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77						
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70						
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64						
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58						
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54						
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49						
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45						
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74068
5°	75326
10°	78729
15°	83562
20°	87228
25°	86470
30°	80406
35°	68794
40°	52410
45°	30735
50°	13130
55°	3877
60°	1106
65°	669
70°	395
75°	522
80°	0
85°	0



TEST NUMBER: P572285

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.0	6.0
10°-20°	186.1	18.9
20°-30°	290.3	29.5
30°-40°	282.4	28.7
40°-50°	141.1	14.3
50°-60°	21.8	2.2
60°-70°	2.7	0.3
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	535.3	54.4
0°-40°	817.7	83.1
0°-60°	980.6	99.7
0°-90°	984.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	984.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	603	
5°	611	59
15°	657	186
25°	638	290
35°	459	282
45°	177	141
55°	18	22
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P572285

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-35 F4X-W-X-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	602.9
2.5°	605.1
5°	610.8
7.5°	619.8
10°	631.1
12.5°	645.7
15°	657.0
17.5°	666.0
20°	667.2
22.5°	659.3
25°	637.9
27.5°	606.3
30°	566.8
32.5°	517.3
35°	458.7
37.5°	394.4
40°	326.8
42.5°	254.7
45°	176.9
47.5°	113.8
50°	68.7
52.5°	37.2
55°	18.1
57.5°	7.9
60°	4.5
62.5°	3.4
65°	2.3
67.5°	2.3
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)