

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572344

Luminaire Tested: **FLD4C-10-D010 FEU4C-X-90-50 F4X-N-X-LI-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572344
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-10-D010 FEU4C-X-90-50 F4X-N-X-LI-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBNLI TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 308.1 lumens
Efficiency: N/A
Efficacy: 31.6 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572344

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-50 F4X-N-X-LI-BL89AM

Luminous Intensity Polar Plot



TEST NUMBER: P572344

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-50 F4X-N-X-LI-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95						
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90						
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85						
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81						
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77						
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73						
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69						
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66						
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63						
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97374
5°	87633
10°	67926
15°	49171
20°	34044
25°	24820
30°	18030
35°	10678
40°	4490
45°	1407
50°	191
55°	107
60°	123
65°	145
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P572344

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-50 F4X-N-X-LI-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.5	20.3
10°-20°	106.9	34.7
20°-30°	85.0	27.6
30°-40°	45.0	14.6
40°-50°	7.8	2.5
50°-60°	0.6	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	254.4	82.6
0°-40°	299.4	97.2
0°-60°	307.8	99.9
0°-90°	308.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	308.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	793	
5°	711	62
15°	387	107
25°	183	85
35°	71	45
45°	8	8
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P572344

CATALOG NUMBER: FLD4C-10-D010 FEU4C-X-90-50 F4X-N-X-LI-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	792.6
2.5°	772.2
5°	710.6
7.5°	629.9
10°	544.5
12.5°	462.0
15°	386.6
17.5°	316.4
20°	260.4
22.5°	217.7
25°	183.1
27.5°	155.1
30°	127.1
32.5°	98.7
35°	71.2
37.5°	47.0
40°	28.0
42.5°	16.1
45°	8.1
47.5°	2.9
50°	1.0
52.5°	1.0
55°	0.5
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)