

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P571647

Luminaire Tested: **FLD4C-02-D010 FEU4C-X-90-27 F4X-M-X-LI-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P571647
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-02-D010 FEU4C-X-90-27 F4X-M-X-LI-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 4LBMLI TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 265.0 lumens
Efficiency: N/A
Efficacy: 75.7 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P571647

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-27 F4X-M-X-LI-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P571647

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-27 F4X-M-X-LI-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	106		111	109	107	105		105	103	101		101	100	98		98	97	96
2	108	103	100	96		106	102	98	95		99	96	93		96	93	91		93	91	89
3	103	97	92	88		101	95	91	87		93	89	86		90	87	85		88	85	83
4	98	91	85	81		96	89	84	81		87	83	80		85	82	79		83	80	78
5	93	85	79	75		91	84	79	75		82	78	74		81	77	73		79	76	73
6	89	80	74	70		87	79	74	70		78	73	69		76	72	69		75	71	68
7	84	75	69	65		83	75	69	65		73	68	65		72	68	64		71	67	64
8	80	71	65	61		79	70	65	61		69	64	61		68	64	60		67	63	60
9	77	67	61	57		75	67	61	57		66	61	57		65	60	57		64	60	57
10	73	64	58	54		72	63	58	54		62	57	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40738
5°	40351
10°	38235
15°	34722
20°	30684
25°	26528
30°	20726
35°	12718
40°	6527
45°	2589
50°	841
55°	300
60°	246
65°	203
70°	108
75°	142
80°	0
85°	0



TEST NUMBER: P571647

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-27 F4X-M-X-LI-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.5	11.5
10°-20°	76.1	28.7
20°-30°	88.4	33.4
30°-40°	54.2	20.4
40°-50°	13.4	5.1
50°-60°	1.6	0.6
60°-70°	0.6	0.2
70°-80°	0.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	195.0	73.6
0°-40°	249.2	94.0
0°-60°	264.2	99.7
0°-90°	265.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	265.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	332	
5°	327	31
15°	273	76
25°	196	88
35°	85	54
45°	15	13
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P571647

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-27 F4X-M-X-LI-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	331.6
2.5°	331.3
5°	327.2
7.5°	318.4
10°	306.5
12.5°	290.9
15°	273.0
17.5°	253.6
20°	234.7
22.5°	215.7
25°	195.7
27.5°	172.6
30°	146.1
32.5°	115.3
35°	84.8
37.5°	59.7
40°	40.7
42.5°	25.4
45°	14.9
47.5°	8.5
50°	4.4
52.5°	2.0
55°	1.4
57.5°	1.0
60°	1.0
62.5°	0.7
65°	0.7
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)