

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P571784

Luminaire Tested: **FLD4C-02-D010 FEU4C-X-90-50 F4X-M-X-H-BL85**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P571784
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-02-D010 FEU4C-X-90-50 F4X-M-X-H-BL85
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBMH TRIM
AND BOTTOM LENS, 0.187" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 226.0 lumens
Efficiency: N/A
Efficacy: 64.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P571784

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-50 F4X-M-X-H-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P571784

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-50 F4X-M-X-H-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	113	110	108	105		111	108	106	104		104	102	100			100	99	97			97
2	107	102	98	94		105	100	96	93		97	94	91			94	91	89			91
3	101	94	89	85		99	93	88	84		90	86	83			88	84	82			86
4	96	88	82	77		94	86	81	77		84	80	76			82	78	75			80
5	90	82	75	71		89	81	75	70		79	74	70			77	73	69			75
6	86	76	70	65		84	75	69	65		74	68	64			72	68	64			71
7	81	71	65	60		80	70	64	60		69	64	60			68	63	59			67
8	77	67	60	56		75	66	60	56		65	59	56			64	59	55			63
9	73	63	56	52		72	62	56	52		61	56	52			60	55	52			59
10	69	59	53	49		68	59	53	49		58	52	49			57	52	48			56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	27531
5°	27131
10°	25998
15°	24560
20°	22918
25°	20808
30°	17378
35°	12583
40°	7874
45°	4500
50°	2351
55°	1307
60°	835
65°	494
70°	359
75°	142
80°	212
85°	0



TEST NUMBER: P571784

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-50 F4X-M-X-H-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.6	9.1
10°-20°	54.1	23.9
20°-30°	69.5	30.8
30°-40°	52.3	23.2
40°-50°	21.0	9.3
50°-60°	5.9	2.6
60°-70°	1.9	0.8
70°-80°	0.5	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	144.2	63.8
0°-40°	196.6	87.0
0°-60°	223.5	98.9
0°-90°	226.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	226.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	224	
5°	220	21
15°	193	54
25°	154	70
35°	84	52
45°	26	21
55°	6	6
65°	2	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P571784

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-50 F4X-M-X-H-BL85

CANDELA DISTRIBUTION (FULL):

	0°
0°	224.1
2.5°	222.7
5°	220.0
7.5°	214.9
10°	208.4
12.5°	200.6
15°	193.1
17.5°	184.5
20°	175.3
22.5°	165.4
25°	153.5
27.5°	139.2
30°	122.5
32.5°	103.7
35°	83.9
37.5°	65.5
40°	49.1
42.5°	36.2
45°	25.9
47.5°	17.7
50°	12.3
52.5°	8.5
55°	6.1
57.5°	4.4
60°	3.4
62.5°	2.4
65°	1.7
67.5°	1.4
70°	1.0
72.5°	0.7
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)