

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P571792

Luminaire Tested: **FLD4C-02-D010 FEU4C-X-90-50 F4X-M-X-LI-BL89AM**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P571792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-02-D010 FEU4C-X-90-50 F4X-M-X-LI-BL89AM
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBMLI TRIM
AND BOTTOM LENS, 0.125" OPAL POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 128.0 lumens
Efficiency: N/A
Efficacy: 36.6 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 3.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P571792

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-50 F4X-M-X-LI-BL89AM

Luminous Intensity Polar Plot





TEST NUMBER: P571792

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-50 F4X-M-X-LI-BL89AM

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	90	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	19681
5°	19497
10°	18475
15°	16763
20°	14813
25°	12810
30°	10015
35°	6134
40°	3159
45°	1251
50°	401
55°	150
60°	123
65°	87
70°	72
75°	95
80°	0
85°	0



TEST NUMBER: P571792

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-50 F4X-M-X-LI-BL89AM

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.8	11.5
10°-20°	36.7	28.7
20°-30°	42.7	33.4
30°-40°	26.1	20.4
40°-50°	6.5	5.1
50°-60°	0.8	0.6
60°-70°	0.3	0.2
70°-80°	0.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	94.2	73.6
0°-40°	120.3	94.0
0°-60°	127.6	99.7
0°-90°	128.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	128.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	160	
5°	158	15
15°	132	37
25°	94	43
35°	41	26
45°	7	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P571792

CATALOG NUMBER: FLD4C-02-D010 FEU4C-X-90-50 F4X-M-X-LI-BL89AM

CANDELA DISTRIBUTION (FULL):

	0°
0°	160.2
2.5°	160.0
5°	158.1
7.5°	153.8
10°	148.1
12.5°	140.5
15°	131.8
17.5°	122.5
20°	113.3
22.5°	104.2
25°	94.5
27.5°	83.4
30°	70.6
32.5°	55.7
35°	40.9
37.5°	28.8
40°	19.7
42.5°	12.3
45°	7.2
47.5°	4.1
50°	2.1
52.5°	1.0
55°	0.7
57.5°	0.5
60°	0.5
62.5°	0.3
65°	0.3
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)