

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572763

Luminaire Tested: **FLD4C-25-D010 FEU4C-X-90-30 F4X-M-X-LI-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572763
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-25-D010 FEU4C-X-90-30 F4X-M-X-LI-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBMLI TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2099.0 lumens
Efficiency: N/A
Efficacy: 66.6 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572763

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-30 F4X-M-X-LI-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P572763

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-30 F4X-M-X-LI-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	106		111	109	107	105		105	103	101		101	100	98		98	97	96
2	108	103	100	96		106	102	98	95		99	96	93		96	93	91		93	91	89
3	103	97	92	88		101	95	91	87		93	89	86		90	87	85		88	85	83
4	98	91	85	81		96	89	84	81		87	83	80		85	82	79		83	80	78
5	93	85	79	75		91	84	79	75		82	78	74		81	77	73		79	76	73
6	89	80	74	70		87	79	74	70		78	73	69		76	72	69		75	71	68
7	84	75	69	65		83	75	69	65		73	68	65		72	68	64		71	67	64
8	80	71	65	61		79	70	65	61		69	64	61		68	64	60		67	63	60
9	77	67	61	57		75	67	61	57		66	61	57		65	60	57		64	60	57
10	73	64	58	54		72	63	58	54		62	57	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	322712
5°	319640
10°	302890
15°	274992
20°	243003
25°	210081
30°	164216
35°	100709
40°	51688
45°	20536
50°	6670
55°	2292
60°	1966
65°	1570
70°	970
75°	1282
80°	0
85°	0



TEST NUMBER: P572763

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-30 F4X-M-X-LI-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.0	11.5
10°-20°	602.5	28.7
20°-30°	700.3	33.4
30°-40°	428.9	20.4
40°-50°	106.5	5.1
50°-60°	12.4	0.6
60°-70°	4.6	0.2
70°-80°	1.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1544.8	73.6
0°-40°	1973.6	94.0
0°-60°	2092.6	99.7
0°-90°	2099.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2099.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2627	
5°	2592	242
15°	2162	602
25°	1550	700
35°	672	429
45°	118	107
55°	11	12
65°	5	5
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P572763

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-30 F4X-M-X-LI-BL86

CANDELA DISTRIBUTION (FULL):

0°	
0°	2626.8
2.5°	2624.1
5°	2591.9
7.5°	2522.0
10°	2428.0
12.5°	2304.5
15°	2162.1
17.5°	2009.0
20°	1858.7
22.5°	1708.2
25°	1549.8
27.5°	1367.1
30°	1157.6
32.5°	913.2
35°	671.5
37.5°	472.7
40°	322.3
42.5°	201.4
45°	118.2
47.5°	67.2
50°	34.9
52.5°	16.1
55°	10.7
57.5°	8.0
60°	8.0
62.5°	5.4
65°	5.4
67.5°	2.7
70°	2.7
72.5°	2.7
75°	2.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)