

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P861194

Luminaire Tested: **4APVTLD-SL3C3 LOW POWER 5000K 277V**

Issue Date: 1/31/2023

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P861194
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2210-820-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/31/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 4APVTLD-SL3C3 LOW POWER 5000K 277V
Description: LOW POWER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2977.1 lumens
Efficiency: N/A
Efficacy: 134.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.29 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 8' x H: 0.08')
CIE Type: Direct

Input Watts (W): 22.2
Input Voltage (V): 277
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P861194

CATALOG NUMBER: 4APVTLD-SL3C3 LOW POWER 5000K 277V

Luminous Intensity Polar Plot





TEST NUMBER: P861194

CATALOG NUMBER: 4APVTLD-SL3C3 LOW POWER 5000K 277V

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	117	117	117	117		114	114	114	114		107	107	107		101	101	101		95	95	95
1	105	100	95	90		102	97	92	88		91	87	84		86	83	80		81	79	76
2	95	86	79	72		92	83	77	71		79	73	68		74	70	65		70	66	63
3	86	75	66	59		83	73	65	58		69	62	56		65	59	54		61	57	53
4	79	66	57	50		76	64	56	49		61	53	48		58	51	46		55	49	45
5	72	59	50	43		70	57	49	42		54	47	41		52	45	40		49	43	39
6	67	53	44	37		64	52	43	37		49	41	36		47	40	35		44	38	34
7	62	48	39	33		60	47	38	32		44	37	31		42	36	31		40	34	30
8	57	44	35	29		55	43	34	29		41	33	28		39	32	27		37	31	27
9	54	40	32	26		52	39	31	26		37	30	25		36	29	25		34	28	24
10	50	37	29	23		49	36	28	23		35	28	23		33	27	22		32	26	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3492	3492	3492
5°	3461	3425	3434
10°	3445	3362	3360
15°	3417	3297	3294
20°	3376	3225	3213
25°	3333	3150	3131
30°	3280	3071	3055
35°	3229	2990	2986
40°	3165	2912	2931
45°	3102	2835	2868
50°	3021	2765	2816
55°	2926	2691	2774
60°	2823	2614	2727
65°	2691	2527	2667
70°	2467	2429	2617
75°	2192	2320	2550
80°	1822	2206	2500
85°	1324	2178	2497



TEST NUMBER: P861194

CATALOG NUMBER: 4APVTLD-SL3C3 LOW POWER 5000K 277V

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.8	2.7
10°-20°	234.3	7.9
20°-30°	354.7	11.9
30°-40°	429.8	14.4
40°-50°	455.2	15.3
50°-60°	430.6	14.5
60°-70°	360.8	12.1
70°-80°	257.2	8.6
80°-90°	151.5	5.1
90°-100°	96.0	3.2
100°-110°	62.3	2.1
110°-120°	36.1	1.2
120°-130°	17.8	0.6
130°-140°	6.3	0.2
140°-150°	1.8	0.1
150°-160°	0.8	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-30°	670.8	22.5
0°-40°	1100.6	37.0
0°-60°	1986.3	66.7
0°-90°	2755.9	92.6
90°-120°	194.4	6.5
90°-150°	220.3	7.4
90°-180°	221.0	7.4
0°-180°	2977.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	865	865	865	865	865	
5°	855	866	859	859	866	81
15°	820	831	828	833	841	231
25°	752	765	768	777	785	346
35°	660	674	685	702	712	412
45°	549	567	588	615	628	423
55°	422	447	483	518	535	377
65°	288	319	369	411	429	284
75°	146	191	251	299	316	155
85°	32	84	146	191	208	38
90°	11	55	114	158	174	7
95°	9	40	95	135	151	7
105°	7	20	61	95	108	8
115°	6	8	36	61	72	6
125°	4	4	16	34	42	3
135°	2	3	4	14	19	2
145°	2	2	2	3	3	1
155°	2	1	2	2	2	1
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	



TEST NUMBER: P861194

CATALOG NUMBER: 4APVTLD-SL3C3 LOW POWER 5000K 277V

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	865	865	865	865	865
2.5°	859	870	862	863	866
5°	855	866	859	859	866
7.5°	850	861	854	855	863
10°	842	853	847	849	856
12.5°	831	842	838	841	848
15°	820	831	828	833	841
17.5°	805	817	815	822	829
20°	789	801	801	808	816
22.5°	771	783	786	792	802
25°	752	765	768	777	785
27.5°	731	744	749	760	768
30°	708	721	729	741	750
32.5°	684	698	707	722	731
35°	660	674	685	702	712
37.5°	633	648	662	681	693
40°	606	622	638	659	673
42.5°	578	595	613	638	651
45°	549	567	588	615	628
47.5°	519	538	563	591	606
50°	487	508	537	567	582
52.5°	455	477	510	543	559
55°	422	447	483	518	535
57.5°	389	415	455	492	510
60°	356	383	427	466	484
62.5°	322	352	398	439	457
65°	288	319	369	411	429
67.5°	253	287	340	383	402
70°	215	255	310	355	374
72.5°	181	223	281	328	345
75°	146	191	251	299	316
77.5°	113	161	222	270	288
80°	83	133	194	241	260
82.5°	56	107	169	215	233
85°	32	84	146	191	208
87.5°	17	66	127	172	188
90°	11	55	114	158	174
92.5°	10	47	104	146	162
95°	9	40	95	135	151
97.5°	9	34	86	125	140
100°	8	29	77	114	129
102.5°	8	25	69	104	118
105°	7	20	61	95	108



TEST NUMBER: P861194

CATALOG NUMBER: 4APVTLD-SL3C3 LOW POWER 5000K 277V

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	6	10	42	69	80
115°	6	8	36	61	72
117.5°	5	6	31	54	64
120°	5	5	25	47	56
122.5°	4	5	21	41	49
125°	4	4	16	34	42
127.5°	3	4	12	29	36
130°	3	4	9	23	30
132.5°	3	3	6	18	24
135°	2	3	4	14	19
137.5°	2	2	3	9	14
140°	2	2	3	6	10
142.5°	2	2	3	4	6
145°	2	2	2	3	3
147.5°	2	2	2	3	3
150°	2	1	2	3	3
152.5°	2	1	2	2	3
155°	2	1	2	2	2
157.5°	2	1	2	2	2
160°	2	1	1	1	2
162.5°	0	0	0	0	0
165°	0	0	0	0	0
167.5°	0	0	0	0	0
170°	0	0	0	0	0
172.5°	0	0	0	0	0
175°	0	0	0	0	0
177.5°	0	0	0	0	0
180°	0	0	0	0	0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - 90°-270°







107.5°	7	17	54	86	98
110°	6	13	48	77	89



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

METALUX

Report Number: SP1-2210-820-18

Test Date: 11/11/2022

Luminaire Tested: 4APVTLD-SL3C3

Data in this report applies to families of products including 4APVTLD-SL3C3.


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2210-820-18
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/11/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: METALUX
 Catalog Number: **4APVTLD-SL3C3**
 Description: METALUX

0.1699(@277V) [AT MAX POWER AND 5000K]

Spectral Parameters

CCT (K):	4943	CRI (Ra):	85.1		
CIE u':	0.2108	R1:	83.6	R9:	16.8
CIE v':	0.4873	R2:	91.2	R10:	78.4
Duv:	0.0017	R3:	95.3	R11:	82.6
CIE x:	0.3470	R4:	83.2	R12:	60.5
CIE y:	0.3564	R5:	83.4	R13:	86.0
CIE z:	0.2966	R6:	86.5	R14:	97.8
Peak Wavelength (nm):	452	R7:	88.0		
Dominant Wavelength (nm):	571	R8:	69.5		
Purity:	11.1				
Rf:	85.4				
Rg:	95.7				



Test Conditions


Stabilization Time: 70M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.0/52%
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2210-820-18


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	8/8/2022	2/8/2023
Power Meter	XITRON 2801 IN0071	11/29/2021	11/29/2022
AC Power Source	CHROMA 61603 IN0063	11/29/2021	11/29/2022
DC Power Source	AGILENT E3634A IN0208	11/29/2021	11/29/2022
Sphere Thermometer	ONSET IN0085	11/29/2021	11/29/2022
Room Thermometer	ONSET IN0046	11/29/2021	11/29/2022

REPORT NUMBER: SP1-2210-820-18

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2210-820-18

Photopic Flux vs. Wavelength




#####

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	1893	NR	490	34177	NR	620	54916	NR	750	2782	NR	880	1820	NR
365	1545	NR	495	38010	NR	625	51257	NR	755	2500	NR	885	2271	NR
370	1699	NR	500	42146	NR	630	47308	NR	760	2486	NR	890	1534	NR
375	1869	NR	505	46431	NR	635	44039	NR	765	2313	NR	895	1734	NR
380	1777	NR	510	49788	NR	640	39981	NR	770	1952	NR	900	1568	NR
385	1753	NR	515	52380	NR	645	36389	NR	775	1752	NR	905	1643	NR
390	1511	NR	520	54014	NR	650	32774	NR	780	1548	NR	910	1551	NR
395	1483	NR	525	54953	NR	655	29367	NR	785	1620	NR	915	1428	NR
400	1318	NR	530	56065	NR	660	26307	NR	790	1393	NR	920	1468	NR
405	1342	NR	535	57107	NR	665	23364	NR	795	1627	NR	925	1750	NR
410	1469	NR	540	58306	NR	670	20576	NR	800	1553	NR	930	1641	NR
415	2297	NR	545	59230	NR	675	17969	NR	805	1356	NR	935	1881	NR
420	3731	NR	550	60272	NR	680	15411	NR	810	1669	NR	940	2088	NR
425	6912	NR	555	61298	NR	685	13354	NR	815	1647	NR	945	1721	NR
430	12723	NR	560	62528	NR	690	11535	NR	820	1702	NR	950	1281	NR
435	22892	NR	565	63874	NR	695	9837	NR	825	1689	NR	955	2199	NR
440	39880	NR	570	64630	NR	700	8571	NR	830	1456	NR	960	1889	NR
445	68496	NR	575	65183	NR	705	7495	NR	835	1385	NR	965	707	NR
450	101099	NR	580	65979	NR	710	6588	NR	840	1748	NR	970	2458	NR
455	97717	NR	585	66701	NR	715	5938	NR	845	1548	NR	975	2097	NR
460	70276	NR	590	66508	NR	720	5289	NR	850	1920	NR	980	3285	NR
465	54311	NR	595	65934	NR	725	4630	NR	855	1663	NR	985	3054	NR
470	43940	NR	600	65218	NR	730	4073	NR	860	2052	NR	990	2145	NR
475	34008	NR	605	63482	NR	735	3717	NR	865	1849	NR	995	2463	NR
480	30758	NR	610	61041	NR	740	3235	NR	870	1628	NR	1000	3802	NR
485	31504	NR	615	58238	NR	745	2924	NR	875	1526	NR			

REPORT NUMBER: SP1-2210-820-18

Scotopic Flux vs. Wavelength




Scotopic Lumens: 8348.9

S/P: 1.99

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	1893	NR	490	34177	NR	620	54916	NR	750	2782	NR	880	1820	NR
365	1545	NR	495	38010	NR	625	51257	NR	755	2500	NR	885	2271	NR
370	1699	NR	500	42146	NR	630	47308	NR	760	2486	NR	890	1534	NR
375	1869	NR	505	46431	NR	635	44039	NR	765	2313	NR	895	1734	NR
380	1777	NR	510	49788	NR	640	39981	NR	770	1952	NR	900	1568	NR
385	1753	NR	515	52380	NR	645	36389	NR	775	1752	NR	905	1643	NR
390	1511	NR	520	54014	NR	650	32774	NR	780	1548	NR	910	1551	NR
395	1483	NR	525	54953	NR	655	29367	NR	785	1620	NR	915	1428	NR
400	1318	NR	530	56065	NR	660	26307	NR	790	1393	NR	920	1468	NR
405	1342	NR	535	57107	NR	665	23364	NR	795	1627	NR	925	1750	NR
410	1469	NR	540	58306	NR	670	20576	NR	800	1553	NR	930	1641	NR
415	2297	NR	545	59230	NR	675	17969	NR	805	1356	NR	935	1881	NR
420	3731	NR	550	60272	NR	680	15411	NR	810	1669	NR	940	2088	NR
425	6912	NR	555	61298	NR	685	13354	NR	815	1647	NR	945	1721	NR
430	12723	NR	560	62528	NR	690	11535	NR	820	1702	NR	950	1281	NR
435	22892	NR	565	63874	NR	695	9837	NR	825	1689	NR	955	2199	NR
440	39880	NR	570	64630	NR	700	8571	NR	830	1456	NR	960	1889	NR
445	68496	NR	575	65183	NR	705	7495	NR	835	1385	NR	965	707	NR
450	101099	NR	580	65979	NR	710	6588	NR	840	1748	NR	970	2458	NR
455	97717	NR	585	66701	NR	715	5938	NR	845	1548	NR	975	2097	NR
460	70276	NR	590	66508	NR	720	5289	NR	850	1920	NR	980	3285	NR
465	54311	NR	595	65934	NR	725	4630	NR	855	1663	NR	985	3054	NR
470	43940	NR	600	65218	NR	730	4073	NR	860	2052	NR	990	2145	NR
475	34008	NR	605	63482	NR	735	3717	NR	865	1849	NR	995	2463	NR
480	30758	NR	610	61041	NR	740	3235	NR	870	1628	NR	1000	3802	NR
485	31504	NR	615	58238	NR	745	2924	NR	875	1526	NR			

REPORT NUMBER: SP1-2210-820-18

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3536.5 S/P: 0.84

λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)
360	1893	NR	490	34177	NR	620	54916	NR	750	2782	NR	880	1820	NR
365	1545	NR	495	38010	NR	625	51257	NR	755	2500	NR	885	2271	NR
370	1699	NR	500	42146	NR	630	47308	NR	760	2486	NR	890	1534	NR
375	1869	NR	505	46431	NR	635	44039	NR	765	2313	NR	895	1734	NR
380	1777	NR	510	49788	NR	640	39981	NR	770	1952	NR	900	1568	NR
385	1753	NR	515	52380	NR	645	36389	NR	775	1752	NR	905	1643	NR
390	1511	NR	520	54014	NR	650	32774	NR	780	1548	NR	910	1551	NR
395	1483	NR	525	54953	NR	655	29367	NR	785	1620	NR	915	1428	NR
400	1318	NR	530	56065	NR	660	26307	NR	790	1393	NR	920	1468	NR
405	1342	NR	535	57107	NR	665	23364	NR	795	1627	NR	925	1750	NR
410	1469	NR	540	58306	NR	670	20576	NR	800	1553	NR	930	1641	NR
415	2297	NR	545	59230	NR	675	17969	NR	805	1356	NR	935	1881	NR
420	3731	NR	550	60272	NR	680	15411	NR	810	1669	NR	940	2088	NR
425	6912	NR	555	61298	NR	685	13354	NR	815	1647	NR	945	1721	NR
430	12723	NR	560	62528	NR	690	11535	NR	820	1702	NR	950	1281	NR
435	22892	NR	565	63874	NR	695	9837	NR	825	1689	NR	955	2199	NR
440	39880	NR	570	64630	NR	700	8571	NR	830	1456	NR	960	1889	NR
445	68496	NR	575	65183	NR	705	7495	NR	835	1385	NR	965	707	NR
450	101099	NR	580	65979	NR	710	6588	NR	840	1748	NR	970	2458	NR
455	97717	NR	585	66701	NR	715	5938	NR	845	1548	NR	975	2097	NR
460	70276	NR	590	66508	NR	720	5289	NR	850	1920	NR	980	3285	NR
465	54311	NR	595	65934	NR	725	4630	NR	855	1663	NR	985	3054	NR
470	43940	NR	600	65218	NR	730	4073	NR	860	2052	NR	990	2145	NR
475	34008	NR	605	63482	NR	735	3717	NR	865	1849	NR	995	2463	NR
480	30758	NR	610	61041	NR	740	3235	NR	870	1628	NR	1000	3802	NR
485	31504	NR	615	58238	NR	745	2924	NR	875	1526	NR			


REPORT NUMBER: SP1-2210-820-18

TM-30-18





Summary

$R_f = 85.4$
 $R_g = 95.7$
 CIE $R_a = 85.1$
 $R_g = 16.8$

Spectral Power Distribution Comparison



Color Vector Graphics




REPORT NUMBER: SP1-2210-820-18

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)




CES01 = 85	CES26 = 85	CES51 = 94	CES76 = 78
CES02 = 60	CES27 = 92	CES52 = 95	CES77 = 83
CES03 = 31	CES28 = 92	CES53 = 91	CES78 = 76
CES04 = 69	CES29 = 91	CES54 = 90	CES79 = 93
CES05 = 47	CES30 = 93	CES55 = 88	CES80 = 90
CES06 = 50	CES31 = 92	CES56 = 87	CES81 = 83
CES07 = 40	CES32 = 84	CES57 = 86	CES82 = 96
CES08 = 39	CES33 = 97	CES58 = 86	CES83 = 97
CES09 = 29	CES34 = 88	CES59 = 92	CES84 = 91
CES10 = 73	CES35 = 93	CES60 = 90	CES85 = 80
CES11 = 56	CES36 = 81	CES61 = 87	CES86 = 78
CES12 = 62	CES37 = 93	CES62 = 83	CES87 = 86
CES13 = 42	CES38 = 88	CES63 = 87	CES88 = 90
CES14 = 74	CES39 = 98	CES64 = 80	CES89 = 80
CES15 = 71	CES40 = 96	CES65 = 78	CES90 = 90
CES16 = 46	CES41 = 97	CES66 = 77	CES91 = 71
CES17 = 49	CES42 = 93	CES67 = 75	CES92 = 67
CES18 = 56	CES43 = 92	CES68 = 79	CES93 = 80
CES19 = 70	CES44 = 99	CES69 = 83	CES94 = 66
CES20 = 64	CES45 = 95	CES70 = 76	CES95 = 74
CES21 = 85	CES46 = 93	CES71 = 70	CES96 = 85
CES22 = 77	CES47 = 97	CES72 = 90	CES97 = 92
CES23 = 91	CES48 = 86	CES73 = 70	CES98 = 87
CES24 = 90	CES49 = 92	CES74 = 91	CES99 = 78
CES25 = 71	CES50 = 94	CES75 = 73	



REPORT NUMBER: SP1-2210-820-18

TM-30-18



Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2210-820-18

TM-30-18

Measure Comparisons



(END OF REPORT)