

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572773

Luminaire Tested: **FLD4C-25-D010 FEU4C-X-90-30 F4X-N-X-LI-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572773
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-25-D010 FEU4C-X-90-30 F4X-N-X-LI-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3000K, 90 CRI LEDS, 4LBNI TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1703.0 lumens
Efficiency: N/A
Efficacy: 54.1 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572773

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-30 F4X-N-X-LI-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P572773

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-30 F4X-N-X-LI-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108	112	110	108	106		106	104	103		102	101	100		99	98	97
2	109	105	102	99	107	103	100	98		100	98	95		97	95	93		95	93	92
3	105	99	95	92	103	98	94	91		95	92	89		93	90	88		91	89	87
4	101	94	89	86	99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80	95	88	84	80		87	82	79		85	81	79		83	80	78
6	92	85	80	76	91	84	79	76		83	78	75		81	78	75		80	77	74
7	89	81	76	72	88	80	75	72		79	75	71		78	74	71		77	73	71
8	85	77	72	68	84	77	72	68		76	71	68		75	71	68		74	70	67
9	82	74	69	65	81	73	68	65		72	68	65		72	68	65		71	67	64
10	79	71	66	62	78	70	65	62		69	65	62		69	65	62		68	64	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	538405
5°	484510
10°	375606
15°	271863
20°	188236
25°	137235
30°	99713
35°	59001
40°	24810
45°	7731
50°	1013
55°	557
60°	639
65°	756
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P572773

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-30 F4X-N-X-LI-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.4	20.3
10°-20°	591.3	34.7
20°-30°	469.9	27.6
30°-40°	248.8	14.6
40°-50°	42.9	2.5
50°-60°	3.2	0.2
60°-70°	1.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1406.6	82.6
0°-40°	1655.3	97.2
0°-60°	1701.4	99.9
0°-90°	1703.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1703.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4382	
5°	3929	345
15°	2138	591
25°	1012	470
35°	393	249
45°	44	43
55°	3	3
65°	3	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P572773

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-30 F4X-N-X-LI-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	4382.5
2.5°	4269.7
5°	3928.8
7.5°	3483.0
10°	3010.9
12.5°	2554.5
15°	2137.5
17.5°	1749.3
20°	1439.8
22.5°	1203.8
25°	1012.4
27.5°	857.6
30°	702.9
32.5°	545.5
35°	393.4
37.5°	259.7
40°	154.7
42.5°	89.2
45°	44.5
47.5°	15.8
50°	5.3
52.5°	5.3
55°	2.6
57.5°	2.6
60°	2.6
62.5°	2.6
65°	2.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)