

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P861199

Luminaire Tested: **4APVTLD-SL3C3 MID POWER 5000K 120V**

Issue Date: 3/21/2023



Test Information

Test Method: LM-79-08
Report Number: P861199
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2210-820-17)
Test Lab: INNOVATION CENTER
Issue Date: 3/21/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 4APVTLD-SL3C3 MID POWER 5000K 120V
Description: MID POWER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4231.1 lumens
Efficiency: N/A
Efficacy: 127.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.29 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.08')
CIE Type: Direct

Input Watts (W): 33.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P861199

CATALOG NUMBER: 4APVTLD-SL3C3 MID POWER 5000K 120V

Luminous Intensity Polar Plot





TEST NUMBER: P861199

CATALOG NUMBER: 4APVTLD-SL3C3 MID POWER 5000K 120V

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	117	117	117	117		114	114	114	114		107	107	107		101	101	101		95	95	95
1	105	100	95	90		102	97	92	88		91	87	84		86	83	80		81	79	76
2	95	86	79	72		92	83	77	71		79	73	68		74	69	65		70	66	63
3	86	75	66	59		83	73	65	58		69	62	56		65	59	54		61	57	53
4	79	66	57	50		76	64	56	49		61	53	48		58	51	46		55	49	45
5	72	59	50	43		70	57	49	42		54	47	41		52	45	40		49	43	39
6	67	53	44	37		64	52	43	37		49	41	36		47	40	35		44	38	34
7	62	48	39	33		60	47	38	32		44	37	31		42	36	31		40	34	30
8	57	44	35	29		55	43	34	29		41	33	28		39	32	27		37	31	27
9	54	40	32	26		52	39	31	26		37	30	25		36	29	25		34	28	24
10	50	37	29	23		49	36	28	23		35	28	23		33	27	22		32	26	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9922	9922	9922
5°	9820	9732	9762
10°	9760	9539	9539
15°	9666	9349	9345
20°	9558	9148	9127
25°	9431	8921	8895
30°	9276	8688	8676
35°	9102	8447	8496
40°	8938	8217	8310
45°	8723	7991	8156
50°	8493	7782	8022
55°	8215	7571	7862
60°	7870	7335	7718
65°	7479	7082	7561
70°	6921	6790	7430
75°	6107	6494	7261
80°	4948	6173	7114
85°	3441	6013	7156



TEST NUMBER: P861199

CATALOG NUMBER: 4APVTLD-SL3C3 MID POWER 5000K 120V

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.2	2.7
10°-20°	332.7	7.9
20°-30°	503.9	11.9
30°-40°	610.5	14.4
40°-50°	646.3	15.3
50°-60°	611.4	14.4
60°-70°	512.6	12.1
70°-80°	366.2	8.7
80°-90°	216.0	5.1
90°-100°	136.5	3.2
100°-110°	88.9	2.1
110°-120°	51.5	1.2
120°-130°	25.5	0.6
130°-140°	9.1	0.2
140°-150°	2.5	0.1
150°-160°	1.2	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-30°	952.9	22.5
0°-40°	1563.4	36.9
0°-60°	2821.1	66.7
0°-90°	3915.8	92.5
90°-120°	276.9	6.5
90°-150°	313.9	7.4
90°-180°	315.0	7.4
0°-180°	4231.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1229	1229	1229	1229	1229	
5°	1214	1230	1221	1221	1231	115
15°	1163	1179	1176	1183	1193	328
25°	1069	1087	1091	1104	1115	492
35°	937	957	972	996	1013	586
45°	780	804	834	873	893	602
55°	601	634	685	736	758	537
65°	409	455	523	584	608	405
75°	211	273	357	424	450	224
85°	46	119	207	274	298	53
90°	15	78	162	225	248	9
95°	13	57	135	192	215	10
105°	11	29	88	135	153	11
115°	8	11	51	87	102	8
125°	5	6	24	49	60	5
135°	3	4	5	20	27	3
145°	3	3	3	4	5	2
155°	2	2	2	3	3	1
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	



TEST NUMBER: P861199

CATALOG NUMBER: 4APVTLTD-SL3C3 MID POWER 5000K 120V

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1229	1229	1229	1229	1229
2.5°	1220	1234	1225	1225	1229
5°	1214	1230	1221	1221	1231
7.5°	1206	1222	1213	1215	1226
10°	1195	1210	1203	1206	1215
12.5°	1181	1197	1192	1194	1205
15°	1163	1179	1176	1183	1193
17.5°	1144	1160	1158	1168	1177
20°	1121	1138	1139	1148	1159
22.5°	1096	1113	1116	1125	1138
25°	1069	1087	1091	1104	1115
27.5°	1039	1057	1064	1079	1091
30°	1007	1025	1035	1053	1065
32.5°	973	992	1004	1025	1041
35°	937	957	972	996	1013
37.5°	900	921	940	967	984
40°	863	883	905	937	954
42.5°	821	845	871	906	924
45°	780	804	834	873	893
47.5°	737	763	799	840	861
50°	693	722	761	806	829
52.5°	648	678	723	771	794
55°	601	634	685	736	758
57.5°	554	590	645	699	722
60°	505	545	605	662	685
62.5°	459	500	565	623	649
65°	409	455	523	584	608
67.5°	360	408	482	545	569
70°	310	363	439	505	531
72.5°	262	317	400	464	489
75°	211	273	357	424	450
77.5°	164	229	318	384	409
80°	119	188	277	344	370
82.5°	79	151	241	308	333
85°	46	119	207	274	298
87.5°	24	94	181	245	269
90°	15	78	162	225	248
92.5°	14	67	148	208	231
95°	13	57	135	192	215
97.5°	12	49	122	177	198
100°	12	42	110	163	183
102.5°	11	35	98	148	168
105°	11	29	88	135	153



TEST NUMBER: P861199

CATALOG NUMBER: 4APVTLD-SL3C3 MID POWER 5000K 120V

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	9	15	59	98	114
115°	8	11	51	87	102
117.5°	8	9	44	77	91
120°	7	8	36	67	80
122.5°	6	7	30	58	70
125°	5	6	24	49	60
127.5°	4	6	18	41	51
130°	4	5	13	33	42
132.5°	4	5	8	26	34
135°	3	4	5	20	27
137.5°	3	4	5	14	20
140°	3	3	4	9	14
142.5°	3	3	4	5	8
145°	3	3	3	4	5
147.5°	3	2	3	4	4
150°	3	2	3	4	4
152.5°	2	2	3	3	4
155°	2	2	2	3	3
157.5°	3	2	2	3	3
160°	3	2	2	2	3
162.5°	0	0	0	0	0
165°	0	0	0	0	0
167.5°	0	0	0	0	0
170°	0	0	0	0	0
172.5°	0	0	0	0	0
175°	0	0	0	0	0
177.5°	0	0	0	0	0
180°	0	0	0	0	0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - 90°-270°







107.5°	10	24	78	122	140
110°	9	19	68	110	127



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

METALUX

Report Number: SP1-2210-820-18

Test Date: 11/11/2022

Luminaire Tested: 4APVTLD-SL3C3

Data in this report applies to families of products including 4APVTLD-SL3C3.


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2210-820-18
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 11/11/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: METALUX
 Catalog Number: **4APVTLD-SL3C3**
 Description: METALUX

0.1699(@277V) [AT MAX POWER AND 5000K]

Spectral Parameters

CCT (K):	4943	CRI (Ra):	85.1		
CIE u':	0.2108	R1:	83.6	R9:	16.8
CIE v':	0.4873	R2:	91.2	R10:	78.4
Duv:	0.0017	R3:	95.3	R11:	82.6
CIE x:	0.3470	R4:	83.2	R12:	60.5
CIE y:	0.3564	R5:	83.4	R13:	86.0
CIE z:	0.2966	R6:	86.5	R14:	97.8
Peak Wavelength (nm):	452	R7:	88.0		
Dominant Wavelength (nm):	571	R8:	69.5		
Purity:	11.1				
Rf:	85.4				
Rg:	95.7				



Test Conditions


Stabilization Time: 70M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.0/52%
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2210-820-18


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	8/8/2022	2/8/2023
Power Meter	XITRON 2801 IN0071	11/29/2021	11/29/2022
AC Power Source	CHROMA 61603 IN0063	11/29/2021	11/29/2022
DC Power Source	AGILENT E3634A IN0208	11/29/2021	11/29/2022
Sphere Thermometer	ONSET IN0085	11/29/2021	11/29/2022
Room Thermometer	ONSET IN0046	11/29/2021	11/29/2022

REPORT NUMBER: SP1-2210-820-18

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2210-820-18

Photopic Flux vs. Wavelength




#####

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	1893	NR	490	34177	NR	620	54916	NR	750	2782	NR	880	1820	NR
365	1545	NR	495	38010	NR	625	51257	NR	755	2500	NR	885	2271	NR
370	1699	NR	500	42146	NR	630	47308	NR	760	2486	NR	890	1534	NR
375	1869	NR	505	46431	NR	635	44039	NR	765	2313	NR	895	1734	NR
380	1777	NR	510	49788	NR	640	39981	NR	770	1952	NR	900	1568	NR
385	1753	NR	515	52380	NR	645	36389	NR	775	1752	NR	905	1643	NR
390	1511	NR	520	54014	NR	650	32774	NR	780	1548	NR	910	1551	NR
395	1483	NR	525	54953	NR	655	29367	NR	785	1620	NR	915	1428	NR
400	1318	NR	530	56065	NR	660	26307	NR	790	1393	NR	920	1468	NR
405	1342	NR	535	57107	NR	665	23364	NR	795	1627	NR	925	1750	NR
410	1469	NR	540	58306	NR	670	20576	NR	800	1553	NR	930	1641	NR
415	2297	NR	545	59230	NR	675	17969	NR	805	1356	NR	935	1881	NR
420	3731	NR	550	60272	NR	680	15411	NR	810	1669	NR	940	2088	NR
425	6912	NR	555	61298	NR	685	13354	NR	815	1647	NR	945	1721	NR
430	12723	NR	560	62528	NR	690	11535	NR	820	1702	NR	950	1281	NR
435	22892	NR	565	63874	NR	695	9837	NR	825	1689	NR	955	2199	NR
440	39880	NR	570	64630	NR	700	8571	NR	830	1456	NR	960	1889	NR
445	68496	NR	575	65183	NR	705	7495	NR	835	1385	NR	965	707	NR
450	101099	NR	580	65979	NR	710	6588	NR	840	1748	NR	970	2458	NR
455	97717	NR	585	66701	NR	715	5938	NR	845	1548	NR	975	2097	NR
460	70276	NR	590	66508	NR	720	5289	NR	850	1920	NR	980	3285	NR
465	54311	NR	595	65934	NR	725	4630	NR	855	1663	NR	985	3054	NR
470	43940	NR	600	65218	NR	730	4073	NR	860	2052	NR	990	2145	NR
475	34008	NR	605	63482	NR	735	3717	NR	865	1849	NR	995	2463	NR
480	30758	NR	610	61041	NR	740	3235	NR	870	1628	NR	1000	3802	NR
485	31504	NR	615	58238	NR	745	2924	NR	875	1526	NR			

REPORT NUMBER: SP1-2210-820-18

Scotopic Flux vs. Wavelength




Scotopic Lumens: 8348.9

S/P: 1.99

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	1893	NR	490	34177	NR	620	54916	NR	750	2782	NR	880	1820	NR
365	1545	NR	495	38010	NR	625	51257	NR	755	2500	NR	885	2271	NR
370	1699	NR	500	42146	NR	630	47308	NR	760	2486	NR	890	1534	NR
375	1869	NR	505	46431	NR	635	44039	NR	765	2313	NR	895	1734	NR
380	1777	NR	510	49788	NR	640	39981	NR	770	1952	NR	900	1568	NR
385	1753	NR	515	52380	NR	645	36389	NR	775	1752	NR	905	1643	NR
390	1511	NR	520	54014	NR	650	32774	NR	780	1548	NR	910	1551	NR
395	1483	NR	525	54953	NR	655	29367	NR	785	1620	NR	915	1428	NR
400	1318	NR	530	56065	NR	660	26307	NR	790	1393	NR	920	1468	NR
405	1342	NR	535	57107	NR	665	23364	NR	795	1627	NR	925	1750	NR
410	1469	NR	540	58306	NR	670	20576	NR	800	1553	NR	930	1641	NR
415	2297	NR	545	59230	NR	675	17969	NR	805	1356	NR	935	1881	NR
420	3731	NR	550	60272	NR	680	15411	NR	810	1669	NR	940	2088	NR
425	6912	NR	555	61298	NR	685	13354	NR	815	1647	NR	945	1721	NR
430	12723	NR	560	62528	NR	690	11535	NR	820	1702	NR	950	1281	NR
435	22892	NR	565	63874	NR	695	9837	NR	825	1689	NR	955	2199	NR
440	39880	NR	570	64630	NR	700	8571	NR	830	1456	NR	960	1889	NR
445	68496	NR	575	65183	NR	705	7495	NR	835	1385	NR	965	707	NR
450	101099	NR	580	65979	NR	710	6588	NR	840	1748	NR	970	2458	NR
455	97717	NR	585	66701	NR	715	5938	NR	845	1548	NR	975	2097	NR
460	70276	NR	590	66508	NR	720	5289	NR	850	1920	NR	980	3285	NR
465	54311	NR	595	65934	NR	725	4630	NR	855	1663	NR	985	3054	NR
470	43940	NR	600	65218	NR	730	4073	NR	860	2052	NR	990	2145	NR
475	34008	NR	605	63482	NR	735	3717	NR	865	1849	NR	995	2463	NR
480	30758	NR	610	61041	NR	740	3235	NR	870	1628	NR	1000	3802	NR
485	31504	NR	615	58238	NR	745	2924	NR	875	1526	NR			

REPORT NUMBER: SP1-2210-820-18

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3536.5 S/P: 0.84

λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)
360	1893	NR	490	34177	NR	620	54916	NR	750	2782	NR	880	1820	NR
365	1545	NR	495	38010	NR	625	51257	NR	755	2500	NR	885	2271	NR
370	1699	NR	500	42146	NR	630	47308	NR	760	2486	NR	890	1534	NR
375	1869	NR	505	46431	NR	635	44039	NR	765	2313	NR	895	1734	NR
380	1777	NR	510	49788	NR	640	39981	NR	770	1952	NR	900	1568	NR
385	1753	NR	515	52380	NR	645	36389	NR	775	1752	NR	905	1643	NR
390	1511	NR	520	54014	NR	650	32774	NR	780	1548	NR	910	1551	NR
395	1483	NR	525	54953	NR	655	29367	NR	785	1620	NR	915	1428	NR
400	1318	NR	530	56065	NR	660	26307	NR	790	1393	NR	920	1468	NR
405	1342	NR	535	57107	NR	665	23364	NR	795	1627	NR	925	1750	NR
410	1469	NR	540	58306	NR	670	20576	NR	800	1553	NR	930	1641	NR
415	2297	NR	545	59230	NR	675	17969	NR	805	1356	NR	935	1881	NR
420	3731	NR	550	60272	NR	680	15411	NR	810	1669	NR	940	2088	NR
425	6912	NR	555	61298	NR	685	13354	NR	815	1647	NR	945	1721	NR
430	12723	NR	560	62528	NR	690	11535	NR	820	1702	NR	950	1281	NR
435	22892	NR	565	63874	NR	695	9837	NR	825	1689	NR	955	2199	NR
440	39880	NR	570	64630	NR	700	8571	NR	830	1456	NR	960	1889	NR
445	68496	NR	575	65183	NR	705	7495	NR	835	1385	NR	965	707	NR
450	101099	NR	580	65979	NR	710	6588	NR	840	1748	NR	970	2458	NR
455	97717	NR	585	66701	NR	715	5938	NR	845	1548	NR	975	2097	NR
460	70276	NR	590	66508	NR	720	5289	NR	850	1920	NR	980	3285	NR
465	54311	NR	595	65934	NR	725	4630	NR	855	1663	NR	985	3054	NR
470	43940	NR	600	65218	NR	730	4073	NR	860	2052	NR	990	2145	NR
475	34008	NR	605	63482	NR	735	3717	NR	865	1849	NR	995	2463	NR
480	30758	NR	610	61041	NR	740	3235	NR	870	1628	NR	1000	3802	NR
485	31504	NR	615	58238	NR	745	2924	NR	875	1526	NR			


REPORT NUMBER: SP1-2210-820-18

TM-30-18





Summary

$R_f = 85.4$
 $R_g = 95.7$
 CIE $R_a = 85.1$
 $R_g = 16.8$

Spectral Power Distribution Comparison



Color Vector Graphics




REPORT NUMBER: SP1-2210-820-18

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)




CES01 = 85	CES26 = 85	CES51 = 94	CES76 = 78
CES02 = 60	CES27 = 92	CES52 = 95	CES77 = 83
CES03 = 31	CES28 = 92	CES53 = 91	CES78 = 76
CES04 = 69	CES29 = 91	CES54 = 90	CES79 = 93
CES05 = 47	CES30 = 93	CES55 = 88	CES80 = 90
CES06 = 50	CES31 = 92	CES56 = 87	CES81 = 83
CES07 = 40	CES32 = 84	CES57 = 86	CES82 = 96
CES08 = 39	CES33 = 97	CES58 = 86	CES83 = 97
CES09 = 29	CES34 = 88	CES59 = 92	CES84 = 91
CES10 = 73	CES35 = 93	CES60 = 90	CES85 = 80
CES11 = 56	CES36 = 81	CES61 = 87	CES86 = 78
CES12 = 62	CES37 = 93	CES62 = 83	CES87 = 86
CES13 = 42	CES38 = 88	CES63 = 87	CES88 = 90
CES14 = 74	CES39 = 98	CES64 = 80	CES89 = 80
CES15 = 71	CES40 = 96	CES65 = 78	CES90 = 90
CES16 = 46	CES41 = 97	CES66 = 77	CES91 = 71
CES17 = 49	CES42 = 93	CES67 = 75	CES92 = 67
CES18 = 56	CES43 = 92	CES68 = 79	CES93 = 80
CES19 = 70	CES44 = 99	CES69 = 83	CES94 = 66
CES20 = 64	CES45 = 95	CES70 = 76	CES95 = 74
CES21 = 85	CES46 = 93	CES71 = 70	CES96 = 85
CES22 = 77	CES47 = 97	CES72 = 90	CES97 = 92
CES23 = 91	CES48 = 86	CES73 = 70	CES98 = 87
CES24 = 90	CES49 = 92	CES74 = 91	CES99 = 78
CES25 = 71	CES50 = 94	CES75 = 73	



REPORT NUMBER: SP1-2210-820-18

TM-30-18



Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2210-820-18

TM-30-18

Measure Comparisons



(END OF REPORT)