

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572831

Luminaire Tested: **FLD4C-25-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572831
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-25-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBMH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1859.0 lumens
Efficiency: N/A
Efficacy: 59.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572831

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P572831

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	100		100	99	97		97	96	95
2	107	102	98	94		105	100	96	93		97	94	91		94	91	89		91	89	87
3	101	94	89	85		99	93	88	84		90	86	83		88	84	82		86	83	80
4	96	88	82	77		94	86	81	77		84	80	76		82	78	75		80	77	74
5	90	82	75	71		89	81	75	70		79	74	70		77	73	69		75	72	69
6	86	76	70	65		84	75	69	65		74	68	64		72	68	64		71	67	64
7	81	71	65	60		80	70	64	60		69	64	60		68	63	59		67	62	59
8	77	67	60	56		75	66	60	56		65	59	56		64	59	55		63	58	55
9	73	63	56	52		72	62	56	52		61	56	52		60	55	52		59	55	52
10	69	59	53	49		68	59	53	49		58	52	49		57	52	48		56	52	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	226456
5°	223165
10°	213844
15°	201973
20°	188537
25°	171150
30°	142895
35°	103514
40°	64807
45°	37042
50°	19304
55°	10817
60°	6904
65°	4070
70°	3017
75°	1329
80°	1981
85°	0



TEST NUMBER: P572831

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.6	9.1
10°-20°	445.0	23.9
20°-30°	571.9	30.8
30°-40°	430.3	23.1
40°-50°	172.8	9.3
50°-60°	49.1	2.6
60°-70°	15.5	0.8
70°-80°	4.4	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1186.5	63.8
0°-40°	1616.7	87.0
0°-60°	1838.7	98.9
0°-90°	1859.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1859.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1843	
5°	1810	170
15°	1588	445
25°	1263	572
35°	690	430
45°	213	173
55°	50	49
65°	14	16
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P572831

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	1843.3
2.5°	1832.1
5°	1809.6
7.5°	1767.5
10°	1714.2
12.5°	1649.8
15°	1588.0
17.5°	1517.9
20°	1442.1
22.5°	1360.8
25°	1262.6
27.5°	1144.7
30°	1007.3
32.5°	852.9
35°	690.2
37.5°	538.7
40°	404.1
42.5°	297.4
45°	213.2
47.5°	146.0
50°	101.0
52.5°	70.2
55°	50.5
57.5°	36.5
60°	28.1
62.5°	19.6
65°	14.0
67.5°	11.2
70°	8.4
72.5°	5.6
75°	2.8
77.5°	2.8
80°	2.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)