

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572839

Luminaire Tested: **FLD4C-25-D010 FEU4C-X-90-40 F4X-N-X-H-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572839
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-25-D010 FEU4C-X-90-40 F4X-N-X-H-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBNH TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1468.0 lumens
Efficiency: N/A
Efficacy: 46.6 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572839

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-40 F4X-N-X-H-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P572839

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-40 F4X-N-X-H-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	94		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	89	83	79		86	82	78		84	81	78		83	79	77
5	92	84	78	74		91	83	78	73		81	76	73		80	75	72		78	74	72
6	88	79	73	69		86	78	72	68		77	72	68		75	71	67		74	70	67
7	83	74	68	64		82	73	68	64		72	67	63		71	66	63		70	66	63
8	79	70	64	60		78	69	64	60		68	63	59		67	63	59		66	62	59
9	76	66	60	56		74	65	60	56		65	59	56		64	59	56		63	59	55
10	72	62	57	53		71	62	56	53		61	56	53		60	56	52		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	226431
5°	221401
10°	204700
15°	183684
20°	161697
25°	139160
30°	112054
35°	74598
40°	38810
45°	17565
50°	7626
55°	5119
60°	3268
65°	2326
70°	1904
75°	1282
80°	0
85°	0



TEST NUMBER: P572839

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-40 F4X-N-X-H-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.3	11.3
10°-20°	403.4	27.5
20°-30°	468.3	31.9
30°-40°	310.1	21.1
40°-50°	87.0	5.9
50°-60°	21.9	1.5
60°-70°	8.2	0.6
70°-80°	2.8	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1038.0	70.7
0°-40°	1348.1	91.8
0°-60°	1457.0	99.2
0°-90°	1468.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1468.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1843	
5°	1795	166
15°	1444	403
25°	1027	468
35°	497	310
45°	101	87
55°	24	22
65°	8	8
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P572839

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-40 F4X-N-X-H-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	1843.1
2.5°	1835.1
5°	1795.3
7.5°	1726.0
10°	1640.9
12.5°	1545.2
15°	1444.2
17.5°	1345.7
20°	1236.8
22.5°	1135.7
25°	1026.6
27.5°	922.9
30°	789.9
32.5°	648.9
35°	497.4
37.5°	356.4
40°	242.0
42.5°	156.9
45°	101.1
47.5°	61.2
50°	39.9
52.5°	29.2
55°	23.9
57.5°	18.7
60°	13.3
62.5°	10.7
65°	8.0
67.5°	5.3
70°	5.3
72.5°	2.7
75°	2.7
77.5°	2.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)