

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572855

Luminaire Tested: **FLD4C-25-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572855
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-25-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2066.0 lumens
Efficiency: N/A
Efficacy: 65.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572855

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P572855

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91		103	98	93	90		95	91	88		91	88	86		89	86	84
3	99	91	85	80		97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	77	72		90	82	76	71		80	75	70		78	73	70		76	72	69
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	58		80	70	63	58		68	62	58		67	61	57		65	61	57
7	76	65	58	53		75	65	58	53		63	57	53		62	56	52		61	56	52
8	72	60	53	49		70	60	53	49		59	53	48		58	52	48		57	52	48
9	68	56	49	45		66	56	49	45		55	49	44		54	48	44		53	48	44
10	64	52	46	41		63	52	46	41		51	45	41		50	45	41		49	44	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	163604
5°	164229
10°	164718
15°	164733
20°	163828
25°	159994
30°	149534
35°	129490
40°	101164
45°	72572
50°	47151
55°	28230
60°	16512
65°	10610
70°	7040
75°	5316
80°	3962
85°	0



TEST NUMBER: P572855

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.8	6.1
10°-20°	365.4	17.7
20°-30°	539.2	26.1
30°-40°	532.1	25.8
40°-50°	325.6	15.8
50°-60°	124.9	6.0
60°-70°	39.0	1.9
70°-80°	11.4	0.6
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1031.4	49.9
0°-40°	1563.5	75.7
0°-60°	2014.0	97.5
0°-90°	2066.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2066.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1332	
5°	1332	127
15°	1295	365
25°	1180	539
35°	863	532
45°	418	326
55°	132	125
65°	36	39
75°	11	11
85°	0	2
90°	0	



TEST NUMBER: P572855

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-40 F4X-W-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	1331.7
2.5°	1334.5
5°	1331.7
7.5°	1328.9
10°	1320.4
12.5°	1309.2
15°	1295.2
17.5°	1278.3
20°	1253.1
22.5°	1225.2
25°	1180.3
27.5°	1124.1
30°	1054.1
32.5°	967.2
35°	863.4
37.5°	748.5
40°	630.8
42.5°	521.4
45°	417.7
47.5°	325.1
50°	246.7
52.5°	182.3
55°	131.8
57.5°	92.5
60°	67.2
62.5°	50.5
65°	36.5
67.5°	28.1
70°	19.6
72.5°	14.0
75°	11.2
77.5°	5.6
80°	5.6
82.5°	2.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)