

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572873

Luminaire Tested: **FLD4C-25-D010 FEU4C-X-90-50 F4X-M-X-LI-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572873
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-25-D010 FEU4C-X-90-50 F4X-M-X-LI-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBMLI TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2366.0 lumens
Efficiency: N/A
Efficacy: 75.1 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572873

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-50 F4X-M-X-LI-BL89BV

Luminous Intensity Polar Plot



TEST NUMBER: P572873

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-50 F4X-M-X-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94						
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88						
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82						
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76						
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71						
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67						
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63						
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59						
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55						
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	363757
5°	360300
10°	341412
15°	309981
20°	273909
25°	236799
30°	185112
35°	113517
40°	58264
45°	23142
50°	7511
55°	2592
60°	2211
65°	1773
70°	1114
75°	1471
80°	0
85°	0



TEST NUMBER: P572873

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-50 F4X-M-X-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	272.8	11.5
10°-20°	679.1	28.7
20°-30°	789.4	33.4
30°-40°	483.4	20.4
40°-50°	120.0	5.1
50°-60°	14.0	0.6
60°-70°	5.3	0.2
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1741.3	73.6
0°-40°	2224.7	94.0
0°-60°	2358.7	99.7
0°-90°	2366.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2366.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2961	
5°	2922	273
15°	2437	679
25°	1747	789
35°	757	483
45°	133	120
55°	12	14
65°	6	5
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P572873

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-50 F4X-M-X-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	2960.9
2.5°	2957.9
5°	2921.6
7.5°	2842.8
10°	2736.8
12.5°	2597.6
15°	2437.2
17.5°	2264.6
20°	2095.1
22.5°	1925.5
25°	1746.9
27.5°	1541.0
30°	1304.9
32.5°	1029.4
35°	756.9
37.5°	532.8
40°	363.3
42.5°	227.0
45°	133.2
47.5°	75.7
50°	39.3
52.5°	18.2
55°	12.1
57.5°	9.0
60°	9.0
62.5°	6.1
65°	6.1
67.5°	3.1
70°	3.1
72.5°	3.1
75°	3.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)