

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572865

Luminaire Tested: **FLD4C-25-D010 FEU4C-X-90-50 F4X-M-X-H-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572865
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-25-D010 FEU4C-X-90-50 F4X-M-X-H-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBMH TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1742.9 lumens
Efficiency: N/A
Efficacy: 55.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572865

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-50 F4X-M-X-H-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P572865

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-50 F4X-M-X-H-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	113	110	108	105		111	108	106	104		104	102	100			100	99	97			97
2	107	102	98	94		105	100	96	93		97	94	91			94	91	89			91
3	101	94	89	85		99	93	88	84		90	86	83			88	84	82			86
4	96	88	82	77		94	86	81	77		84	80	76			82	78	75			80
5	90	82	75	71		89	81	75	70		79	74	70			77	73	69			75
6	86	76	70	65		84	75	69	65		74	68	64			72	68	64			71
7	81	71	65	60		80	70	64	60		69	64	60			68	63	59			67
8	77	67	60	56		75	66	60	56		65	59	56			64	59	55			63
9	73	63	56	52		72	62	56	52		61	56	52			60	55	52			59
10	69	59	53	49		68	59	53	49		58	52	49			57	52	48			56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	212328
5°	209242
10°	200496
15°	189369
20°	176771
25°	160469
30°	133972
35°	97065
40°	60750
45°	34731
50°	18100
55°	10153
60°	6462
65°	3837
70°	2838
75°	1234
80°	1839
85°	0



TEST NUMBER: P572865

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-50 F4X-M-X-H-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.0	9.1
10°-20°	417.2	23.9
20°-30°	536.2	30.8
30°-40°	403.4	23.1
40°-50°	162.0	9.3
50°-60°	46.1	2.6
60°-70°	14.6	0.8
70°-80°	4.1	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1112.4	63.8
0°-40°	1515.8	87.0
0°-60°	1723.9	98.9
0°-90°	1742.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1742.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1728	
5°	1697	159
15°	1489	417
25°	1184	536
35°	647	403
45°	200	162
55°	47	46
65°	13	15
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P572865

CATALOG NUMBER: FLD4C-25-D010 FEU4C-X-90-50 F4X-M-X-H-BL86

CANDELA DISTRIBUTION (FULL):

0°	
0°	1728.3
2.5°	1717.8
5°	1696.7
7.5°	1657.2
10°	1607.2
12.5°	1546.8
15°	1488.9
17.5°	1423.1
20°	1352.1
22.5°	1275.9
25°	1183.8
27.5°	1073.2
30°	944.4
32.5°	799.7
35°	647.2
37.5°	505.0
40°	378.8
42.5°	278.8
45°	199.9
47.5°	136.8
50°	94.7
52.5°	65.8
55°	47.4
57.5°	34.2
60°	26.3
62.5°	18.4
65°	13.2
67.5°	10.5
70°	7.9
72.5°	5.3
75°	2.6
77.5°	2.6
80°	2.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)