

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P572995

Luminaire Tested: **FLD4C-30-D010 FEU4C-X-90-35 F4X-W-X-H-BL84**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P572995
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-30-D010 FEU4C-X-90-35 F4X-W-X-H-BL84
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWH TRIM
AND BOTTOM LENS, 0.125" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2302.0 lumens
Efficiency: N/A
Efficacy: 72.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P572995

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-35 F4X-W-X-H-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P572995

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-35 F4X-W-X-H-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91		103	98	93	90		95	91	88		91	88	86		89	86	84
3	99	91	85	80		97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	77	72		90	82	76	71		80	75	70		78	73	70		76	72	69
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	58		80	70	63	58		68	62	58		67	61	57		65	61	57
7	76	65	58	53		75	65	58	53		63	57	53		62	56	52		61	56	52
8	72	60	53	49		70	60	53	49		59	53	48		58	52	48		57	52	48
9	68	56	49	45		66	56	49	45		55	49	44		54	48	44		53	48	44
10	64	52	46	41		63	52	46	41		51	45	41		50	45	41		49	44	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	182290
5°	182986
10°	183543
15°	183544
20°	182536
25°	178267
30°	166613
35°	144277
40°	112711
45°	80876
50°	52541
55°	31443
60°	18403
65°	11802
70°	7866
75°	5933
80°	4457
85°	0



TEST NUMBER: P572995

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-35 F4X-W-X-H-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.3	6.1
10°-20°	407.1	17.7
20°-30°	600.8	26.1
30°-40°	592.9	25.8
40°-50°	362.8	15.8
50°-60°	139.1	6.0
60°-70°	43.5	1.9
70°-80°	12.8	0.6
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1149.2	49.9
0°-40°	1742.1	75.7
0°-60°	2244.1	97.5
0°-90°	2302.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2302.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1484	
5°	1484	141
15°	1443	407
25°	1315	601
35°	962	593
45°	466	363
55°	147	139
65°	41	43
75°	12	13
85°	0	2
90°	0	



TEST NUMBER: P572995

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-35 F4X-W-X-H-BL84

CANDELA DISTRIBUTION (FULL):

	0°
0°	1483.8
2.5°	1486.9
5°	1483.8
7.5°	1480.6
10°	1471.3
12.5°	1458.8
15°	1443.1
17.5°	1424.4
20°	1396.2
22.5°	1365.1
25°	1315.1
27.5°	1252.5
30°	1174.5
32.5°	1077.7
35°	962.0
37.5°	834.0
40°	702.8
42.5°	581.0
45°	465.5
47.5°	362.3
50°	274.9
52.5°	203.1
55°	146.8
57.5°	103.0
60°	74.9
62.5°	56.3
65°	40.6
67.5°	31.3
70°	21.9
72.5°	15.6
75°	12.5
77.5°	6.3
80°	6.3
82.5°	3.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)