

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573003

Luminaire Tested: **FLD4C-30-D010 FEU4C-X-90-35 F4X-W-X-LI-BL86**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573003
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-30-D010 FEU4C-X-90-35 F4X-W-X-LI-BL86
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 4LBWLI TRIM
AND BOTTOM LENS, 0.250" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2637.0 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573003

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-35 F4X-W-X-LI-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P573003

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-35 F4X-W-X-LI-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	198494
5°	201855
10°	210987
15°	223939
20°	233746
25°	231716
30°	215498
35°	184351
40°	140455
45°	82388
50°	35205
55°	10367
60°	2973
65°	1744
70°	1078
75°	1424
80°	0
85°	0



TEST NUMBER: P573003

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-35 F4X-W-X-LI-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.0	6.0
10°-20°	498.6	18.9
20°-30°	777.9	29.5
30°-40°	756.9	28.7
40°-50°	378.0	14.3
50°-60°	58.5	2.2
60°-70°	7.1	0.3
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1434.5	54.4
0°-40°	2191.4	83.1
0°-60°	2628.0	99.7
0°-90°	2637.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2637.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1616	
5°	1637	158
15°	1761	499
25°	1709	778
35°	1229	757
45°	474	378
55°	48	59
65°	6	7
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P573003

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-35 F4X-W-X-LI-BL86

CANDELA DISTRIBUTION (FULL):

	0°
0°	1615.7
2.5°	1621.7
5°	1636.8
7.5°	1661.0
10°	1691.3
12.5°	1730.4
15°	1760.7
17.5°	1784.9
20°	1787.9
22.5°	1766.7
25°	1709.4
27.5°	1624.7
30°	1519.1
32.5°	1386.3
35°	1229.2
37.5°	1057.0
40°	875.8
42.5°	682.6
45°	474.2
47.5°	305.0
50°	184.2
52.5°	99.6
55°	48.4
57.5°	21.2
60°	12.1
62.5°	9.1
65°	6.0
67.5°	6.0
70°	3.0
72.5°	3.0
75°	3.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)