

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573008

Luminaire Tested: **FLD4C-30-D010 FEU4C-X-90-40 F4X-M-X-H-BL85**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573008
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-30-D010 FEU4C-X-90-40 F4X-M-X-H-BL85
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBMH TRIM
AND BOTTOM LENS, 0.187" CLEAR POLYCARBONATE

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1978.0 lumens
Efficiency: N/A
Efficacy: 62.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573008

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-40 F4X-M-X-H-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P573008

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-40 F4X-M-X-H-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	100		100	99	97		97	96	95
2	107	102	98	94		105	100	96	93		97	94	91		94	91	89		91	89	87
3	101	94	89	85		99	93	88	84		90	86	83		88	84	82		86	83	80
4	96	88	82	77		94	86	81	77		84	80	76		82	78	75		80	77	74
5	90	82	75	71		89	81	75	70		79	74	70		77	73	69		75	72	69
6	86	76	70	65		84	75	69	65		74	68	64		72	68	64		71	67	64
7	81	71	65	60		80	70	64	60		69	64	60		68	63	59		67	62	59
8	77	67	60	56		75	66	60	56		65	59	56		64	59	55		63	58	55
9	73	63	56	52		72	62	56	52		61	56	52		60	55	52		59	55	52
10	69	59	53	49		68	59	53	49		58	52	49		57	52	48		56	52	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	240953
5°	237458
10°	227529
15°	214908
20°	200604
25°	182103
30°	152030
35°	110143
40°	68945
45°	39404
50°	20546
55°	11523
60°	7347
65°	4331
70°	3233
75°	1424
80°	2122
85°	0



TEST NUMBER: P573008

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-40 F4X-M-X-H-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.5	9.1
10°-20°	473.5	23.9
20°-30°	608.5	30.8
30°-40°	457.8	23.1
40°-50°	183.8	9.3
50°-60°	52.3	2.6
60°-70°	16.5	0.8
70°-80°	4.7	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1262.4	63.8
0°-40°	1720.2	87.0
0°-60°	1956.3	98.9
0°-90°	1978.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1978.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1961	
5°	1926	180
15°	1690	473
25°	1343	608
35°	734	458
45°	227	184
55°	54	52
65°	15	17
75°	3	5
85°	0	0
90°	0	



TEST NUMBER: P573008

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-40 F4X-M-X-H-BL85

CANDELA DISTRIBUTION (FULL):

0°	
0°	1961.3
2.5°	1949.4
5°	1925.5
7.5°	1880.7
10°	1823.9
12.5°	1755.4
15°	1689.7
17.5°	1615.0
20°	1534.4
22.5°	1447.9
25°	1343.4
27.5°	1217.9
30°	1071.7
32.5°	907.5
35°	734.4
37.5°	573.1
40°	429.9
42.5°	316.4
45°	226.8
47.5°	155.3
50°	107.5
52.5°	74.7
55°	53.8
57.5°	38.8
60°	29.9
62.5°	20.9
65°	14.9
67.5°	11.9
70°	9.0
72.5°	6.0
75°	3.0
77.5°	3.0
80°	3.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)