

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P573011

Luminaire Tested: **FLD4C-30-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P573011
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD4C-30-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV
Description: 4 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBMH TRIM
AND BOTTOM LENS, 0.125" CLEAR ACRYLIC

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2182.0 lumens
Efficiency: N/A
Efficacy: 69.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P573011

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P573011

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	100		100	99	97		97	96	95
2	107	102	98	94		105	100	96	93		97	94	91		94	91	89		91	89	87
3	101	94	89	85		99	93	88	84		90	86	83		88	84	82		86	83	80
4	96	88	82	77		94	86	81	77		84	80	76		82	78	75		80	77	74
5	90	82	75	71		89	81	75	70		79	74	70		77	73	69		75	72	69
6	86	76	70	65		84	75	69	65		74	68	64		72	68	64		71	67	64
7	81	71	65	60		80	70	64	60		69	64	60		68	63	59		67	62	59
8	77	67	60	56		75	66	60	56		65	59	56		64	59	55		63	58	55
9	73	63	56	52		72	62	56	52		61	56	52		60	55	52		59	55	52
10	69	59	53	49		68	59	53	49		58	52	49		57	52	48		56	52	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	265806
5°	261950
10°	250994
15°	237064
20°	221287
25°	200877
30°	167720
35°	121496
40°	76065
45°	43470
50°	22668
55°	12701
60°	8084
65°	4796
70°	3556
75°	1566
80°	2335
85°	0



TEST NUMBER: P573011

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.1	9.1
10°-20°	522.3	23.9
20°-30°	671.2	30.8
30°-40°	505.0	23.1
40°-50°	202.8	9.3
50°-60°	57.7	2.6
60°-70°	18.3	0.8
70°-80°	5.2	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1392.6	63.8
0°-40°	1897.6	87.0
0°-60°	2158.1	98.9
0°-90°	2182.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2182.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2164	
5°	2124	199
15°	1864	522
25°	1482	671
35°	810	505
45°	250	203
55°	59	58
65°	16	18
75°	3	5
85°	0	0
90°	0	



TEST NUMBER: P573011

CATALOG NUMBER: FLD4C-30-D010 FEU4C-X-90-40 F4X-M-X-H-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	2163.6
2.5°	2150.4
5°	2124.1
7.5°	2074.6
10°	2012.0
12.5°	1936.4
15°	1863.9
17.5°	1781.6
20°	1692.6
22.5°	1597.2
25°	1481.9
27.5°	1343.6
30°	1182.3
32.5°	1001.1
35°	810.1
37.5°	632.2
40°	474.3
42.5°	349.1
45°	250.2
47.5°	171.3
50°	118.6
52.5°	82.4
55°	59.3
57.5°	42.8
60°	32.9
62.5°	23.1
65°	16.5
67.5°	13.2
70°	9.9
72.5°	6.6
75°	3.3
77.5°	3.3
80°	3.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)